

**WDK 2.5V ZQV OR****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

To feed through power, signal, and data is the classical requirement in electrical engineering and panel building. The insulating material, the connection system and the design of the terminal blocks are the differentiating features. A feed-through terminal block is suitable for joining and/or connecting one or more conductors. They could have one or more connection levels that are on the same potential or insulated against one another.

**General ordering data**

|            |   |
|------------|---|
| Version    | Multi-tier modular terminal, Screw connection, orange, 2.5 mm <sup>2</sup> , 400 V, 800 V, Number of connections: 4, Number of levels: 2, TS 35, V-0, Wemid |
| Order No.  | <a href="#">2732600000</a>  |
| Type       | WDK 2.5V ZQV OR   |
| GTIN (EAN) | 4050118820409   |
| Qty.       | 50 pc(s).   |

**WDK 2.5V ZQV OR****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

|            |          |                 |            |
|------------|----------|-----------------|------------|
| Depth      | 62.5 mm  | Depth (inches)  | 2.461 inch |
| Height     | 69.5 mm  | Height (inches) | 2.736 inch |
| Width      | 5.1 mm   | Width (inches)  | 0.201 inch |
| Net weight | 13.376 g |                 |            |

**Temperatures**

|                                  |                |                                  |        |
|----------------------------------|----------------|----------------------------------|--------|
| Storage temperature              | -25 °C...55 °C | Continuous operating temp., min. | -60 °C |
| Continuous operating temp., max. | 130 °C         |                                  |        |

**Material data**

|                           |       |        |        |
|---------------------------|-------|--------|--------|
| Material                  | Wemid | Colour | orange |
| UL 94 flammability rating | V-0   |        |        |

**Rating data IECEx/ATEX**

|                                |                   |                                 |                   |
|--------------------------------|-------------------|---------------------------------|-------------------|
| Certificate No. (ATEX)         | DEMKO15ATEX1346U  | Certificate No. (IECEX)         | IECEXULD15.0003U  |
| Max. voltage (ATEX)            | 275 V             | Current (ATEX)                  | 21 A              |
| Wire cross section max. (ATEX) | 4 mm <sup>2</sup> | Max. voltage (IECEX)            | 275 V             |
| Current (IECEX)                | 21 A              | Wire cross section max. (IECEX) | 4 mm <sup>2</sup> |

**System specifications**

|                                     |  |                               |       |
|-------------------------------------|--|-------------------------------|-------|
| Version                             | Screw connection, for plug-in cross-connector, One end without connector | End cover plate required      | Yes   |
| Number of potentials                | 1  | Number of levels              | 2     |
| Number of clamping points per level | 2  | Number of potentials per tier | 1     |
| Levels cross-connected internally   | Yes  | Rail                          | TS 35 |
| N-function                          | No   | PE function                   | No    |
| PEN function                        | No   |                               |       |

**2 clampable conductors (H05V/H07V) with equal cross-section (rated connection)**

|  |                     |  |                     |
|--|---------------------|--|---------------------|
| Wire connection cross section, finely stranded with wire-end ferrules DIN 46228/1, 2 clampable wires, max. | 1.5 mm <sup>2</sup> | Wire connection cross section, finely stranded with wire-end ferrules DIN 46228/1, 2 clampable wires, min. | 0.5 mm <sup>2</sup> |
| Wire connection cross section, finely stranded, two clampable wires, min.                                  | 0.5 mm <sup>2</sup> | Wire cross-section, finely stranded, two clampable wires, max.   | 1.5 mm <sup>2</sup> |

**Additional technical data**

|                          |         |                |         |
|--------------------------|---------|----------------|---------|
| Explosion-tested version | Yes     | Open sides     | right   |
| Snap-on                  | Yes     | Type of fixing | Snap-on |
| Type of mounting         | Snap-on |                |         |

**CSA rating data**

|                               |                 |                               |        |
|-------------------------------|-----------------|-------------------------------|--------|
| Certificate No. (CSA)         | 200039-80051002 | Current size B (CSA)          | 25 A   |
| Current size C (CSA)          | 25 A            | Current size D (CSA)          | 5 A    |
| Voltage size B (CSA)          | 600 V           | Voltage size C (CSA)          | 600 V  |
| Voltage size D (CSA)          | 600 V           | Wire cross section max. (CSA) | 12 AWG |
| Wire cross section min. (CSA) | 30 AWG          |                               |        |

Creation date August 28, 2024 9:37:21 PM CEST

## WDK 2.5V ZQV OR

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Conductors for clamping (additional connection)

Connection type, additional connection Screw connection

## Conductors for clamping (rated connection)

|   |                      |   |                     |
|---|----------------------|---|---------------------|
| Blade size  | 0.6 x 3.5 mm         | Clamping range, max.  | 4 mm <sup>2</sup>   |
| Clamping range, min.  | 0.05 mm <sup>2</sup> | Connection cross-section, stranded, max.  | 4 mm <sup>2</sup>   |
| Connection cross-section, stranded, min.  | 0.5 mm <sup>2</sup>  | Connection direction  | on side             |
| Gauge to IEC 60947-1  | A3                   | Number of connections   | 4                   |
| Stripping length  | 10 mm                | Type of connection  | Screw connection    |
| Type of connection 2  | Screw connection     | Wire connection cross section AWG, max.   | AWG 12              |
| Wire connection cross section AWG, min.   | AWG 30               | Wire connection cross section, finely stranded, max.                                    | 4 mm <sup>2</sup>   |
| Wire connection cross section, finely stranded, min.                                    | 0.5 mm <sup>2</sup>  | Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max. | 2.5 mm <sup>2</sup> |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min. | 0.5 mm <sup>2</sup>  | Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max. | 2.5 mm <sup>2</sup> |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min. | 0.5 mm <sup>2</sup>  | Wire connection cross-section, solid core, max.   | 4 mm <sup>2</sup>   |
| Wire connection cross-section, solid core, min.   | 0.5 mm <sup>2</sup>  |   |                     |

## General

|   |        |   |               |
|---|--------|---|---------------|
| Rail                                    | TS 35  | Standards                               | IEC 60947-7-1 |
| Wire connection cross section AWG, max. | AWG 12 | Wire connection cross section AWG, min. | AWG 30        |

## Rating data

|                        |                     |                    |       |
|------------------------|---------------------|--------------------|-------|
| Rated cross-section    | 2.5 mm <sup>2</sup> | Rated voltage      | 400 V |
| Rated DC voltage       | 400 V               | Rated current      | 24 A  |
| Standards              | IEC 60947-7-1       | Pollution severity | 3     |
| Surge voltage category | III                 |                    |       |

## UL rating data

|   |        |   |        |
|---|--------|---|--------|
| Certificate No. (UR)                    | E60693 | Conductor size Factory wiring max. (UR) | 12 AWG |
| Conductor size Factory wiring min. (UR) | 30 AWG | Conductor size Field wiring max. (UR)   | 12 AWG |
| Conductor size Field wiring min. (UR)   | 22 AWG | Current size B (UR)                     | 20 A   |
| Current size C (UR)                     | 20 A   | Voltage size B (UR)                     | 600 V  |
| Voltage size C (UR)                     | 600 V  |   |        |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000897    | ETIM 7.0    | EC000897    |
| ETIM 8.0    | EC000897    | ETIM 9.0    | EC000897    |
| ECLASS 9.0  | 27-14-11-20 | ECLASS 9.1  | 27-14-11-20 |
| ECLASS 10.0 | 27-14-11-20 | ECLASS 11.0 | 27-14-11-20 |
| ECLASS 12.0 | 27-14-11-20 | ECLASS 13.0 | 27-25-01-02 |
| ECLASS 14.0 | 27-25-01-02 |             |             |

## WDK 2.5V ZQV OR

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

## Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| REACH SVHC             | /                           |
| RoHS Compliance Status | Compliant without exemption |

## Approvals

Approvals



|                       |            |
|-----------------------|------------|
| ROHS                  | Conform    |
| UL File Number Search | UL Website |
| Certificate No. (UR)  | E60693     |

## Downloads


|   |   |
|---|---|
| Approval/Certificate/Document of Conformity | <a href="#">Attestation of Conformity</a><br><a href="#">Attestation of Conformity</a><br><a href="#">UKCA Ex Attestation of Conformity</a><br><a href="#">IECEX Certificate</a><br><a href="#">ATEX Certificate</a><br><a href="#">UKCA Ex Certificate</a><br><a href="#">UKCA declaration of conformity</a><br><a href="#">Confirmation of Standards EN 45545-2_2020-10</a> |
| Engineering Data                            | <a href="#">CAD data – STEP</a>   |
| User Documentation                          | <a href="#">NTI WDK 2.5 V ZQV</a>   |
| Catalogues                                  | <a href="#">Catalogues in PDF-format</a>  |

### WDK 2.5V ZQV OR

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings



## WDK 2.5V ZQV OR

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## W-Series



Test adapters and test plugs are used for the electrical connection between terminal blocks and the test equipment. In this way, an electrical contact can be established in the wired state and measurements can be done easily.

## General ordering data

|            |                            |   |
|------------|----------------------------|---|
| Type       | WTA 4N/ZA WDK 2.5          | Version   |
| Order No.  | <a href="#">1879350000</a> | Test adapter (terminal), 1.5 mm <sup>2</sup> , 250 V, 6 A |
| GTIN (EAN) | 4032248503261              |   |
| Qty.       | 25 pc(s).                  |   |
| Type       | WTA 4N WDK 2.5             | Version   |
| Order No.  | <a href="#">1878660000</a> | Test adapter (terminal), 1.5 mm <sup>2</sup> , 250 V, 6 A |
| GTIN (EAN) | 4032248503285              |   |
| Qty.       | 25 pc(s).                  |   |

## Shielding connection



With the LS 2.8 WDU2.5-10, many feed-through modular terminal blocks from the W series can be converted very easily. Inserting the LS 2.8 WDU2.5-10 allows the cable shielding braid to be looped through directly at the terminal block by soldering or using a suitable flat cable lug.

## General ordering data

|            |                            |                      |
|------------|----------------------------|----------------------|
| Type       | LS 2.8 WDU2.5-10           | Version              |
| Order No.  | <a href="#">1056400000</a> | W-Series, Shield bus |
| GTIN (EAN) | 4008190036454              |                      |
| Qty.       | 100 pc(s).                 |                      |

## WDK 2.5V ZQV OR

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## WS 8/5



## WS/ DEK

MultiMark terminal markers use an innovative composite material made from two components. The hard base contour of the marker snaps securely into the connector. The elastic surface finish makes the marker easy to mount. This specially punched material enables the strips to be stretched to accommodate the slight variations in spacing that tend to add up, especially with long terminal blocks. Another advantage: the excellent printability of the surface material guarantees durable and wear-resistant labelling. A print resolution of 300 dpi also produces a very legible script.

## Your benefits with MultiMark

- Firm hold and durable printing
- Continuous strips save installation time
- Easy mounting thanks to an innovative composite material
- Large label field for optimal legibility
- High flexibility thanks to manufacturer independence

## General ordering data

|            |                            |   |
|------------|----------------------------|---|
| Type       | WS 8/5 MM WS               | Version   |
| Order No.  | <a href="#">2007150000</a> | WS, Terminal marker, 8 x 5 mm, Weidmueller, white |
| GTIN (EAN) | 4050118392029              |   |
| Qty.       | 800 pc(s).                 |   |

## W-Series



Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

## General ordering data

|            |                            |  |
|------------|----------------------------|--|
| Type       | WEW 35/2                   | Version  |
| Order No.  | <a href="#">1061200000</a> | End bracket, dark beige, TS 35, HB, Wemid, Width: 8 mm, 100 °C |
| GTIN (EAN) | 4008190030230              |  |
| Qty.       | 50 pc(s).                  |  |

## WDK 2.5V ZQV OR

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## W-Series



Warning covers with a flash symbol provide more safety for man and machine. They are used where external voltage must be indicated within the application.

## General ordering data

|            |                            |  |
|------------|----------------------------|--|
| Type       | WAD 4 WS                   | Version  |
| Order No.  | <a href="#">1072100000</a> | Terminal cover, white, PA 66, Height: 19.8 mm, Width: 4.5 mm,  |
| GTIN (EAN) | 4008190446116              | Depth: 9.6 mm, V-2   |
| Qty.       | 50 pc(s).                  |  |
| Type       | WAD 4 GE BED               | Version  |
| Order No.  | <a href="#">1072000000</a> | Terminal cover, yellow, PA 66, Height: 19.8 mm, Width: 4.5 mm, |
| GTIN (EAN) | 4008190446109              | Depth: 9.6 mm, V-2   |
| Qty.       | 50 pc(s).                  |  |

## Blank



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

|            |                            |   |
|------------|----------------------------|---|
| Type       | DEK 5/5 MC NE WS           | Version   |
| Order No.  | <a href="#">1609801044</a> | Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 |
| GTIN (EAN) | 4008190397111              | Weidmueller, white  |
| Qty.       | 1,000 pc(s).               |   |



## WDK 2.5V ZQV OR

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

2.5 mm<sup>2</sup>


2.5  
mm<sup>2</sup>

The plug-in cross-connections feature easy handling and quick installation. This saves a great deal of time during installation in comparison with screwed solutions.

## General ordering data

|            |                            |  |
|------------|----------------------------|--|
| Type       | ZQV 2.5N/2 RD              | Version  |
| Order No.  | <a href="#">2108470000</a> | Cross-connector (terminal), Plugged, red, 24 A, Number of poles: 2,    |
| GTIN (EAN) | 4050118448542              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 7.9 mm                   |
| Qty.       | 60 pc(s).                  |  |
| Type       | ZQV 2.5N/2                 | Version  |
| Order No.  | <a href="#">1527540000</a> | Cross-connector (terminal), Plugged, orange, 24 A, Number of poles: 2, |
| GTIN (EAN) | 4050118448467              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 7.9 mm                   |
| Qty.       | 60 pc(s).                  |  |
| Type       | ZQV 2.5N/7 BL              | Version  |
| Order No.  | <a href="#">1527830000</a> | Cross-connector (terminal), Plugged, blue, 24 A, Number of poles: 7,   |
| GTIN (EAN) | 4050118448603              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 33.4 mm                  |
| Qty.       | 20 pc(s).                  |  |
| Type       | ZQV 2.5N/5 BL              | Version  |
| Order No.  | <a href="#">1527790000</a> | Cross-connector (terminal), Plugged, blue, 24 A, Number of poles: 5,   |
| GTIN (EAN) | 4050118448627              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 23.2 mm                  |
| Qty.       | 20 pc(s).                  |  |
| Type       | ZQV 2.5N/4 BL              | Version  |
| Order No.  | <a href="#">1527780000</a> | Cross-connector (terminal), Plugged, blue, 24 A, Number of poles: 4,   |
| GTIN (EAN) | 4050118448634              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 18.1 mm                  |
| Qty.       | 60 pc(s).                  |  |
| Type       | ZQV 2.5N/2 BL              | Version  |
| Order No.  | <a href="#">1527740000</a> | Cross-connector (terminal), Plugged, blue, 24 A, Number of poles: 2,   |
| GTIN (EAN) | 4050118448658              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 7.9 mm                   |
| Qty.       | 60 pc(s).                  |  |
| Type       | ZQV 2.5N/5 RD              | Version  |
| Order No.  | <a href="#">2108710000</a> | Cross-connector (terminal), Plugged, red, 24 A, Number of poles: 5,    |
| GTIN (EAN) | 4050118448511              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 23.2 mm                  |
| Qty.       | 20 pc(s).                  |  |
| Type       | ZQV 2.5N/9 BL              | Version  |
| Order No.  | <a href="#">1527870000</a> | Cross-connector (terminal), Plugged, blue, 24 A, Number of poles: 9,   |
| GTIN (EAN) | 4050118448580              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 43.6 mm                  |
| Qty.       | 20 pc(s).                  |  |
| Type       | ZQV 2.5N/8                 | Version  |
| Order No.  | <a href="#">1527670000</a> | Cross-connector (terminal), Plugged, orange, 24 A, Number of poles: 8, |
| GTIN (EAN) | 4050118448405              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 38.5 mm                  |
| Qty.       | 20 pc(s).                  |  |
| Type       | ZQV 2.5N/4                 | Version  |
| Order No.  | <a href="#">1527590000</a> | Cross-connector (terminal), Plugged, orange, 24 A, Number of poles: 4, |
| GTIN (EAN) | 4050118448443              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 18.1 mm                  |
| Qty.       | 60 pc(s).                  |  |

Creation date August 28, 2024 9:37:21 PM CEST

Catalogue status 17.08.2024 / We reserve the right to make technical changes.

## WDK 2.5V ZQV OR

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

|            |                            |   |
|------------|----------------------------|---|
| Type       | ZQV 2.5N/50 RD             | Version   |
| Order No.  | <a href="#">2109000000</a> | Cross-connector (terminal), Plugged, red, 24 A, Number of poles: 50,  |
| GTIN (EAN) | 4050118486001              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 255 mm                  |
| Qty.       | 5 pc(s).                   |   |
| Type       | ZQV 2.5N/6                 | Version   |
| Order No.  | <a href="#">1527630000</a> | Cross-connector (terminal), Plugged, orange, 24 A, Number of poles:   |
| GTIN (EAN) | 4050118448429              | 6, Pitch in mm (P): 5.10, Insulated: Yes, Width: 28.3 mm              |
| Qty.       | 20 pc(s).                  |   |
| Type       | ZQV 2.5N/20 BL             | Version   |
| Order No.  | <a href="#">1527890000</a> | Cross-connector (terminal), Plugged, blue, 24 A, Number of poles: 20, |
| GTIN (EAN) | 4050118448566              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 102 mm                  |
| Qty.       | 20 pc(s).                  |   |
| Type       | ZQV 2.5N/9                 | Version   |
| Order No.  | <a href="#">1527680000</a> | Cross-connector (terminal), Plugged, orange, 24 A, Number of poles:   |
| GTIN (EAN) | 4050118447996              | 9, Pitch in mm (P): 5.10, Insulated: Yes, Width: 43.6 mm              |
| Qty.       | 20 pc(s).                  |   |
| Type       | ZQV 2.5N/20 RD             | Version   |
| Order No.  | <a href="#">2108920000</a> | Cross-connector (terminal), Plugged, red, 24 A, Number of poles: 20,  |
| GTIN (EAN) | 4050118485899              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 102 mm                  |
| Qty.       | 20 pc(s).                  |   |
| Type       | ZQV 2.5N/8 BL              | Version   |
| Order No.  | <a href="#">1527840000</a> | Cross-connector (terminal), Plugged, blue, 24 A, Number of poles: 8,  |
| GTIN (EAN) | 4050118448597              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 38.5 mm                 |
| Qty.       | 20 pc(s).                  |   |
| Type       | ZQV 2.5N/3 RD              | Version   |
| Order No.  | <a href="#">2108690000</a> | Cross-connector (terminal), Plugged, red, 24 A, Number of poles: 3,   |
| GTIN (EAN) | 4050118448535              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 13 mm                   |
| Qty.       | 60 pc(s).                  |   |
| Type       | ZQV 2.5N/6 RD              | Version   |
| Order No.  | <a href="#">2108720000</a> | Cross-connector (terminal), Plugged, red, 24 A, Number of poles: 6,   |
| GTIN (EAN) | 4050118448504              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 28.3 mm                 |
| Qty.       | 20 pc(s).                  |   |
| Type       | ZQV 2.5N/10 BL             | Version   |
| Order No.  | <a href="#">1527880000</a> | Cross-connector (terminal), Plugged, blue, 24 A, Number of poles: 10, |
| GTIN (EAN) | 4050118448573              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 48.7 mm                 |
| Qty.       | 20 pc(s).                  |   |
| Type       | ZQV 2.5N/4 RD              | Version   |
| Order No.  | <a href="#">2108700000</a> | Cross-connector (terminal), Plugged, red, 24 A, Number of poles: 4,   |
| GTIN (EAN) | 4050118448528              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 18.1 mm                 |
| Qty.       | 60 pc(s).                  |   |
| Type       | ZQV 2.5N/7                 | Version   |
| Order No.  | <a href="#">1527640000</a> | Cross-connector (terminal), Plugged, orange, 24 A, Number of poles:   |
| GTIN (EAN) | 4050118448412              | 7, Pitch in mm (P): 5.10, Insulated: Yes, Width: 33.4 mm              |
| Qty.       | 20 pc(s).                  |   |
| Type       | ZQV 2.5N/9 RD              | Version   |
| Order No.  | <a href="#">2108900000</a> | Cross-connector (terminal), Plugged, red, 24 A, Number of poles: 9,   |
| GTIN (EAN) | 4050118448474              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 43.6 mm                 |
| Qty.       | 20 pc(s).                  |   |
| Type       | ZQV 2.5N/6 BL              | Version   |
| Order No.  | <a href="#">1527820000</a> | Cross-connector (terminal), Plugged, blue, 24 A, Number of poles: 6,  |
| GTIN (EAN) | 4050118448610              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 28.3 mm                 |
| Qty.       | 20 pc(s).                  |   |

Creation date August 28, 2024 9:37:21 PM CEST

Catalogue status 17.08.2024 / We reserve the right to make technical changes.

10

## WDK 2.5V ZQV OR

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

|            |                            |   |
|------------|----------------------------|---|
| Type       | ZQV 2.5N/8 RD              | Version   |
| Order No.  | <a href="#">2108870000</a> | Cross-connector (terminal), Plugged, red, 24 A, Number of poles: 8,   |
| GTIN (EAN) | 4050118448481              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 38.5 mm                 |
| Qty.       | 20 pc(s).                  |   |
| Type       | ZQV 2.5N/3                 | Version   |
| Order No.  | <a href="#">1527570000</a> | Cross-connector (terminal), Plugged, orange, 24 A, Number of poles:   |
| GTIN (EAN) | 4050118448450              | 3, Pitch in mm (P): 5.10, Insulated: Yes, Width: 13 mm                |
| Qty.       | 60 pc(s).                  |   |
| Type       | ZQV 2.5N/50                | Version   |
| Order No.  | <a href="#">1527730000</a> | Cross-connector (terminal), Plugged, orange, 24 A, Number of poles:   |
| GTIN (EAN) | 4050118411362              | 50, Pitch in mm (P): 5.10, Insulated: Yes, Width: 255 mm              |
| Qty.       | 5 pc(s).                   |   |
| Type       | ZQV 2.5N/5                 | Version   |
| Order No.  | <a href="#">1527620000</a> | Cross-connector (terminal), Plugged, orange, 24 A, Number of poles:   |
| GTIN (EAN) | 4050118448436              | 5, Pitch in mm (P): 5.10, Insulated: Yes, Width: 23.2 mm              |
| Qty.       | 20 pc(s).                  |   |
| Type       | ZQV 2.5N/3 BL              | Version   |
| Order No.  | <a href="#">1527770000</a> | Cross-connector (terminal), Plugged, blue, 24 A, Number of poles: 3,  |
| GTIN (EAN) | 4050118448641              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 13 mm                   |
| Qty.       | 60 pc(s).                  |   |
| Type       | ZQV 2.5N/10 RD             | Version   |
| Order No.  | <a href="#">2108910000</a> | Cross-connector (terminal), Plugged, red, 24 A, Number of poles: 10,  |
| GTIN (EAN) | 4050118486018              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 48.7 mm                 |
| Qty.       | 20 pc(s).                  |   |
| Type       | ZQV 2.5N/7 RD              | Version   |
| Order No.  | <a href="#">2108810000</a> | Cross-connector (terminal), Plugged, red, 24 A, Number of poles: 7,   |
| GTIN (EAN) | 4050118448498              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 33.4 mm                 |
| Qty.       | 20 pc(s).                  |   |
| Type       | ZQV 2.5N/20                | Version   |
| Order No.  | <a href="#">1527720000</a> | Cross-connector (terminal), Plugged, orange, 24 A, Number of poles:   |
| GTIN (EAN) | 4050118447972              | 20, Pitch in mm (P): 5.10, Insulated: Yes, Width: 102 mm              |
| Qty.       | 20 pc(s).                  |   |
| Type       | ZQV 2.5N/10                | Version   |
| Order No.  | <a href="#">1527690000</a> | Cross-connector (terminal), Plugged, orange, 24 A, Number of poles:   |
| GTIN (EAN) | 4050118447989              | 10, Pitch in mm (P): 5.10, Insulated: Yes, Width: 48.7 mm             |
| Qty.       | 20 pc(s).                  |   |
| Type       | ZQV 2.5N/50 BL             | Version   |
| Order No.  | <a href="#">1527920000</a> | Cross-connector (terminal), Plugged, blue, 24 A, Number of poles: 50, |
| GTIN (EAN) | 4050118448559              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 255 mm                  |
| Qty.       | 5 pc(s).                   |   |

## WDK 2.5V ZQV OR

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

### Test plugs



Test adapters and test plugs are used for the electrical connection between terminal blocks and the test equipment. In this way, an electrical contact can be established in the wired state and measurements can be done easily.

#### General ordering data

| Type       | PS_ZQV                     | Version                               |
|------------|----------------------------|---------------------------------------|
| Order No.  | <a href="#">1121740000</a> | Test adapter (terminal), 1000 V, 20 A |
| GTIN (EAN) | 4032248902675              |                                       |
| Qty.       | 1 pc(s).                   |                                       |
| Type       | PS_ZQV_SET                 | Version                               |
| Order No.  | <a href="#">1116710000</a> | Test adapter (terminal), 1000 V, 20 A |
| GTIN (EAN) | 4032248911455              |                                       |
| Qty.       | 1 pc(s).                   |                                       |

### Marker holder



The marker holder offer the possibility of additional mounting of standard markers with a pitch of 5 or 5.1 mm. The angled holders can be optionally snapped together and could be mounted in all standard marking channels of the Klippon<sup>®</sup> Connect modular terminal blocks. Fitting marker types could be found under the respective accessories of the designation marking holder.

#### General ordering data

| Type       | BZT 1 WS 10/5              | Version                    |
|------------|----------------------------|----------------------------|
| Order No.  | <a href="#">1805490000</a> | Accessories, Marker holder |
| GTIN (EAN) | 4032248270231              |                            |
| Qty.       | 100 pc(s).                 |                            |
| Type       | BZT 1 ZA WS 10/5           | Version                    |
| Order No.  | <a href="#">1805520000</a> | Accessories, Marker holder |
| GTIN (EAN) | 4032248270248              |                            |
| Qty.       | 100 pc(s).                 |                            |

## WDK 2.5V ZQV OR

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

2.5 mm<sup>2</sup>2.5  
mm<sup>2</sup>

End plates are fitted to the open side of the last modular terminal before the end bracket. The use of an end plate ensures the function of the modular terminal and the specified rated voltage. It guarantees protection against contact with live parts and makes the final terminal finger-proof.

## General ordering data

|            |                            |   |
|------------|----------------------------|---|
| Type       | WAP WDK2.5 BL              | Version   |
| Order No.  | <a href="#">1059180000</a> | End plate (terminals), blue, Height: 69 mm, Width: 1.5 mm, V-0,       |
| GTIN (EAN) | 4008190081089              | Wemid   |
| Qty.       | 20 pc(s).                  |   |
| Type       | WAP WDK2.5                 | Version   |
| Order No.  | <a href="#">1059100000</a> | End plate (terminals), dark beige, Height: 69 mm, Width: 1.5 mm, V-0, |
| GTIN (EAN) | 4008190101954              | Wemid   |
| Qty.       | 20 pc(s).                  |   |

## W-Series

W  
Series

A partition plate is used for the optical separation of circuits or used for electrical isolation from neighbouring cross-connectors. In contrast to the end plate, the contour can be larger than the adjacent terminal blocks. However, it should not be smaller, as otherwise the required clearance and creepage distances within the application can no longer be maintained.

## General ordering data

|            |                            |   |
|------------|----------------------------|---|
| Type       | WZR WDK2.5                 | Version   |
| Order No.  | <a href="#">1074000000</a> | W-Series, Intermediate frame  |
| GTIN (EAN) | 4008190890384              |   |
| Qty.       | 20 pc(s).                  |   |
| Type       | WTW EN                     | Version   |
| Order No.  | <a href="#">1058800000</a> | Partition plate (terminal), dark beige, Height: 86 mm, Width: 3 mm, |
| GTIN (EAN) | 4008190140175              | V-0, Wemid  |
| Qty.       | 20 pc(s).                  |   |

**WDK 2.5V ZQV OR****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Blank**

WS markers are the perfect match for the W-series connectors. Thanks to their system compatibility, the WS tags can also be used with the I-series and the Z-series. The large marking surfaces do not only permit long character strings but also multi-line text. WS markers are ideal for labels with long, customised character strings. Thanks to the proven MultiCard format, printing with PrintJet CONNECT oder/or Plotter is possible.

- Can be fitted in strips or individually
- Markers in proven MultiCard format

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

**General ordering data**

|            |                            |   |
|------------|----------------------------|---|
| Type       | WS 8/5 MC NE WS            | Version   |
| Order No.  | <a href="#">1640740000</a> | WS, Terminal marker, 8 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, |
| GTIN (EAN) | 4008190279103              | Allen-Bradley, white  |
| Qty.       | 720 pc(s).                 |   |