

**FP PRO TOP3 24/20 2P****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

PROtop power supplies offer a wide range of functions with many advantages.

These include high energy efficiency, outstanding power reserves, high reliability and optional communication capability. PROtop also supports direct parallel connection with load balancing. With the possibility of integrating our PROtop power supplies into the FieldPower® system, the entire range of functions becomes available in the field – with all the advantages of the FieldPower® modular system.

**General ordering data**

Version	FieldPower® power supply unit, IP65, in closed state, in complete state, 20A, 24 V, DC, IDC terminal, PUSH IN, M12, A-coded
Order No.	<a href="#">2743450000</a>
Type	FP PRO TOP3 24/20 2P
GTIN (EAN)	4050118846966
Qty.	1 pc(s).

## FP PRO TOP3 24/20 2P

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	220 mm	Depth (inches)	8.661 inch
Height	196 mm	Height (inches)	7.717 inch
Width	196 mm	Width (inches)	7.717 inch
Net weight	4,211 g		

## Temperatures

Storage temperature	-10 °C...60 °C	Operating temperature	-25 °C...45 °C
Operating temperature range	-25 °C ... +45 °C (regard derating) Start up ≥ -40 °C	Humidity	35...85%, non condensing and non freezing

## Input

AC current consumption	1,5 A @ 400 V DC / 2 A @ 320 V AC	AC input voltage range	3 x 320...3 x 575 V AC / 2 x 360...2 x 575 V AC
DC input voltage range	450...800 V DC (max. 500 V DC acc. to UL508)	Frequency range AC	45...65 Hz
Recommended back-up fuse	3 - 5 A, Char C	Surge protection	Varistor
Inrush current	Max. 10 A	Input fuse (internal)	5 A F (6.3 x 32 mm)

## Output

Adjustable rated current	No	Output current	20A
Output power	480 W	Output voltage	24 V
Output voltage type	DC	Output voltage, max.	28.8 V
Output voltage, min.	22.5 V	Output voltage, note	(adjustable via potentiometer)
Switch-on delay	1 s	Triggering characteristic	see characteristic curve
Rated output voltage	24 V DC ± 1 %	Nominal output current for U <sub>nom</sub>	20 A @ 60 °C

## General data

Humidity	35...85%, non condensing and non freezing	Installation advice	Lid screws included
Protection degree	IP65, in closed state, in complete state	Short-circuit protection	Yes, internal
Standards	UL 508	Surge voltage category	III, II

## Insulation coordination

Surge voltage category	III, II
------------------------	---------

## Connection data (input)

Connection system	IDC terminal
-------------------	--------------

## Approbations

Certificate no. (cULus)	E258476	Institute (cULus)	CULUS
-------------------------	---------	-------------------	-------

**FP PRO TOP3 24/20 2P**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data****Clamping capacity**

Connection data - contact element power bus

Wire connection method	Insulation displacement connection (IDC)
Blade size of operating tool	0.6 x 3.5 mm
Number of poles	5
Conductor connection cross-section, solid, max.	6 mm <sup>2</sup>
Conductor connection cross-section, solid, min.	1.5 mm <sup>2</sup>
Conductor connection cross-section, stranded, max.	6 mm <sup>2</sup>
Conductor connection cross-section, stranded, min.	2.5 mm <sup>2</sup>
Conductor connection cross-section, finely stranded, max.	6 mm <sup>2</sup>
Conductor connection cross-section, finely stranded, min.	2.5 mm <sup>2</sup>
Conductor connection cross-section, finest stranded, max.	6 mm <sup>2</sup>
Conductor connection cross-section, finest stranded, min.	2.5 mm <sup>2</sup>

## FP PRO TOP3 24/20 2P

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

Connection data - contact element Branch / Feed-in	Wire connection method		PUSH IN
	Blade size of operating tool		0.6 x 3.5 mm
	Stripping length		14 mm
	Number of poles		5
	Conductor connection cross-section, solid, max.		6 mm <sup>2</sup>
	Conductor connection cross-section, solid, min.		0.5 mm <sup>2</sup>
	Conductor connection cross-section, stranded, max.		6 mm <sup>2</sup>
	Conductor connection cross-section, stranded, min.		0.5 mm <sup>2</sup>
	Conductor connection cross-section, finely stranded, max.		10 mm <sup>2</sup>
	Conductor connection cross-section, finely stranded, min.		0.5 mm <sup>2</sup>
	Conductor connection cross-section, finest stranded, max.		6 mm <sup>2</sup>
	Conductor connection cross-section, finest stranded, min.		0.5 mm <sup>2</sup>
	Conductor connection cross-section with wire end ferrule	Type of wire end ferrule	12 mm with plastic collar
		Standard	DIN 46228/1
		Cross-section, min.	0.5 mm <sup>2</sup>
		Cross-section, max.	6 mm <sup>2</sup>
		Type of wire end ferrule	12 mm with plastic collar
		Standard	DIN 46228/4
		Cross-section, min.	0.5 mm <sup>2</sup>
		Cross-section, max.	6 mm <sup>2</sup>
		Type of wire end ferrule	8 mm with plastic collar
		Standard	DIN 46228/1
		Cross-section, min.	0.5 mm <sup>2</sup>
		Cross-section, max.	6 mm <sup>2</sup>
		Type of wire end ferrule	8 mm with plastic collar
		Standard	DIN 46228/4
		Cross-section, min.	0.5 mm <sup>2</sup>
		Cross-section, max.	6 mm <sup>2</sup>
		Type of wire end ferrule	Twin wire-end ferrules
		Cross-section, min.	0.5 mm <sup>2</sup>
		Cross-section, max.	6 mm <sup>2</sup>

## Rated data acc. to IEC

Rated data acc. to IEC for contact element	Voltage type		AC, DC
	Standard		IEC 60947-7-1, IEC 60947-7-2
	Rated voltage		800 V
	Rated impulse withstand voltage		8 kV
	Rated current (3 loaded poles)		41 A
	Rated current (4 loaded poles)		25 A
Rated data acc. to IEC for fuse plug	Voltage type		AC
	Number of phases		3
	Standard		IEC 61984, IEC 60947-7-3
	Rated voltage		36 V
	Rated impulse withstand voltage		6 kV
	Rated current		12 A

## FP PRO TOP3 24/20 2P

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

Rated data acc. to IEC for plug-in connector

Voltage type	DC
Standard	IEC 60947-7-1, IEC 60947-7-2, IEC 61984
Rated voltage	690 V
Rated impulse withstand voltage	8 kV
Rated current (3 loaded poles)	32 A
Rated current (4 loaded poles)	25 A

## Rated data acc. to UL

Rated data acc. to UL for contact element

Standard	UL 1059
Note	for use with UL-listed TC-ER cables
Conductor connection cross-section, AWG, max.	AWG 10
Conductor connection cross-section, AWG, min.	AWG 14
Rated voltage	600 V
Rated current	30 A

Rated data acc. to UL for fuse plug

Rated data acc. to UL for plug-in connector

Standard	UL 1059
Note	for use with UL-listed TC-ER cables
Conductor connection cross-section, AWG, max.	AWG 12
Conductor connection cross-section, AWG, min.	AWG 16
Rated voltage	600 V
Rated current	20 A

Standards

UL 508

## Classifications

ETIM 6.0	EC002540	ETIM 7.0	EC002540
ETIM 8.0	EC002540	ETIM 9.0	EC002540
ECLASS 9.1	27-04-07-01	ECLASS 10.0	27-04-07-01
ECLASS 11.0	27-04-07-01	ECLASS 12.0	27-04-07-01
ECLASS 13.0	27-04-90-02		

## Environmental Product Compliance

REACH SVHC

Lead 7439-92-1 Potassium perfluorobutane sulfonate 29420-49-3

SCIP

7645f3b1-6db9-495d-9e21-ab1d894aff05

## Approvals

Approvals



ROHS

Conform

UL File Number Search

UL Website

Certificate no. (cULus)

E258476

**FP PRO TOP3 24/20 2P****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Downloads**Approval/Certificate/Document of Con-  
formity[CE Declaration of Conformity Fieldpower® PROtop and topGUARD](#)

Engineering Data

[CAD data – STEP](#)

Product Change Notification

[Produktänderungsmitteilung FieldPower® PROtop](#)[Product Change Notification FieldPower® PROtop](#)[Technical change to FieldPower® IP65 power supplies](#)[Technische Änderung für FieldPower® IP65 Stromversorgungen](#)

User Documentation

[Manual FieldPower® PT6 IEC cURus](#)[Manual FieldPower® PROtop size 2](#)

Catalogues




[Catalogues in PDF-format](#)

## FP PRO TOP3 24/20 2P

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings



M12 A-coded	FP PRO TOP3 ... 2P	FP PRO TOP3 24/20 2PIOL
1	13	L+
2	I/O	n.c.
3	GND	L-
4	14	C/Q

