

**HDC C HS BM0.08-0.12 AU****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Crimps provide a electrical and mechanical connection between wire and contact that is both secure and reliable. The optimal crimp connection is gas-tight and corrosion-resistant.

**General ordering data**

Version	Female, gold, 0.08 - 0.12 mm <sup>2</sup>
Order No.	<a href="#">2748730000</a>
Type	HDC C HS BM0.08-0.12 AU
GTIN (EAN)	4050118890549
Qty.	100 pc(s).

**HDC C HS BM0.08-0.12 AU****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Net weight	0.18 g
------------	--------

**Temperatures**

Limit temperature	-55 °C ... 130 °C
-------------------	-------------------

**General data**

Conductor cross-section, max.	0.12 mm <sup>2</sup>	Conductor cross-section, min.	0.08 mm <sup>2</sup>
Cross-section for connected wire	0.08 - 0.12 mm <sup>2</sup>	Material	Copper alloy
Surface finish	gold	Type	Female
Type of connection	Crimp connection	Wire connection cross section AWG, max.	AWG 28
Wire connection cross section AWG, min.	AWG 24		

**Classifications**

ETIM 6.0	EC000796	ETIM 7.0	EC000796
ETIM 8.0	EC000796	ETIM 9.0	EC000796
ECLASS 9.0	27-44-02-04	ECLASS 9.1	27-44-02-04
ECLASS 10.0	27-44-02-04	ECLASS 11.0	27-44-02-04
ECLASS 12.0	27-44-02-04	ECLASS 13.0	27-44-02-04

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
SCIP	6eabd5ae-2d6b-409e-8bdf-87c27ee10e40

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Engineering Data	<a href="#">CAD data – STEP</a>
User Documentation	<a href="#">Manual GigaBit Module</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

**HDC C HS BM0.08-0.12 AU****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Tools****Compact**

The new two-pole bus module is extremely compact and can accommodate both megabit and gigabit data inserts. It enables the connection of 2 Gigabit Cat 6A cables (10 gigabit) to one module.

**General ordering data**

Type	HDC MBUS CT X/D 0.6/1.0	Version
Order No.	<a href="#">2592650000</a>	Crimping tool for contacts
GTIN (EAN)	4050118603774	
Qty.	1 pc(s).	

**Electrical modules****Flexible**

The four module sizes make for individual plug solutions that save a huge amount of space. The smaller pitch translates into an optimised design too.

**General ordering data**

Type	HDC MGBIT 8 FC	Version
Order No.	<a href="#">2748530000</a>	Data module
GTIN (EAN)	4050118890839	
Qty.	1 pc(s).	

Type	HDC MBUS HS 8 F	Version
Order No.	<a href="#">2748640000</a>	Data use
GTIN (EAN)	4050118890686	
Qty.	1 pc(s).	