

IE-C5DHAG-500**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Bulk stock, copper cable, hybrid, flexible, 6 x 0.5 mm² + 4
x AWG 22/7

General ordering data

Version	System cable, Cat.5 (ISO/IEC 11801) / Cat.5e (TIA T568-B), PVC, 500 m
Order No.	2763460000
Type	IE-C5DHAG-500
GTIN (EAN)	4064675030959
Qty.	1 pc(s).

IE-C5DHAG-500

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Length	500 m	Length (inches)	19,685.039 inch
Net weight	31,500 g		

Temperatures

Storage temperature	-40 °C...70 °C	Operating temperature	-30 °C...75 °C
Installation temperature	0 °C...50 °C		

Technical specifications for cable

Halogen	Yes	Insulation	PE
Number of wires	10	Resistance to oils	limited
Resistance to spread of flame	in accordance with IEC 60332-1 / UL 1685	Sheathing colour	green (RAL 6018)
Test voltage: wire-wire-shield	700 V AC		

Cable structure

Arrangement of wire cores	Star-quad	Complete shielding	Aluminium foil, Shielding braid made from copper wiring
Cross-section	4*AWG 22/7 - 0.32 mm ² , 6*0.5 mm ²	Filler	As central element
Insulation	PE	Insulation cross-section	1.6 mm
Insulation diameter 2	1.75 mm	Material sheath	PVC
Number of wires	10	Overlap of shielding braid	85 %
Sheath diameter, max.	9.8 mm	Sheath diameter, min.	9.2 mm
Sheathing colour	green (RAL 6018)	Shielding	SF/UTP
Shielding braid thickness	0.1 mm	Standard designations	2YY(ST)CY 2x2x0.75/1.5-100 LI VZN GN
Strands	7	Tensile force, max.	200 N
Wire material	Stranded tin-plated copper wire		

Electrical properties of cable

Category	Cat.5 (ISO/IEC 11801) / Cat.5e (TIA T568-B)	Characteristic impedance	100 ± 15 Ω at 1–100 MHz
Delay skew	25 ns/100m	Insulation strength	500 MΩ
Loop resistance	120 Ω/km	Operating voltage	125 V
Operating voltage	125 V max.	Operating voltage, UL	600
Shield attenuation	85 db at 100 MHz	Signal propagation time	5.1 ns/m
Test voltage: wire-wire-shield	700 V AC	Transfer impedance	50 mΩ/m at 1 MHz, 50 mΩ/m at 10 MHz, 80 mΩ/m at 30 Mhz

Mechanical and material properties of cable

Abrasion resistance	good	Colour	green (RAL 6018)
Halogen	Yes	Min. bending radius, once only	10 x cable diameter
Resistance to oils	limited	Resistance to spread of flame	in accordance with IEC 60332-1 / UL 1685

IE-C5DHAG-500**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Classifications**

ETIM 6.0	EC000830	ETIM 7.0	EC003249
ETIM 8.0	EC003249	ETIM 9.0	EC003249
ECLASS 9.0	27-06-18-05	ECLASS 9.1	27-06-90-90
ECLASS 10.0	27-06-18-01	ECLASS 11.0	27-06-18-01
ECLASS 12.0	27-06-18-01	ECLASS 13.0	27-06-18-01

Environmental Product Compliance

REACH SVHC /

Approvals

ROHS Conform

DownloadsCatalogues [Catalogues in PDF-format](#)

IE-C5DHAG-500

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Detailed drawing

