

**IE-C5AS4VG-500****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Bulk stock, copper cable, PROFINET, type A, PVC, rigid,  
green

**General ordering data**

Version	Installation cable, PROFINET, Cat.5 (ISO/IEC 11801) / Cat.5e (TIA T568-B), PVC, 500 m
Order No.	<a href="#">2763430000</a>
Type	IE-C5AS4VG-500
GTIN (EAN)	4064675030904
Qty.	1 pc(s).

## IE-C5AS4VG-500

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Length	500 m	Length (inches)	19,685.039 inch
Net weight	33,000 g		

## Temperatures

Storage temperature	-40 °C...80 °C	Operating temperature	-40 °C...80 °C
Installation temperature	-40 °C...80 °C		

## Technical specifications for cable

Core cross-section	0.33 mm <sup>2</sup>	Insulation	PE
Number of poles	4	Number of wires	4
Resistance to oils	limited	Resistance to spread of flame	in accordance with IEC 60332-1 / UL 1685
Sheathing colour	green (RAL 6018)	Test voltage: wire-wire-shield	2000 V <sub>eff</sub> , 50 Hz, 1 min

## Cable specific standards

Standard, additional standards	UL-File E11901 Vol.3 Sec.1 Page 2 Verified Cat. 5e, UL-File E116441 Vol.1 Sec.6 Page 8, UL-File E306668 Vol.1 Sec.3 Page 1	Standard, assembly	UL-Style 21694
Standard, insulating material	DIN EN 50290-2-23 (VDE 0819) Table 2/A (HD 624.3)	Standard, shielding material	DIN EN 13602 Cu-ETP-A..B
Standard, wire material	DIN EN 13602 Cu-ETP-A		

## Standards

Standard, additional standards	UL-File E11901 Vol.3 Sec.1 Page 2 Verified Cat. 5e, UL-File E116441 Vol.1 Sec.6 Page 8, UL-File E306668 Vol.1 Sec.3 Page 1	Standard, assembly	UL-Style 21694
Standard, insulating material	DIN EN 50290-2-23 (VDE 0819) Table 2/A (HD 624.3)	Standard, shielding material	DIN EN 13602 Cu-ETP-A..B
Standard, wire material	DIN EN 13602 Cu-ETP-A		

## IE-C5AS4VG-500

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Cable structure

Arrangement of wire cores	Star-quad	Colour sequence or wires - wire pairs	white, yellow, blue, orange
Complete shielding	Aluminium foil, Shielding braid made from copper wiring	Cross-section	4*AWG 22/1 - 0.33 mm <sup>2</sup>
Diameter of inner sheathing	4.05 mm	Filler	As central element
Insulation	PE	Insulation cross-section	1.5 mm
Material sheath	PVC	Number of wires	4
Overlap of shielding braid	85 %	Sheath diameter, max.	6.7 mm
Sheath diameter, min.	6.3 mm	Sheathing colour	green (RAL 6018)
Sheathing material thickness	0.9 mm	Shielding	SF/UTP
Shielding braid thickness	0.13 mm	Standard designations	2YY(ST)CY 2x2x0,64/1,5-100 GN
Strands	1	Wire core insulation thickness	0.43 mm
Wire material	Non-insulated copper wire		

## Electrical properties of cable

Capacity at 1 kHz	52 nF/km	Category	Cat.5 (ISO/IEC 11801) / Cat.5e (TIA T568-B)
Characteristic impedance	100 ± 5 Ω at 100MHz	Delay skew	40 ns/100m
Loop resistance	115 Ω/km	Operating voltage (UL rating)	600 V
Operating voltage, UL	600 V	Resistance differential	3 %
Signal propagation time	5.3 ns/m	Test voltage: wire-wire-shield	2000 V <sub>eff</sub> , 50 Hz, 1 min
Transfer impedance	10 mΩ/m at 10 MHz		

## Mechanical and material properties of cable

Abrasion resistance	good	Colour	green
Min. bending radius, once only	4 x cable diameter	Min. bending radius, repetitive	8 x cable diameter
Resistance to oils	limited	Resistance to spread of flame	in accordance with IEC 60332-1 / UL 1685
UV-resistant	Complies with UL 1581 Sec. 1200		

## Classifications

ETIM 6.0	EC000830	ETIM 7.0	EC003249
ETIM 8.0	EC003249	ETIM 9.0	EC003249
ECLASS 9.0	27-06-18-05	ECLASS 9.1	27-06-90-90
ECLASS 10.0	27-06-18-01	ECLASS 11.0	27-06-18-01
ECLASS 12.0	27-06-18-01	ECLASS 13.0	27-06-18-01

## Approvals

ROHS	Conform
------	---------

## Downloads

Approval/Certificate/Document of Conformity	<a href="#">PROFINET Manufacturer's Declaration</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

## IE-C5AS4VG-500

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

# Drawings

## Detailed drawing

