

**VPU AC I 1 R 275/25 LCF MB****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Type I/II lightning arrester for use upstream of the electrical meter**

- With 25 kA (10/350  $\mu$ s) suitable for protective zones I, II, III and IV (LPL I/II/III/IV)
- With remote monitoring function, one changeover contact
- Tested according to IEC 61643-11 for type I and II surge protection

**General ordering data**

Version	Surge voltage arrester, Low voltage, Surge protection, Leakage-current-free, with remote contact, Single-phase, TN
Order No.	<a href="#">2774940000</a>
Type	VPU AC I 1 R 275/25 LCF MB
GTIN (EAN)	4064675038863
Qty.	1 pc(s).
Replacement parts	<a href="#">2855300000</a>

Creation date June 3, 2024 6:41:12 AM CEST

Catalogue status 18.05.2024 / We reserve the right to make technical changes.

## VPU AC I 1 R 275/25 LCF MB

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	71 mm	Depth (inches)	2.795 inch
Height	99 mm	Height (inches)	3.898 inch
Width	35 mm	Width (inches)	1.378 inch
Net weight	57 g		

## Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-40 °C...85 °C
Humidity	5 - 95% rel. humidity		

## Connection data, remote alert

Connection type	Screw connection: plug-gable	Cross-section for connected wire, solid core, max.	1.5 mm <sup>2</sup>
Cross-section for connected wire, solid core, min.	0.14 mm <sup>2</sup>	Max. torque	0.25 Nm
Stripping length	8 mm		

## General data

Colour	grey	Design	Installation housing; 2TE, Insta IP 20
Operating altitude	≤ 2000 m	Optical function display	green = OK; red = arrester is defective - replace
Protection degree	IP20 in installed state	Rail	TS 35
Segment	Power distribution	UL 94 flammability rating	V-0
Version	Surge protection, Leakage-current-free, with remote contact		

## Insulation coordination acc. to EN 50178

Pollution severity	2	Surge voltage category	II
--------------------	---	------------------------	----

## Rated data IEC / EN

Discharge current $I_{\max}$ (8/20μs) wire-PE	100 kA	Discharge current $I_n$ (8/20μs) wire-PE	25 kA
Energy coordination (≤10 m)	Type I, Type II, Type III	Follow-on current extinguishing capability $I_{fi}$	Not available due for technical reasons
Frequency range, max.	60 Hz	Frequency range, min.	50 Hz
Fuse	No Fuse necessary ≤250 A gG, 250 A gL (if back up fuse > 250 A)	Leakage current at $U_n$	1 μA
Lightning test current $I_{imp}$ (10/350 μs) (L-PE)	25 kA	Low voltage network	Single-phase, TN
Max. continuous voltage, $U_c$ (AC)	275 V	Number of poles	1
PE conductor current $I_{PE}$	1 μA	Protection level $U_p$ at $I_N$ (L/N-PE)	≤ 1.5 kV
Rated load current $I_L$	100 A	Rated voltage (AC)	230 V
Requirements category acc. to IEC 61643-11	Type I, Type II	Requirements class, acc. to EN 61643-11	T1, T2
Response time	≤ 25 ns	SPD type	T1, T2
Short-circuit current rating $I_{SCCR}$	50 kA	Signalling contact	250 V 1A 1CO
Standards	IEC61643-11, EN61643-11	Temporary surge voltage (over-voltage) - TOV	438 V
Voltage type	AC		

## VPU AC I 1 R 275/25 LCF MB

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Connection data

Stripping length	15 mm	Wire connection method	Clamping yoke
Type of connection	Screw connection	Stripping length, rated connection	15 mm
Tightening torque, min.	2 Nm	Tightening torque, max.	3 Nm
Clamping range, rated connection	16 mm <sup>2</sup>	Clamping range, min.	4 mm <sup>2</sup>
Clamping range, max.	35 mm <sup>2</sup>	Wire cross-section, solid, min.	4 mm <sup>2</sup>
Wire cross-section, solid, max.	35 mm <sup>2</sup>	Wire connection cross section, finely stranded, min.	4 mm <sup>2</sup>
Wire connection cross section, finely stranded, max.	25 mm <sup>2</sup>	Conductor cross-section, flexible, AEH (DIN 46228-1), min.	4 mm <sup>2</sup>
Conductor cross-section, flexible, AEH (DIN 46228-1), max.	35 mm <sup>2</sup>	Connection cross-section, stranded, min.	4 mm <sup>2</sup>
Connection cross-section, stranded, max.	35 mm <sup>2</sup>		

## Guarantee

Time interval	5 years
---------------	---------

## Classifications

ETIM 6.0	EC000941	ETIM 7.0	EC000941
ETIM 8.0	EC000941	ETIM 9.0	EC000941
ECLASS 9.0	27-13-08-05	ECLASS 9.1	27-13-08-05
ECLASS 10.0	27-13-08-05	ECLASS 11.0	27-13-08-05
ECLASS 12.0	27-17-90-90	ECLASS 13.0	27-17-90-90

## Approvals

Approvals



ROHS	Conform
------	---------

## Downloads


Approval/Certificate/Document of Conformity	<a href="#">EU_Konformitätserklärung / EU_Declaration_of_Conformity</a>
Engineering Data	<a href="#">CAD data – STEP</a>
User Documentation	<a href="#">Beipackzettel / Instruction sheet</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

## VPU AC I 1 R 275/25 LCF MB

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings



Principle circuit diagram

## VPU AC I 1 R 275/25 LCF MB

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Replacement parts

### VPU Series



Extensive accessories round off the product range

### General ordering data

Type	PLUG VPU AC
Order No.	<a href="#">2855300000</a>
GTIN (EAN)	4064675533283
Qty.	10 pc(s).

**VPU AC I 1 R 275/25 LCF MB****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Crosshead screwdriver Phillips**

VDE insulated crosshead screwdriver, for Phillips screws, SDIK PH DIN 7438, ISO 8764/2-PH, output to ISO 8764-PH, SoftFinish grip

**General ordering data**

Type	SDIK PH1 X 80	Version
Order No.	<a href="#">2749890000</a>	Screwdriver, Blade width (B): 1 mm, 80 mm, Blade thickness (A): 1
GTIN (EAN)	4050118897098	
Qty.	1 pc(s).	