

IE-SFP-10GE-MM-03**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Features of SFP-Transceiver series**

- Huge variety of transceiver types for several transmission speeds (up to 10 Gigabit Ethernet) and distances (up to 60 km)
- BiDi SFP models for communication via single fiber
- Easy control of transceiver status due to support of Digital Diagnostic Monitoring (DDM)
- Hot pluggable (during operation)
- Class 1 laser product, EN60825-1 compliant
- Applicable for switches of the Eco-, Advanced- and SubstationLine

General ordering data

Version	SFP+ transceiver, 10 Gbps, Multimode, LC-Duplex, 0.3 km, -40 °C...85 °C
Order No.	2779110000
Type	IE-SFP-10GE-MM-03
GTIN (EAN)	4064675048473
Qty.	1 pc(s).

IE-SFP-10GE-MM-03**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Net weight	17.5 g
------------	--------

Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-40 °C...85 °C
---------------------	----------------	-----------------------	----------------

EMC conformity and approvals

EMC standards	EN 55032, EN 55035	Safety standard	UL 62368-1
---------------	--------------------	-----------------	------------

Environmental conditions

Operating temperature, max.	85 °C	Operating temperature, min.	-40 °C
Storage temperature, max.	85 °C	Storage temperature, min.	-40 °C

Fibre optic transceiver characteristics

Transmission rate	10 Gbps
-------------------	---------

Digital diagnostic monitor function (DDM)	Supported
---	-----------

Transceiver type	Multimode
------------------	-----------

Connector type	LC-Duplex
----------------	-----------

Transmission distance, typ.	0.3 km
-----------------------------	--------

Wavelength	typ.	850 nm
	Wavelength	TX
	min.	840 nm
	max.	860 nm
	Wavelength	RX
	min.	840 nm
Receive power	max.	860 nm
	min.	-9.9 dBm
Transmission power	max.	-1 dBm
	min.	-6.5 dBm
Link-budget	max.	-1 dBm
	min.	3.4 dB

Guarantee

Time interval	3 years
---------------	---------

Power supply

Voltage supply	3.3 V (via Ethernet switch)
----------------	-----------------------------

Technical data

Type of mounting	Insert in SFP slot
------------------	--------------------

IE-SFP-10GE-MM-03

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Classifications

ETIM 6.0	EC001121	ETIM 7.0	EC001121
ETIM 8.0	EC003628	ETIM 9.0	EC003628
ECLASS 9.1	27-44-02-92	ECLASS 10.0	27-44-02-92
ECLASS 11.0	19-17-03-03	ECLASS 12.0	19-17-03-03
ECLASS 13.0	19-17-03-03		

Environmental Product Compliance

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E230683

Downloads

Approval/Certificate/Document of Conformity	EU Declaration of Conformity RCM Declaration of Conformity UK Declaration of Conformity
Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format