

IE-FPOB2EG-500**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Bulk stock, FO cable, POF

General ordering data

Version	System cable, 980 µm, Polyethylene
Order No.	2781950000
Type	IE-FPOB2EG-500
GTIN (EAN)	4064675057109
Qty.	1 pc(s).

IE-FPOB2EG-500**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Net weight	24,500 g
------------	----------

Temperatures

Storage temperature	-30 °C...70 °C	Operating temperature	-30 °C...70 °C
---------------------	----------------	-----------------------	----------------

Technical specifications for cable

Bending cycles	10.000	Colour coding	orange, black
Halogen	No	Number of wires	2
Sheathing colour	green		

Fibre-optic

Attenuation	≤ 160 dB/km at 650 nm	Bandwidth	> 35 MHz*100 m at 650 nm
Fibre type	POF	Numerical aperture	0.5

Cable structure

Cable layout	Mini-Breakout	Colour coding	orange, black
Core diameter	980 µm	Diameter of wire pair	2.2 mm
Material sheath	Polyethylene	Number of wires	2
Primary coating	245 µm	Sheath diameter, max.	7.5 mm
Sheathing colour	green	Tensile force, max.	1,000 N

Mechanical and material properties of cable

Bending cycles	10.000	Colour	green
Halogen	No		

Classifications

ETIM 6.0	EC000034	ETIM 7.0	EC000034
ETIM 8.0	EC000034	ETIM 9.0	EC000034
ECLASS 9.0	27-06-18-03	ECLASS 9.1	27-06-90-90
ECLASS 10.0	27-06-18-03	ECLASS 11.0	27-06-18-03
ECLASS 12.0	27-06-18-03	ECLASS 13.0	27-06-18-03

Environmental Product Compliance

REACH SVHC	/
------------	---

Approvals

ROHS	Conform
------	---------

Downloads

Approval/Certificate/Document of Conformity	PROFINET Manufacturer's Declaration
Catalogues	Catalogues in PDF-format

IE-FPOB2EG-500

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Detailed drawing

