

**IE-C5ES8VB0030N40N40-B-K6KV****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Assembled cables with 2x RJ45, suitable for smart metering applications, different colors in accordance with DIN VDE 0603-100. Short plugs and cables with small bending radius for tight spaces, plug housing with circumferential insulation allow protection class IP30 in mated condition.

**General ordering data**

Order No.	<a href="#">2813820030</a>
Type	IE-C5ES8VB0030N40N40-B-K6KV
GTIN (EAN)	4064675668725
Qty.	1 pc(s).

**IE-C5ES8VB0030N40N40-B-K6KV****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Length	3 m	Length (inches)	118.11 inch
Net weight	135 g		

**Temperatures**

Installation temperature	0 °C...50 °C
--------------------------	--------------

**Electrical properties**

Operating voltage	125 V	PoE / PoE+	conforming to IEEE 802.3at
-------------------	-------	------------	----------------------------

**General standards**

Application-specific communication cable facilities	VDE-AR-N 4100:2019-04	Connector standard	IEC 60603-7-51
---	-----------------------	--------------------	----------------

**Standards**

Connector standard	IEC 60603-7-51
--------------------	----------------

**Cable structure**

Cable layout	Double insulation according to VDE 0603-100	Colour coding	white / blue, white / orange, white / green, white / brown
Complete shielding	Shielding braid made from copper wiring, Aluminium foil	Cross-section	4x2xAWG 26/7. 4x2x0.128 mm <sup>2</sup>
Insulation	PE	Insulation cross-section	1 mm
Material sheath	PVC	Number of wires	8
Sheath diameter	5.5 mm	Sheathing colour	blue
Shielding	SF/UTP		

**Electrical properties of cable**

Category	Cat.5 (ISO/IEC 11801) / Cat.5e (TIA T568-B)	Operating voltage	125 V
Rated impulse withstand voltage	6 kV	Signal propagation time	5.1 ns/m

**Mechanical and material properties of cable**

Bending radius	4 x cable diameter	Colour	blue (RAL 5015)
Min. bending radius, once only	5 x cable diameter	Resistance to spread of flame	in accordance with IEC 60332-1-2

**Plug**

Plug left	RJ45, IP30 (plugged), male contact, straight, plug, shielded	Plug right	RJ45, IP30 (plugged), male contact, straight, plug, shielded
-----------	--	------------	--

## IE-C5ES8VB0030N40N40-B-K6KV

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

## Plug, left

Plug left	RJ45, IP30 (plugged), male contact, straight, plug, shielded
-----------	--

## Plug, right

Plug right	RJ45, IP30 (plugged), male contact, straight, plug, shielded
------------	--

## Classifications

ETIM 6.0	EC002599	ETIM 7.0	EC002599
ETIM 8.0	EC002599	ETIM 9.0	EC002599
ECLASS 9.0	27-06-03-08	ECLASS 9.1	27-06-03-08
ECLASS 10.0	27-06-03-08	ECLASS 11.0	27-06-03-08
ECLASS 12.0	27-06-03-08	ECLASS 13.0	27-06-03-08
ECLASS 14.0	27-06-03-08		

## Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	No SVHC above 0.1 wt%

## Approvals

Approvals



ROHS	Conform
------	---------

## Downloads


Engineering Data	<a href="#">CAD data – STEP</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

**IE-C5ES8VB0030N40N40-B-K6KV****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Drawings****Wiring**

RJ45	1	red	1	RJ45
	2	orange	2	
	3	black	3	
	4	blue	4	
	5	white	5	
	6	green	6	
	7	yellow	7	
	8	brown	8	