

WIPL 20W DC RC M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Energy-efficient emergency lighting with a long service life**

- **developed and to be used in accordance with DIN EN 60598-2-22**
- LED lamp for harsh environmental conditions (shocks and vibration, temperature range)
- higher energy efficiency and service life than fluorescent lamps
- Can be used worldwide thanks to the multi-voltage input (21.5 V...60 VDC)
- high fire protection classification V0
- Beam direction to one side
- 20W Power

Versions

- Pluggable with round connector

General ordering data

Order No.	2820600000
Type	WIPL 20W DC RC M
GTIN (EAN)	4064675357087

WIPL 20W DC RC M

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	105 mm	Depth (inches)	4.134 inch
Height	44 mm	Height (inches)	1.732 inch
Width	250 mm	Width (inches)	9.842 inch
Length	250 mm	Length (inches)	9.842 inch
Net weight	649.05 g		

Temperatures

Storage temperature	-40 °C...70 °C	Operating temperature	-40 °C...55 °C
Humidity	5...95 %, no condensation		

General data

Amplitude of acceleration	50 m/s ² (@ 9-200 Hz)	Amplitude of deflection	1.5 mm (2-9 Hz)
Circuit breaker	<10 A	Connector cross-section, max.	2.5 mm ²
Connector cross-section, min.	0.5 mm ²	Efficiency class (according to EU Directive No. 874/2012)	E
Halogen	No	Height	≤ 3000 m
Insulation voltage	<500 V (housing/PE)	LED operating life	> 50.000 h
Light colour (CCT)	5700K	Light current	2,000 lm
Mounting position, installation notice	Arbitrary	Peak acceleration, type L	70 m/s ²
Pollution severity	2	Pre-assembled connector cross-section	2.5 mm ²
Protection class	II	Protection degree	IP67
Rated voltage	24 V	Shape of the LED module	Other
Shock resistance EN 60721-3-3	Class 3M3 portable	Short-circuit protection	Yes, internal
Silicone	No	Surge voltage category	II
Type of connection	Plug-in round connector with fixed number of poles	Type of mounting	Screw mounting
UL 94 flammability rating	V-0	Vibration resistance EN 60721-3-3	Class 3M3 sinusoidal, stationary

Rated data acc. to IEC 60598-1

DC input voltage range	21.5...60 V DC	Input voltage	21.5...60 V DC
Power rating	20 W	Rated current	420 mA

Classifications

ETIM 6.0	EC000996	ETIM 7.0	EC000996
ETIM 8.0	EC000996	ETIM 9.0	EC000996
ECLASS 9.1	27-11-06-35	ECLASS 10.0	27-11-06-35
ECLASS 11.0	27-11-06-35	ECLASS 12.0	27-11-06-35
ECLASS 13.0	27-11-06-35	ECLASS 14.0	27-11-06-35

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1 Potassium perfluorobutane sulfonate 29420-49-3
SCIP	27e86d18-c41d-4565-b758-0d85dd7b9596
RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c, 7a, 7cl

WIPL 20W DC RC M

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

UL File Number Search UL Website

Certificate no. (cULus) E345151

Downloads



Catalogues [Catalogues in PDF-format](#)

WIPL 20W DC RC M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



WIPL 20W DC RC M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****RC-distributor****H-distributor:**

The H distributor is equipped with four poles and impresses with its versatility and IP68 protection class.

General ordering data

Type	RC D 4/4P
Order No.	2819550000
GTIN (EAN)	4064675591290
Qty.	

M20

Protective caps suitable for FieldPower and WIPL family with round connector

**General ordering data**

Type	PC RC F
Order No.	2833850000
GTIN (EAN)	4064675591412
Qty.	

Type	PC RC M
Order No.	2820090000
GTIN (EAN)	4064675591405
Qty.	

WIPL 20W DC RC M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

DC connectors



DC connector:

The circular connectors of the DC family are characterised by their compact design. This allows them to be used in a wide range of applications and industries. They are available both as male and female connectors.

General ordering data

Type	RC M P2 SP
Order No.	2903190000
GTIN (EAN)	4099986122369
Qty.	

Type	RC F P2 SP
Order No.	2903200000
GTIN (EAN)	4099986122376
Qty.	