

**WIL-LWXXXX-5000D024-555SXX3.0BXXXXXXXXXX****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

The WIL-LED lights family: Only 8mm (9.4mm with magnet) high LED lamp for 24V DC with very high luminous efficacy and high Lifespan (greater 60 000h). Very robust construction, by full potting and metal housing - water-proof (IP67). Due to its 5000K light color, neutral white, suitable for the various applications. Very easy to connect thanks to the M12 connection. Due to the low power consumption, a small enough power supply with 24V for operation.

**General ordering data**

|            |                                          |
|------------|------------------------------------------|
| Order No.  | <a href="#">2821120000</a>               |
| Type       | WIL-LWXXXX-5000D024-555SXX3.0BXXXXXXXXXX |
| GTIN (EAN) | 4064675358565                            |
| Qty.       | 1 pc(s).                                 |

WIL-LWXXXX-5000D024-555SXX3.0BXXXXXXXXXX

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

### Dimensions and weights

|            |        |                 |            |
|------------|--------|-----------------|------------|
| Depth      | 40 mm  | Depth (inches)  | 1.575 inch |
| Height     | 8 mm   | Height (inches) | 0.315 inch |
| Width      | 555 mm | Width (inches)  | 21.85 inch |
| Net weight | 226 g  |                 |            |

### Temperatures

|                       |            |
|-----------------------|------------|
| Operating temperature | -20 - 60°C |
|-----------------------|------------|

### Cable technical specifications

|                |     |                  |       |
|----------------|-----|------------------|-------|
| Cable Material | PUR | Sheathing colour | black |
| Cable length   | 3 m |                  |       |

### Connection data

|         |                |                   |                                                               |
|---------|----------------|-------------------|---------------------------------------------------------------|
| Version | Cable end open | Connection thread | without                                                       |
| Coding  |                | Wiring            | Pin 4 (Strand: black) control white LED, Pin 3 (Strand: blue) |
|         | A-coded        |                   |                                                               |

### Electric data

|               |         |               |        |
|---------------|---------|---------------|--------|
| Rated voltage | 24 V DC | Rated current | 0,90 A |
| Power         | 22.0 W  | Dimmable      | Yes    |

### General technical data

|                                       |             |                                                              |                     |
|---------------------------------------|-------------|--------------------------------------------------------------|---------------------|
| Electronic equipment on rolling stock | No          | Recommended class according to UL for use of an power supply | NEC Class 2         |
| Shape of the LED module               | Rectangular | Type of connection                                           | Pre-assembled cable |
| Number of LEDs                        | 105         | Light colour (CCT)                                           | 5000K, White        |
| Luminosity                            | 650 cd      | Light current                                                | 1,874 lm            |
| Emitting angle                        | 40 °        | Illumination level                                           | 650 lux             |
| Operating life                        | 60.000 h    | Type of mounting                                             | Screw mounting      |
| Drill hole spacing                    | 540 mm      | Impact resistance                                            | IK05                |
| Protection degree                     | IP67        | Efficiency class (according to EU Directive No. 874/2012)    | G                   |

### Material data

|                       |                             |                        |        |
|-----------------------|-----------------------------|------------------------|--------|
| Housing main material | hard anodised aluminium     | Encapsulation compound | PUR V0 |
| Material of end caps  | Diecast zinc, nickel-plated |                        |        |

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000996    | ETIM 7.0    | EC000996    |
| ETIM 8.0    | EC000996    | ETIM 9.0    | EC000996    |
| ECLASS 9.1  | 27-11-06-35 | ECLASS 10.0 | 27-11-06-35 |
| ECLASS 11.0 | 27-11-06-35 | ECLASS 12.0 | 27-11-06-35 |
| ECLASS 13.0 | 27-11-06-35 |             |             |

WIL-LWXXXX-5000D024-555SXX3.0BXXXXXXXXXX

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

## Environmental Product Compliance

|                           |                                      |
|---------------------------|--------------------------------------|
| REACH SVHC                | Lead 7439-92-1                       |
| SCIP                      | bf1e8170-69bb-4440-b3e0-4da351a9a3b0 |
| EPREL Registration number | 1321229                              |

## Approvals

Approvals



|                         |            |
|-------------------------|------------|
| ROHS                    | Conform    |
| UL File Number Search   | UL Website |
| Certificate no. (cULus) | E354496    |

## Downloads

|                    |                                          |
|--------------------|------------------------------------------|
| Engineering Data   | <a href="#">CAD data – STEP</a>          |
| User Documentation | <a href="#">Flyer WIL</a>                |
| Catalogues         | <a href="#">Catalogues in PDF-format</a> |


**WIL-LWXXXX-5000D024-555SXX3.0BXXXXXXXXXX**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

### Dimensioned drawing



**WIL-LWXXXX-5000D024-555SXX3.0BXXXXXXXXXX**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

Drawings

