

**VPU ZPA S I 3 R 300/7,5****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

Similar to illustration

Lightning arresters for 40 mm rail systems

- Simple and safe to use and install
- Complete and permanent status control
- Leakage current free surge protection
- Application-specific application classes with 7.5 kA and 12.5 kA discharge current

**General ordering data**

Version	Surge voltage arrester, Low voltage, Leakage-current-free, TN-C
Order No.	<a href="#">2830940000</a>
Type	VPU ZPA S I 3 R 300/7,5
GTIN (EAN)	4064675390145
Qty.	1 pc(s).

## VPU ZPA S I 3 R 300/7,5

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	101.6 mm	Depth (inches)	4 inch
Height	230.6 mm	Height (inches)	9.079 inch
Width	36 mm	Width (inches)	1.417 inch
Net weight	618 g		

## Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-40 °C...85 °C
Humidity	5...95 %, no condensation		

## Connection data, remote alert

Connection type	Screw connection	Cross-section for connected wire, solid core, max.	1.5 mm <sup>2</sup>
Cross-section for connected wire, solid core, min.	0.14 mm <sup>2</sup>	Max. torque	0.4 Nm

## General data

Colour	grey	Design	for 40mm busbars
Operating altitude	≤ 4000 m	Optical function display	green = OK; red = arrester is defective - replace
Protection degree	IP30, in combination with the cover, IP20	Segment	Power distribution
UL 94 flammability rating	V-0	Version	Leakage-current-free
auxiliary contact	No		

## Rated data IEC / EN

Combined pulse U <sub>OC</sub>	6 kV	Discharge current I <sub>max</sub> (8/20μs) wire-PE	40 kA
Discharge current I <sub>n</sub> (8/20μs) wire-PE	20 kA	Energy coordination (≤10 m)	Type I, Type II, Type III
Follow-on current extinguishing capability I <sub>fi</sub>	Follow current need not be taken into account	Fuse	No Fuse necessary ≤160 A gG
Leakage current at U <sub>n</sub>	20 μA	Lightning test current I <sub>imp</sub> (10/350 μs) (L-PE)	7.5 kA
Low voltage network	TN-C	Mains voltage	230 V / 400 V
Max. continuous voltage, U <sub>c</sub> (AC)	300 V	Number of poles	1
Protection level U <sub>p</sub> at I <sub>N</sub> (L/N-PE)	≤ 1.5 kV	Rated voltage (AC)	240 V
Requirements category acc. to IEC 61643-11	Type I, Type II, Type III	Requirements class, acc. to EN 61643-11	T1, T2, T3
Response time	≤ 100 ns	SPD type	T1, T2, T3
Short-circuit current rating I <sub>SCCR</sub>	25 kA	Signalling contact	250 V 1A 1CO
Standards	IEC 61643-11, EN 61643-11	Temporary surge voltage (over-voltage) - TOV	442 V
Voltage type	AC		

## Connection data

Wire connection method	Screw connection	Type of connection	Clamped
Tightening torque, max.	4.5 Nm	Clamping range, rated connection	16 mm <sup>2</sup>
Clamping range, min.	4 mm <sup>2</sup>	Clamping range, max.	35 mm <sup>2</sup>
Conductor cross-section, flexible, AEH (DIN 46228-1), min.	16 mm <sup>2</sup>	Conductor cross-section, flexible, AEH (DIN 46228-1), max.	25 mm <sup>2</sup>
Connection cross-section, stranded, min.	16 mm <sup>2</sup>	Connection cross-section, stranded, max.	35 mm <sup>2</sup>

Creation date August 24, 2024 7:31:24 AM CEST

Catalogue status 17.08.2024 / We reserve the right to make technical changes.

## VPU ZPA S I 3 R 300/7,5

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Guarantee

Time interval	5 years
---------------	---------

## Classifications

ETIM 6.0	EC000941	ETIM 7.0	EC000941
ETIM 8.0	EC000941	ETIM 9.0	EC000941
ECLASS 9.0	27-13-08-05	ECLASS 9.1	27-13-08-05
ECLASS 10.0	27-13-08-05	ECLASS 11.0	27-13-08-05
ECLASS 12.0	27-17-90-90	ECLASS 13.0	27-17-90-90
ECLASS 14.0	27-17-90-90		

## Environmental Product Compliance

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

## Approvals

Approvals



ROHS	Conform
------	---------

## Downloads


Approval/Certificate/Document of Conformity	<a href="#">EU Konformitätserklärung / EU Declaration of Conformity</a>
Engineering Data	<a href="#">CAD data – STEP</a>
User Documentation	<a href="#">Beipackzettel / Instruction sheet</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

**VPU ZPA S I 3 R 300/7,5****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Drawings****Electric symbol**

## VPU ZPA S I 3 R 300/7,5

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

## Slotted screwdriver



VDE insulated slot-head screwdriver, SDI DIN 7437, ISO 2380/2, drive output acc. to DIN 5264, ISO 2380/1. SoftFinish grip

## General ordering data

Type	SDIS 1.0X5.5X125	Version
Order No.	<a href="#">2749850000</a>	Screwdriver, Blade width (B): 5.5 mm, Blade length: 125 mm, Blade
GTIN (EAN)	4050118897050	thickness (A): 1 mm
Qty.	1 pc(s).	

## Crosshead screwdriver Phillips



VDE insulated crosshead screwdriver, for Phillips screws, SDIK PH DIN 7438, ISO 8764/2-PH, output to ISO 8764-PH, SoftFinish grip

## General ordering data

Type	SDIK PH1 X 80	Version
Order No.	<a href="#">2749890000</a>	Screwdriver, Blade width (B): 1 mm, 80 mm, Blade thickness (A): 1
GTIN (EAN)	4050118897098	
Qty.	1 pc(s).	

**VPU ZPA S I 3 R 300/7,5****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Accessories****General ordering data**

Type	V-ZPA FUSE HOLDER
Order No.	<a href="#">2904480000</a>
GTIN (EAN)	4099986010383
Qty.	1 pc(s).
Type	V-ZPA TERMINAL
Order No.	<a href="#">2904470000</a>
GTIN (EAN)	4099986010352
Qty.	1 pc(s).