

**IE-BI-SP0-C****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**SPElink®**

FrontCom® Vario integrates multiple functions in only one single frame. The system is easy to install and you can select from a wide range of data, signal and power modules. In addition to being extremely compact, FrontCom® Vario offers a number of unique product features that will make your project planning and work activities secure, fast and future-proof. Furthermore, the FrontCom® Vario system has an attractive housing design that, by the way, offers highest impact-resistance and fully meets the requirements of IP 65 protection class.

**General ordering data**

Version	Single Pair Ethernet, Coupling, SPE socket acc. to IEC 63171-2, PoDL acc. to IEEE 802.3bu / cg, Number of poles: 2
Order No.	<a href="#">2861260000</a>
Type	IE-BI-SP0-C
GTIN (EAN)	4064675579977
Qty.	10 pc(s).

## IE-BI-SP0-C

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Net weight	6.415 g
------------	---------

## Temperatures

Operating temperature	-40 °C...85 °C
-----------------------	----------------

## General data

Insert type	Insert data SteadyTec	Product type	Single Pair Ethernet, Coupling
Protection degree	IP67 with housing		

## General data

Connection 1	SPE socket acc. to IEC 63171-2	Connection 2	SPE socket acc. to IEC 63171-2
UL 94 flammability rating	V-0	Housing main material	PA 66
Category	T1-B	Contact material	Cu
Contact surface	Gold over nickel	Protection degree	IP67 with housing
Plugging cycles	750		

## Electrical properties

Dielectric strength, contact / contact	≥ 1000 V DC	Dielectric strength, contact / shield	2250 V DC
Insulation strength	≥ 500 MΩ	Operational voltage range	≤ 50 V AC, ≤ 60 V DC
PoE / PoE+	PoDL acc. to IEEE 802.3bu / cg	Rated current	3.5 A at 0°C

## General standards

Connector standard	Network standard	IEEE 802.3cg (10BaseT1), IEEE 802.3bw (100 BaseT1), IEEE 802.3bp (1000 BaseT1)
IEC 63171-2		

## Classifications

ETIM 7.0	EC000313	ETIM 8.0	EC000313
ETIM 9.0	EC000313	ECLASS 10.0	27-44-03-20
ECLASS 11.0	27-44-03-20	ECLASS 12.0	27-44-03-20
ECLASS 13.0	27-44-03-20		

## Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>


## IE-BI-SP0-C

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

### Dimensioned drawing



### Derating curve

Level I gem. IEC 63171

