

**CC-FO 74/101 MM WS****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Standard included: CC**

Our systematically matching product range includes labels for identifying standardised components, as well as all-purpose and familiar formats such as the CC 85/54 marker for nameplates.

**Your benefits with MultiMark**

- "Different materials for various requirements"
- Can be used with equipment from many manufacturers
- Device markers with a familiar design

**General ordering data**

|            |  |
|------------|--|
| Version    | ClipCard, Device markers, 74 x 101 mm, white |
| Order No.  | <a href="#">2885720000</a>                   |
| Type       | CC-FO 74/101 MM WS                           |
| GTIN (EAN) | 4064675854326                                |
| Qty.       | 100 pc(s).                                   |

**CC-FO 74/101 MM WS****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Depth      | 0.55 mm | Depth (inches)  | 0.022 inch |
| Height     | 74 mm   | Height (inches) | 2.913 inch |
| Width      | 101 mm  | Width (inches)  | 3.976 inch |
| Net weight | 0.014 g |                 |            |

**General data**

|                                   |                               |                                   |           |
|-----------------------------------|-------------------------------|-----------------------------------|-----------|
| Adhesive                          | PE-foam with acrylic adhesive | Colour                            | white     |
| Halogen                           | No                            | Material                          | Polyester |
| Operating temperature range, max. | 80 °C                         | Operating temperature range, min. | -30 °C    |
| Printed characters                | neutral                       | UL 94 flammability rating         | V-0       |
| Version                           | Self-adhesive, halogen-free   | Width                             | 101 mm    |

**Device markers**

|         |    |
|---------|----|
| Halogen | No |
|---------|----|

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001288    | ETIM 7.0    | EC001288    |
| ETIM 8.0    | EC001288    | ETIM 9.0    | EC001288    |
| ECLASS 9.0  | 27-40-06-29 | ECLASS 9.1  | 27-40-06-29 |
| ECLASS 10.0 | 27-40-06-29 | ECLASS 11.0 | 27-28-11-04 |
| ECLASS 12.0 | 27-28-11-04 | ECLASS 13.0 | 27-28-11-04 |
| ECLASS 14.0 | 27-28-11-04 |             |             |

**Environmental Product Compliance**

|                        |                             |
|------------------------|-----------------------------|
| REACH SVHC             | /                           |
| RoHS Compliance Status | Compliant without exemption |

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Downloads**

|                  |  |
|------------------|--|
| Engineering Data | <a href="#">CAD data – STEP</a>          |
| Catalogues       | <a href="#">Catalogues in PDF-format</a> |