

MF 5/4.2 MM WS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**MultiMark MultiFit**

For connectors from competitors.

The elastic surface finish makes for simple installation.

This special material enables the strips to be stretched to accommodate slight variations in spacing, especially with long terminal blocks.

A print resolution of 300 dpi also produces a very legible script.

Your benefits with MultiMark

- Firm hold and durable printing
- Continuous strips save installation time
- Easy mounting thanks to an innovative composite material
- Large label field for optimal legibility
- High flexibility thanks to manufacturer independence
- Firm hold and durable printing
- Continuous strips save installation time
- Easy mounting thanks to an innovative composite material
- Large label field for optimal legibility
- High flexibility thanks to manufacturer independence

]

- Easy mounting thanks to an innovative composite material
- Large label field for optimal legibility
- High flexibility thanks to manufacturer independence

General ordering data

Version	Terminal marker, 5 x 4.2 mm, Pitch in mm (P): 4.20 white
Order No.	2885910000
Type	MF 5/4.2 MM WS
GTIN (EAN)	4064675854517
Qty.	1,500 pc(s).

- Firm hold and durable printing
- Continuous strips save installation time

MF 5/4.2 MM WS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	0.7 mm	Depth (inches)	0.028 inch
Height	5 mm	Height (inches)	0.197 inch
Width	4.2 mm	Width (inches)	0.165 inch
Net weight	0.056 g		

Temperatures

Operating temperature range	-50...90 °C
-----------------------------	-------------

General data

Colour	white	Material	PC-ABS, TPU
Operating temperature range	-50...90 °C	Operating temperature range, max.	90 °C
Operating temperature range, min.	-50 °C	Printed characters	neutral
UL 94 flammability rating	V-2	Version	halogen-free
Width	4.2 mm		

Connector markers

Pitch in mm (P)	4.2 mm
-----------------	--------

Classifications

ETIM 6.0	EC000761	ETIM 7.0	EC000761
ETIM 8.0	EC000761	ETIM 9.0	EC000761
ECLASS 9.0	27-14-11-37	ECLASS 9.1	27-14-11-37
ECLASS 10.0	27-14-11-37	ECLASS 11.0	27-28-11-01
ECLASS 12.0	27-28-11-01	ECLASS 13.0	27-28-11-01

Environmental Product Compliance

REACH SVHC	/
------------	---

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format

MF 5/4.2 MM WS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings

