


**VPU AC II+III 2 440/20 S****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**General ordering data**

Version	Surge voltage arrester, Low voltage, TN-S, TN-C, IT with N, IT without N
Order No.	<a href="#">2908440000</a>
Type	VPU AC II+III 2 440/20 S
GTIN (EAN)	4099986190641
Qty.	1 pc(s).

## VPU AC II+III 2 440/20 S

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	70 mm	Depth (inches)	2.756 inch
Height	97 mm	Height (inches)	3.819 inch
Width	18 mm	Width (inches)	0.709 inch
Net weight	162.5 g		

## Temperatures

Operating temperature	-40 °C...85 °C
-----------------------	----------------

## General data

Colour	grey	Design	Installation housing; 1TE, Insta IP 20
Operating altitude	≤ 2000 m	Optical function display	green = OK; red = arrester is defective - replace
Protection degree	IP20 in installed state	Rail	TS 35
Segment	Power distribution	UL 94 flammability rating	V-0

## Insulation coordination acc. to EN 50178

Pollution severity	2	Surge voltage category	III
--------------------	---	------------------------	-----

## Rated data IEC / EN

Combined pulse $U_{OC}$	6 kV	Discharge current (type III)	3 kA
Discharge current $I_{max}$ (8/20μs) wire-PE	20 kA	Discharge current $I_n$ (8/20μs) wire-PE	10 kA
Frequency range, max.	60 Hz	Frequency range, min.	50 Hz
Fuse	No Fuse necessary ≤ 100 A gG	Low voltage network	TN-S, TN-C, IT with N, IT without N
Max. continuous voltage, $U_c$ (AC)	440 V	Number of poles	2
Protection level $U_p$ at $I_N$ (L-PE) (type III)	≤ 1 kV	Protection level $U_p$ at $I_N$ (L/N-PE)	≤ 1.7 kV, ≤ 1.4 kV
Rated voltage (AC)	230 V	Requirements category acc. to IEC 61643-11	Type II, Type III
Requirements class, acc. to EN 61643-11	T2, T3	Response time	≤ 25 ns
Short-circuit current rating $I_{SCCR}$	25 kA	Signalling contact	No
Standards	IEC 61643-11, EN 61643-11	Temporary surge voltage (over-voltage) - TOV	440 V
Voltage type	AC		

## Connection data

Conductor connection cross-section PE, solid, max.	35 mm <sup>2</sup>	Conductor connection cross-section PE, stranded, max.	35 mm <sup>2</sup>
Wire connection method	Screw connection	Type of connection	Screw connection
Stripping length, rated connection	15 mm	Tightening torque, max.	1.2 Nm
Wire cross-section, solid, min.	2.5 mm <sup>2</sup>	Wire cross-section, solid, max.	10 mm <sup>2</sup>
Wire connection cross section, finely stranded, min.	2.5 mm <sup>2</sup>	Wire connection cross section, finely stranded, max.	6 mm <sup>2</sup>
Connection cross-section, stranded, min.	2.5 mm <sup>2</sup>	Connection cross-section, stranded, max.	10 mm <sup>2</sup>

## Guarantee

Time interval	5 years
---------------	---------

Creation date July 5, 2024 2:18:20 AM CEST

## VPU AC II+III 2 440/20 S

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Classifications

ETIM 6.0	EC000941	ETIM 7.0	EC000941
ETIM 8.0	EC000941	ETIM 9.0	EC000941
ECLASS 9.0	27-13-08-05	ECLASS 9.1	27-13-08-05
ECLASS 10.0	27-13-08-05	ECLASS 11.0	27-13-08-05
ECLASS 12.0	27-17-90-90	ECLASS 13.0	27-17-90-90

## Environmental Product Compliance

REACH SVHC

/

## Important note

Product information

For use in DC applications, please use the fuse of SIBA Type NH2XL aR/aSF DC 1500 V

## Approvals

Approvals



ROHS

Conform

## Downloads

Approval/Certificate/Document of Conformity

[EU\\_Konformitätserklärung / EU\\_Declaration\\_of\\_Conformity](#)

Engineering Data

[CAD data – STEP](#)[CAD data – STEP](#)

Tender specification

[Ausschreibungstext DE](#)

User Documentation

[Beipackzettel / Instruction Sheet](#)

Catalogues


[Catalogues in PDF-format](#)

**VPU AC II+III 2 440/20 S****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Drawings****Electric symbol****Schematic circuit diagram**

**VPU AC II+III 2 440/20 S**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Accessories****Crosshead screwdriver Phillips**

VDE insulated crosshead screwdriver, for Phillips screws, SDIK PH DIN 7438, ISO 8764/2-PH, output to ISO 8764-PH, SoftFinish grip

**General ordering data**

Type	SDIK PHO X 60	Version
Order No.	<a href="#">2749880000</a>	Screwdriver, Blade width (B): 0 mm, 60 mm, Blade thickness (A): 0
GTIN (EAN)	4050118897081	
Qty.	1 pc(s).	