

VPU AC II+III 3 275/20 S**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**General ordering data**

Version	Surge voltage arrester, Low voltage, TN-C, U _P (L/N-PE) <1000 V
Order No.	2907870000
Type	VPU AC II+III 3 275/20 S
GTIN (EAN)	4099986189928
Qty.	1 pc(s).

VPU AC II+III 3 275/20 S

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	70 mm	Depth (inches)	2.756 inch
Height	97 mm	Height (inches)	3.819 inch
Width	36 mm	Width (inches)	1.417 inch
Net weight	246 g		

Temperatures

Operating temperature	-40 °C...85 °C
-----------------------	----------------

General data

Colour	grey	Design	Installation housing; 2TE, Insta IP 20
Operating altitude	≤ 2000 m	Optical function display	green = OK; red = arrester is defective - replace
Protection degree	IP20 in installed state	Rail	TS 35
Segment	Power distribution	UL 94 flammability rating	V-0

Insulation coordination acc. to EN 50178

Pollution severity	2	Surge voltage category	III
--------------------	---	------------------------	-----

Rated data IEC / EN

Combined pulse U_{OC}	6 kV	Discharge current (type III)	3 kA
Discharge current I_{max} (8/20μs) wire-PE	20 kA	Discharge current I_n (8/20μs) wire-PE	10 kA
Energy coordination (≤10 m)	Type II, Type III	Frequency range, max.	60 Hz
Frequency range, min.	50 Hz	Fuse	No Fuse necessary ≤100 A gG
Low voltage network	TN-C	Max. continuous voltage, U_c (AC)	275 V
Number of poles	3	Protection level U_p (typ.)	<1000 V
Protection level U_p at I_N (L-PE) (type III)	≤1 kV	Protection level U_p at I_N (L/N-PE)	≤ 1.25 kV
Rated voltage (AC)	230 V	Requirements category acc. to IEC 61643-11	Type II, Type III
Requirements class, acc. to EN 61643-11	T2, T3	Response time	≤ 25 ns
Short-circuit current rating I_{SCCR}	25 kA	Signalling contact	No
Standards	IEC 61643-11, EN 61643-11	Temporary surge voltage (over-voltage) - TOV	335 V
Voltage type	AC		

VPU AC II+III 3 275/20 S

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Connection data

Conductor connection cross-section PE, solid, max.	35 mm ²
Stripping length	15 mm
Type of connection	Screw connection
Tightening torque, min.	1.2 Nm
Clamping range, rated connection	10 mm ²
Clamping range, max.	35 mm ²
Wire cross-section, solid, max.	10 mm ²
Wire connection cross section, finely stranded, max.	6 mm ²
Connection cross-section, stranded, max.	10 mm ²

Conductor connection cross-section PE, stranded, max.	35 mm ²
Wire connection method	Screw connection
Stripping length, rated connection	15 mm
Tightening torque, max.	2 Nm
Clamping range, min.	2.5 mm ²
Wire cross-section, solid, min.	2.5 mm ²
Wire connection cross section, finely stranded, min.	2.5 mm ²
Connection cross-section, stranded, min.	2.5 mm ²

Guarantee

Time interval	5 years
---------------	---------

Classifications

ETIM 6.0	EC000941	ETIM 7.0	EC000941
ETIM 8.0	EC000941	ETIM 9.0	EC000941
ECLASS 9.0	27-13-08-05	ECLASS 9.1	27-13-08-05
ECLASS 10.0	27-13-08-05	ECLASS 11.0	27-13-08-05
ECLASS 12.0	27-17-90-90	ECLASS 13.0	27-17-90-90
ECLASS 14.0	27-17-90-90		

Environmental Product Compliance

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

Important note

Product information	For use in DC applications, please use the fuse of SIBA Type NH2XL aR/aSF DC 1500 V
---------------------	---

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Approval/Certificate/Document of Conformity	EU Konformitätserklärung / EU Declaration of Conformity
Engineering Data	STEP CAD data – STEP
Tender specification	Ausschreibungstext DE
User Documentation	Beipackzettel / Instruction Sheet
Catalogues	Catalogues in PDF-format

Creation date August 29, 2024 5:21:48 PM CEST



Catalogue status 17.08.2024 / We reserve the right to make technical changes.

VPU AC II+III 3 275/20 S**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Drawings****Electric symbol****Schematic circuit diagram**

VPU AC II+III 3 275/20 S

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Spare arrester



General ordering data

Type	VPU AC II+III 0 L-N 275 ...	Version
Order No.	2908010000	Surge voltage arrester, Low voltage, Spare arrester, TN-S, TT, U _p (L/N-PE) <1000 V
GTIN (EAN)	4099986190153	
Qty.	1 pc(s).	
Type	VPU AC II+III 0 L3-PEN ...	Version
Order No.	2907980000	Surge voltage arrester, Low voltage, Spare arrester, TN-S, TT, U _p (L/N-PE) <1000 V
GTIN (EAN)	4099986190139	
Qty.	1 pc(s).	

Crosshead screwdriver Phillips



VDE insulated crosshead screwdriver, for Phillips screws, SDIK PH DIN 7438, ISO 8764/2-PH, output to ISO 8764-PH, SoftFinish grip

General ordering data

Type	SDIK PH0 X 60	Version
Order No.	2749880000	Screwdriver, Blade width (B): 0 mm, 60 mm, Blade thickness (A): 0
GTIN (EAN)	4050118897081	
Qty.	1 pc(s).	