

**PV PS VAPM 5P F****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**General ordering data**

Order No.	<a href="#">2920110000</a>
Type	PV PS VAPM 5P F
GTIN (EAN)	4099986583009
Qty.	1 pc(s).

## PV PS VAPM 5P F

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Net weight	149.5 g
------------	---------

## Temperatures

Continuous operating temp., min.	-40 °C	Continuous operating temp., max.	105 °C
----------------------------------	--------	----------------------------------	--------

## General Data

Colour	black	Conductor cross-section, max.	16 mm <sup>2</sup>
Conductor cross-section, min.	0.2 mm <sup>2</sup>	Insulation strength	≥ 1000 MΩ
Material	Polycarbonate	Number of poles	5
Pollution severity	3	Rated impulse voltage (DIN EN 61984)	6 kV
Type of connection	Screw connection		

## Technical data

Conductor cross-section, max.	16 mm <sup>2</sup>	Conductor cross-section, min.	0.2 mm <sup>2</sup>
Pollution severity	3	Protection degree	IP65, in closed state, IP2x open
Rated current	60 A	Rated voltage	600 V

## Guarantee

Time interval	2 years
---------------	---------

## Classifications

ETIM 6.0	EC002928	ETIM 7.0	EC002928
ETIM 8.0	EC002928	ETIM 9.0	EC002928
ECLASS 9.0	22-57-92-03	ECLASS 9.1	27-44-01-07
ECLASS 10.0	27-44-01-07	ECLASS 11.0	22-57-02-92
ECLASS 12.0	22-57-02-92	ECLASS 13.0	22-57-02-92

## Approvals

Approvals



ROHS	Conform
------	---------

## Downloads

Product Change Notification	<a href="#">Änderung für PV – AC Steckverbinder</a> <a href="#">Change to PV – AC connector</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

### PV PS VAPM 5P F

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

