


**VPU AC I 3 300/12.5 LH****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

Weidmüller VPU I (Type I), VPU II (Type II) and VPU III (Type III) surge protection products effectively reduce the interference coupling that can occur due to transient surge voltages, even significantly below the limits prescribed by insulation co-ordination according to EN 60664-3 / DIN VDE 0110-3. This means that the whole installation is exposed to fewer malfunctions. The arresters are co-ordinated using technical means. This means that decoupling between Types I, II and III is unnecessary. The arresters are tested according to product standard IEC 61643-11 / DIN EN 61643-11 and can be installed in systems according to IEC 61643-12 / VDE 0675-6-12 and IEC 62305-4 / VDE 0185-4. This lightning and surge protection device is suited for installation in power supply systems. Weidmüller offers different products depending on the particular mains network type and voltage level. A special Type I and Type II protective device is even available for photovoltaic applications.

**General ordering data**

Version	Surge protection, TN-C
Order No.	<a href="#">2983570000</a>
Type	VPU AC I 3 300/12.5 LH
GTIN (EAN)	4099986839694
Qty.	1 pc(s).

## VPU AC I 3 300/12.5 LH

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	70 mm	Depth (inches)	2.756 inch
Height	90 mm	Height (inches)	3.543 inch
Width	54 mm	Width (inches)	2.126 inch
Net weight	534 g		

## Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-40 °C...85 °C
Humidity at operating temperature	5 - 95% rel. humidity	Humidity	5 - 95% rel. humidity

## Rated data UL

Ambient temperature (operational), max. 85 °C		MCOV (L-PE)	300 V
I <sub>n</sub>	20 kA	Category	SPD TYPE 4CA
Ambient temperature (operational), min. -40 °C		MODE	L-G
Measured. Limiting Voltage	1,200 V	Voltage type	AC

## Connection data, remote alert

Connection type	PUSH IN	Stripping length	8 mm
-----------------	---------	------------------	------

## General data

Acoustic signal	No	Colour	orange, black
Design	Installation housing; 3TE, Insta IP 20	Operating altitude	≤ 4000 m
Optical function display	green = OK; red = arrester is defective - replace	Protection degree	IP20 in installed state
Rail	TS 35	UL 94 flammability rating	V-0
Version	Surge protection		

## Insulation coordination acc. to EN 50178

Pollution severity	2	Surge voltage category	III
--------------------	---	------------------------	-----

## VPU AC I 3 300/12.5 LH

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Rated data IEC / EN

Acoustic signal	No	Discharge current $I_{\max}$ (8/20 $\mu$ s) wire-PE	50 kA
Discharge current $I_n$ (8/20 $\mu$ s) wire-PE	20 kA	Energy coordination ( $\leq 10$ m)	Type I, Type II, Type III
Follow-on current extinguishing capability $I_{fi}$	Not available due for technical reasons	Frequency range, max.	60 Hz
Frequency range, min.	50 Hz	Fuse	No Fuse necessary $\leq 315$ A gG, 250 A gG @50 kA $I_{sccr}$ , 315 A gG @25 kA $I_{sccr}$
Leakage current at $U_n$	6 $\mu$ A	Lightning test current $I_{imp}$ (10/350 $\mu$ s) (L-PE)	12.5 kA
Lightning test current $I_{imp}$ (10/350 $\mu$ s)	12.5 kA	Low voltage network	TN-C
Mains voltage	230 V / 400 V	Max. continuous voltage, $U_c$ (AC)	300 V
Number of poles	3	Protection level $U_p$ at $I_N$ (L/N-PE)	$\leq 1.5$ kV
Protection level, $U_p$ wire - PE	1,500 V	Protection level, $U_p$ wire - wire	1,500 V
Rated voltage (AC)	230 V	Requirements category acc. to IEC 61643-11	Type I, Type II
Requirements class, acc. to EN 61643-11	T1, T2	Response time	$\leq 25$ ns
Short-circuit current rating $I_{sccr}$	50 kA	Signalling contact	No
Standards	IEC 61643-11, EN 61643-11, UL 1449	Temporary surge voltage (over-voltage) - TOV	337 V
Voltage type	AC		

## Connection data

Stripping length	18 mm	Wire connection method	Screw connection
Tightening torque, min.	3 Nm	Tightening torque, max.	4.5 Nm
Clamping range, rated connection	16 mm <sup>2</sup>	Clamping range, min.	1.5 mm <sup>2</sup>
Clamping range, max.	35 mm <sup>2</sup>	Wire cross-section, solid, min.	1.5 mm <sup>2</sup>
Wire cross-section, solid, max.	35 mm <sup>2</sup>	Wire connection cross section, finely stranded, min.	1.5 mm <sup>2</sup>
Wire connection cross section, finely stranded, max.	25 mm <sup>2</sup>	Connection cross-section, stranded, min.	1.5 mm <sup>2</sup>
Connection cross-section, stranded, max.	35 mm <sup>2</sup>		

## Guarantee

Time interval	5 years
---------------	---------

## Classifications

ETIM 6.0	EC000941	ETIM 7.0	EC000941
ETIM 8.0	EC000941	ETIM 9.0	EC000941
ECLASS 9.0	27-13-08-05	ECLASS 9.1	27-13-08-05
ECLASS 10.0	27-13-08-05	ECLASS 11.0	27-13-08-05
ECLASS 12.0	27-17-90-90	ECLASS 13.0	27-17-90-90
ECLASS 14.0	27-17-90-90		

## Environmental Product Compliance

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

**VPU AC I 3 300/12.5 LH****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Important note**

Product information

For use in DC applications, please use the fuse of SIBA Type NH2XL aR/aSF DC 1500 V

**Approvals**

Approvals



ROHS

Conform

**Downloads**Approval/Certificate/Document of Con-  
formity[DE PA5300 240418 001 ISS 02](#)

Engineering Data

[CAD data – STEP](#)

User Documentation

[Beipackzettel / Instruction sheet](#)

Catalogues


[Catalogues in PDF-format](#)

**VPU AC I 3 300/12.5 LH****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Drawings****Electric symbol**

Schematic circuit diagram

**VPU AC I 3 300/12.5 LH****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Spare arrester**

In the event of a defective arrester, you can easily reorder this spare arrester, replace the defective arrester and thus restore protection.

**General ordering data**

Type	VPU AC I 0 300/12.5 LH	Version
Order No.	<a href="#">2983620000</a>	Surge protection
GTIN (EAN)	4099986839748	
Qty.	1 pc(s).	