

**THM PV 90/140 WFF****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

UV-radiation causes high stress and aging of plastic in the outdoor application.

Our new THM PV labels resist these influences and are extremely durable in outdoor use.

Compact designed packaging are our TABPACK-PV.

These are-printed warning labels, which should be a part of the basic equipment of a professional photovoltaic builder.

Your advantages at a glance:

- Weathering resistance tested according to ISO DIN EN ISO 4892-2:2013 table 3, procedure A cycle 1 at 5000 hours
- Individually labeled with the M-Print® PRO
- Easy and fast printing with the THM MultiMark

**General ordering data**

Version	Device markers, Device markers, 140 x 90 mm, coloured
Order No.	<a href="#">2986850000</a>
Type	THM PV 90/140 WFF
GTIN (EAN)	4099986852921
Qty.	200 pc(s).

**THM PV 90/140 WFF****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Depth	0.1 mm	Depth (inches)	0.004 inch
Height	140 mm	Height (inches)	5.512 inch
Width	90 mm	Width (inches)	3.543 inch
Net weight	500 g		

**General data**

Adhesive	Polyacrylate adhesive	Colour	coloured
Halogen	Yes	Material	Vinyl film
Operating temperature range, max.	110 °C	Operating temperature range, min.	-50 °C
UL 94 flammability rating	V-0	Width	90 mm

**Conductor and cable markers**

Halogen	Yes
---------	-----

**Device markers**

Halogen	Yes
---------	-----

**Classifications**

ETIM 6.0	EC001288	ETIM 7.0	EC001288
ETIM 8.0	EC001288	ETIM 9.0	EC001288
ECLASS 9.0	27-40-06-29	ECLASS 9.1	27-40-06-29
ECLASS 10.0	27-40-06-29	ECLASS 11.0	27-28-11-04
ECLASS 12.0	27-28-11-04	ECLASS 13.0	27-28-11-04

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Engineering Data	<a href="#">CAD data – STEP</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>