

**VPU AC I O 300/12.5 LH****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

In the event of a defective arrester, you can easily reorder this spare arrester, replace the defective arrester and thus restore protection.

**General ordering data**

Version	Surge protection
Order No.	<a href="#">2983620000</a>
Type	VPU AC I O 300/12.5 LH
GTIN (EAN)	4099986839748
Qty.	1 pc(s).

## VPU AC I O 300/12.5 LH

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	70 mm	Depth (inches)	2.756 inch
Height	105.7 mm	Height (inches)	4.161 inch
Width	18 mm	Width (inches)	0.709 inch
Net weight	116.2 g		

## Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-40 °C...85 °C
Humidity at operating temperature	5 - 95% rel. humidity		

## Probability of failure

MTBF	15 a
------	------

## General data

Acoustic signal	No	Colour	orange, black
Design	Installation housing, Insta IP 20	Operating altitude	≤ 4000 m
Optical function display	green = OK; red = arrester is defective - replace	Protection degree	IP20 in installed state
Rail	TS 35	Version	Surge protection

## Rated data IEC / EN

Acoustic signal	No	Discharge current $I_{\max}$ (8/20µs) wire-PE	50 kA
Discharge current $I_n$ (8/20µs) wire-PE	20 kA	Discharge current, $I_{\text{imp}}$ (10/350 µs)	12.5 kA
Discharge current, max. (8/20 µs)	40 kA	Frequency range, max.	60 Hz
Frequency range, min.	50 Hz	Mains voltage	230 V / 400 V
Max. continuous voltage, $U_c$ (AC)	300 V	Protection level $U_p$ at $I_N$ (L/N-PE)	≤ 1500 V
Protection level, $U_p$ wire - PE	1,500 V	Protection level, $U_p$ wire - wire	1,500 V
Rated voltage (AC)	240 V	Requirements category acc. to IEC 61643-11	Type I, Type II
Requirements class, acc. to EN 61643-11	T1, T2	Short-circuit current rating $I_{\text{SCCR}}$	50 kA
Standards	IEC61643-11, EN61643-11	Temporary surge voltage (over-voltage) - TOV	442 V
Voltage type	AC		

## Connection data

Type of connection	Plug-in connection
--------------------	--------------------

## Classifications

ETIM 6.0	EC000941	ETIM 7.0	EC000941
ETIM 8.0	EC000941	ETIM 9.0	EC000941
ECLASS 9.0	27-13-08-05	ECLASS 9.1	27-13-08-05
ECLASS 10.0	27-13-08-05	ECLASS 11.0	27-13-08-05
ECLASS 12.0	27-17-90-90	ECLASS 13.0	27-17-90-90

## VPU AC I O 300/12.5 LH

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Approvals

Approvals



ROHS

Conform

### Downloads

Engineering Data

[CAD data – STEP](#)

User Documentation

[Beipackzettel / Instruction sheet](#)

Catalogues

[Catalogues in PDF-format](#)