

**HDC 06B TOLU 1M20G EXI****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

The option of disconnecting cables in the EXI area simplifies installation and servicing and enables better preparation.

The Rockstar<sup>®</sup> EXI enclosures shown here are identified for use by their article designation.

A blue color is therefore not required. A blue EXI gland is required to complete the enclosure.

**General ordering data**

Version	, Size: 3, Protection degree: IP65 (in plugged condition), Cable entry from side, Plug housing, Side-locking clamp on lower side, Standard, Size of cable entries: M 20
Order No.	<a href="#">3001360000</a>
Type	HDC 06B TOLU 1M20G EXI
GTIN (EAN)	4099986902435
Qty.	1 pc(s).

**HDC 06B TOLU 1M20G EXI****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Height	52 mm	Height (inches)	2.047 inch
Width	43 mm	Width (inches)	1.693 inch
Net weight	124 g		

**Temperatures**

Limit temperature	-40 °C ... 125 °C
-------------------	-------------------

**Dimensions**

Cable entry	w. thread	Height of housing B	52 mm
Total length housing	60 mm	Width housing C	43 mm

**General data**

EMC housings	No	Housing main material	diecast aluminium
Material of locking element		Protection degree	IP65 (in plugged condition)
Surface finish	Stainless steel, rust-proof	Tightening torque	1.2 Nm
Explosion protection type	Powder coating		
	II 2G Ex ib IIC T6 Gb		

**Version**

BG	3	Cable entry	w. thread
Clamp version	End-locking clamp	Colour (RAL)	RAL 7035
Design		Design of housing	Cable entry from side, Plug housing
	Standard		
Design of locking system	Side-locking clamp on lower side	Internal thread	M 20
Number of cable entry on top	1	Size	3
Size of cable entries	M 20	Suitable for ModuPlug®	No
Tightening torque	1.2 Nm	Top part/bottom part/lid	upper part
Type	Plug		

**Classifications**

ETIM 6.0	EC000437	ETIM 7.0	EC000437
ETIM 8.0	EC000437	ETIM 9.0	EC000437
ECLASS 9.0	27-44-02-02	ECLASS 9.1	27-44-02-02
ECLASS 10.0	27-44-02-02	ECLASS 11.0	27-44-02-02
ECLASS 12.0	27-44-02-02	ECLASS 13.0	27-44-02-02

**Downloads**

Catalogues	<a href="#">Catalogues in PDF-format</a>
------------	--

## HDC 06B TOLU 1M20G EXI

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Chloroprene seal material, -40°C - +70°C



Polyamide cable glands, which are suitable for usage in explosion risk zones Ex e (increased safety) and Ex i (intrinsic safety).

Weidmüller offers a product family without restrictions and besides compliance with standards, the cable gland excels thanks to its increased impact resistance of 4/7 Joule and a possible temperature range down to -60°C without restrictions. They have been tested to the current standard and EN 60079-0 directive, they are ATEX and IECEx certified.

## General ordering data

Type	VG M20 EXI 11-14 CR7J G4	Version
Order No.	<a href="#">2722260000</a>	VG Exi 7J (Ex plastic cable gland 7J Exi), Cable glands, straight, M 20,
GTIN (EAN)	4050118821499	10 mm, OD min. 11 - OD max. 14 mm, IP54, IP66, IP67, IP68 - 5 bar
Qty.	50 pc(s).	(30 min.), Polyamide 6
Type	VG M20 EXI 7-13 CR7J G4	Version
Order No.	<a href="#">2722250000</a>	VG Exi 7J (Ex plastic cable gland 7J Exi), Cable glands, straight, M 20,
GTIN (EAN)	4050118821482	10 mm, OD min. 7 - OD max. 13 mm, IP54, IP66, IP67, IP68 - 5 bar
Qty.	50 pc(s).	(30 min.), Polyamide 6
Type	VG M20 EXI 7-12 CR7J G4	Version
Order No.	<a href="#">2722240000</a>	VG Exi 7J (Ex plastic cable gland 7J Exi), Cable glands, straight, M 20,
GTIN (EAN)	4050118821475	10 mm, OD min. 7 - OD max. 12 mm, IP54, IP66, IP67, IP68 - 5 bar
Qty.	50 pc(s).	(30 min.), Polyamide 6