

**VPU AC I F 0 N-PE 275/25****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Abb. ähnlich

Weidmüller VPU I (Type I), VPU II (Type II) and VPU III (Type III) surge protection products effectively reduce the interference coupling that can occur due to transient surge voltages, even significantly below the limits prescribed by insulation co-ordination according to EN 60664-3 / DIN VDE 0110-3. This means that the whole installation is exposed to fewer malfunctions. The arresters are co-ordinated using technical means. This means that decoupling between Types I, II and III is unnecessary. The arresters are tested according to product standard IEC 61643-11 / DIN EN 61643-11 and can be installed in systems according to IEC 61643-12 / VDE 0675-6-12 and IEC 62305-4 / VDE 0185-4. This lightning and surge protection device is suited for installation in power supply systems. Weidmüller offers different products depending on the particular mains network type and voltage level. The VPU AC I F series is characterised by a fuse integrated in the arrester. These arresters do not require a fuse.

**General ordering data**

Version	Surge protection
Order No.	<a href="#">3022930000</a>
Type	VPU AC I F 0 N-PE 275/25
GTIN (EAN)	4099986942226
Qty.	1 pc(s).

## VPU AC I F 0 N-PE 275/25

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	73 mm	Depth (inches)	2.874 inch
Height	45 mm	Height (inches)	1.772 inch
Width	36 mm	Width (inches)	1.417 inch
Net weight	95 g		

## Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-40 °C...85 °C
Humidity	5 - 95% rel. humidity		

## General data

Colour	orange	Design	Insta IP 20
Operating altitude	≤ 2000 m	Optical function display	green = OK; red = arrester is defective - replace
Protection degree	IP20 in installed state	Rail	TS 35
UL 94 flammability rating	V-0	Version	Surge protection

## Insulation coordination acc. to EN 50178

Pollution severity	2	Surge voltage category	III
--------------------	---	------------------------	-----

## Rated data IEC / EN

Discharge current $I_{\max}$ (8/20μs) wire-PE	65 kA	Discharge current $I_n$ (8/20μs) N-PE	100 kA
Discharge current $I_n$ (8/20μs) wire-PE	25 kA	Discharge current, max. (8/20 μs)	130 kA
Energy coordination (≤10 m)	Type III, Type I, Type II	Follow-on current extinguishing capability $I_{fi}$	Not available due for technical reasons
Frequency range, max.	60 Hz	Frequency range, min.	50 Hz
Fuse	Not required	Lightning test current $I_{imp}$ (10/350 μs)	12.5 kA
Mains voltage	230 V / 400 V	Max. continuous voltage, $U_c$ (AC)	305 V
Protection level $U_p$ at $I_N$ (L/N-PE)	≤ 2.1 kV	Rated voltage (AC)	230 V
Requirements category acc. to IEC 61643-11	Type II, Type I	Requirements class, acc. to EN 61643-11	T1, T2, T3
Response time	<100 ns	Short-circuit current rating $I_{SCCR}$	100 kA
Standards	IEC61643-11, EN61643-11	Temporary surge voltage (over-voltage) - TOV	442 V
Voltage type	AC		

## Connection data

Tightening torque, min.	2 Nm	Wire cross-section, solid, min.	1.5 mm <sup>2</sup>
Wire connection cross section, finely stranded, min.	1.5 mm <sup>2</sup>		

## Guarantee

Time interval	5 years
---------------	---------

**VPU AC I F 0 N-PE 275/25****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Classifications**

ETIM 6.0	EC000941	ETIM 7.0	EC000941
ETIM 8.0	EC000941	ETIM 9.0	EC000941
ECLASS 9.0	27-13-08-05	ECLASS 9.1	27-13-08-05
ECLASS 10.0	27-13-08-05	ECLASS 11.0	27-13-08-05
ECLASS 12.0	27-17-90-90	ECLASS 13.0	27-17-90-90

**Downloads**Catalogues [Catalogues in PDF-format](#)