

**VPU AC I 1 N-PE 305/50 LH****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Picture similar

Weidmüller VPU I (Type I), VPU II (Type II) and VPU III (Type III) surge protection products effectively reduce the interference coupling that can occur due to transient surge voltages, even significantly below the limits prescribed by insulation co-ordination according to EN 60664-3 / DIN VDE 0110-3. This means that the whole installation is exposed to fewer malfunctions. The arresters are co-ordinated using technical means. This means that decoupling between Types I, II and III is unnecessary. The arresters are tested according to product standard IEC 61643-11 / DIN EN 61643-11 and can be installed in systems according to IEC 61643-12 / VDE 0675-6-12 and IEC 62305-4 / VDE 0185-4. This lightning and surge protection device is suited for installation in power supply systems. Weidmüller offers different products depending on the particular mains network type and voltage level. A special Type I and Type II protective device is even available for photovoltaic applications.

**General ordering data**

Version	Surge protection, TN-S, TT nur für N-PE, Single-phase
Order No.	<a href="#">3037010000</a>
Type	VPU AC I 1 N-PE 305/50 LH
GTIN (EAN)	4099986998919

## VPU AC I 1 N-PE 305/50 LH

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	70 mm	Depth (inches)	2.756 inch
Height	105.7 mm	Height (inches)	4.161 inch
Width	18 mm	Width (inches)	0.709 inch
Net weight	0 g		

## Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-40 °C...85 °C
Humidity at operating temperature	5 - 95% rel. humidity		

## Probability of failure

MTBF	15 a
------	------

## General data

Acoustic signal	No	Colour	black, orange, blue
Design	Insta IP 20, Installation housing, Installation housing; 1TE	Operating altitude	≤ 4000 m
Optical function display	green = OK; red = arrester is defective - replace	Protection degree	IP20 in installed state
Rail	TS 35	UL 94 flammability rating	V-0
Version	Surge protection		

## Insulation coordination acc. to EN 50178

Pollution severity	2	Surge voltage category	IV
--------------------	---	------------------------	----

## Rated data IEC / EN

Acoustic signal	No	Discharge current $I_{\max}$ (8/20μs) N-PE	100 kA
Discharge current $I_n$ (8/20μs) N-PE	50 kA	Energy coordination (≤10 m)	Type I, Type II, Type III
Follow-on current extinguishing capability $I_{fi}$	Not available due for technical reasons	Frequency range, max.	60 Hz
Frequency range, min.	50 Hz	Fuse	Not required
Leakage current at $U_n$	1 μA	Lightning test current, $I_{imp}$ (10/350 μs) (N-PE)	100 kA
Low voltage network	TN-S, TT nur für N-PE, Single-phase	Mains voltage	230 V / 400 V
Max. continuous voltage, $U_c$ (AC)	300 V	Number of poles	1
Protection level $U_p$ at $I_N$ (N-PE)	≤ 1500 V	Protection level, $U_p$ wire - PE	1,500 V
Protection level, $U_p$ wire - wire	1,500 V	Rated load current $I_L$	100 A
Rated voltage (AC)	240 V	Requirements category acc. to IEC 61643-11	Type II, Type I
Requirements class, acc. to EN 61643-11	T1, T2	Response time	≤ 100 ns
Short-circuit current rating $I_{SCCR}$	50 kA	Signalling contact	No
Standards	IEC61643-11, EN61643-11	Temporary surge voltage (over-voltage) - TOV	442 V
Voltage type	AC		

**VPU AC I 1 N-PE 305/50 LH****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Connection data**

Stripping length	15 mm	Wire connection method	Screw connection
Type of connection	Screw connection	Stripping length, rated connection	15 mm
Tightening torque, min.	2 Nm	Tightening torque, max.	4.5 Nm
Clamping range, rated connection	16 mm <sup>2</sup>	Clamping range, min.	4 mm <sup>2</sup>
Clamping range, max.	35 mm <sup>2</sup>	Wire cross-section, solid, min.	1.5 mm <sup>2</sup>
Wire cross-section, solid, max.	35 mm <sup>2</sup>	Wire connection cross section, finely stranded, max.	35 mm <sup>2</sup>
Conductor cross-section, flexible, AEH (DIN 46228-1), min.	2.5 mm <sup>2</sup>	Conductor cross-section, flexible, AEH (DIN 46228-1), max.	35 mm <sup>2</sup>
Connection cross-section, stranded, max.	35 mm <sup>2</sup>		

**Guarantee**

Time interval	5 years
---------------	---------

**Classifications**

ETIM 6.0	EC000941	ETIM 7.0	EC000941
ETIM 8.0	EC000941	ETIM 9.0	EC000941
ECLASS 9.0	27-13-08-05	ECLASS 9.1	27-13-08-05
ECLASS 10.0	27-13-08-05	ECLASS 11.0	27-13-08-05
ECLASS 12.0	27-17-90-90	ECLASS 13.0	27-17-90-90

**Important note**

Product information	For use in DC applications, please use the fuse of SIBA Type NH2XL aR/aSF DC 1500 V
---------------------	---

**Approvals**

Approvals

**Downloads**

Engineering Data	<a href="#">CAD data – STEP</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

**VPU AC I 1 N-PE 305/50 LH****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Spare arrester**

In the event of a defective arrester, you can easily reorder this spare arrester, replace the defective arrester and thus restore protection.

**General ordering data**

Type	VPU AC I 0 N-PE 305/50 ...	Version
Order No.	<a href="#">2983630000</a>	Surge protection
GTIN (EAN)	4099986839755	
Qty.	1 pc(s).	