

ACT20P-VMR-1PH-H-P**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**ACT20P: The flexible solution**

- Precise and highly functional signal converters
- Release levers simplify handling

General ordering data

Version	Limit value monitoring, Input : 110 / 240 / 400 V AC/DC, Output : 2 x relays, Input: single-phase voltage, Relay output
Order No.	7760054359
Type	ACT20P-VMR-1PH-H-P
GTIN (EAN)	4050118559736
Qty.	1 pc(s).

ACT20P-VMR-1PH-H-P

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	114.3 mm	Depth (inches)	4.5 inch
Height	117 mm	Height (inches)	4.606 inch
Width	22.5 mm	Width (inches)	0.886 inch
Net weight	140 g		

Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-20 °C...65 °C
Humidity at operating temperature	0...95 % (no condensation)	Humidity	5...85 % rel. humidity, no condensation

Probability of failure

SIL in compliance with IEC 61508	None
----------------------------------	------

Input

Input resistance, voltage		Input voltage	Channel 1: (U1-E): 110V AC/DC, Channel 2: (U2-E): 240V AC/DC, Channel 3 1: (U3-E): 400V AC/DC
	1 MΩ±5%		
Number of inputs	1		

Output

Number of outputs	2
-------------------	---

Output (digital)

Alarm function	Top and bottom limit values, window range, Holding function can be activated, Alarm delay: 0...10 s	Hysteresis	5% of final value
Max. switching frequency	20 Hz	Max. switching voltage, AC	250 V
Max. switching voltage, DC	30 V	Number of digital outputs	2
Rated switching current	5 A	Switch-on delay	0...10 s, configurable
Switching thresholds	Adjustable, MIN = 50...100 % x U _{Rated input voltage} (undervoltage alarm), MAX = 70...120 % x U _{Rated input voltage} (overvoltage alarm)	Type	2 x 1 - or 1 x 2 changeover contact relay, Relay polarity can be inverted

General data

Accuracy	3 % *U _{rated voltage}	Configuration	DIP switch and potentiometer
Galvanic isolation	3-way isolator, between input/output/supply, yes	Long-term drift	0.1 % / 10.000 h
Power consumption	≤ 100 mA @ 24 VDC, ≤ 120mA @ 24V AC, <2 W	Protection degree	IP20
Rail	TS 35	Repeat accuracy	2 % *U _{rated voltage}
Step response time	<220 ms (10...90 %)	Temperature coefficient	350 ppm/K
Voltage supply	24...240 VUC ±10%		

ACT20P-VMR-1PH-H-P

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Insulation coordination

EMC standards	EN 61326-1	Galvanic isolation	3-way isolator, between input/output/supply, yes
Impulse withstand voltage	Supply/output: 4 kV; input/output, input/output: 6 kV, 1.2/50 µs	Insulation voltage	2.5 kV (input / output), 2 kV input / output/ power supply
Pollution severity	2	Rated voltage	300 VAC (output 1 - output 2), 300 VAC (supply-output), 500 VAC (supply-input; input-output)
Surge voltage category	III		

Connection data

Type of connection	PUSH IN, Screw connection	Tightening torque, min.	0.4 Nm
Tightening torque, max.	0.6 Nm	Clamping range, rated connection	2.5 mm ²
Clamping range, min.	0.5 mm ²	Clamping range, max.	2.5 mm ²
Wire connection cross section AWG, min.	AWG 26	Wire connection cross section AWG, max.	AWG 14

Classifications

ETIM 6.0	EC002654	ETIM 7.0	EC002654
ETIM 8.0	EC002654	ETIM 9.0	EC002654
ECLASS 9.0	27-21-01-22	ECLASS 9.1	27-21-01-22
ECLASS 10.0	27-21-01-22	ECLASS 11.0	27-21-01-22
ECLASS 12.0	27-21-01-22	ECLASS 13.0	27-21-01-22

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	2f6dd957-421a-46db-a0c2-cf1609156924

Important note

Product information	<p>The ACT20P-VMR-1PH-H is a monitoring relay for DC voltage or single-phase AC voltage. The device has two independent relay outputs which emit an alarm when levels exceed or fall below preset voltage limits. The alarm can also be set to trigger after an adjustable time delay.</p> <p>Features</p> <ul style="list-style-type: none"> • Manual front-sided configuration via DIP switch, potentiometer and rotary switch • Various alarm functions: upper/lower limit value alarm, window alarm • Adjustable start and alarm delay • Front LEDs indicates operation status and malfunction[• 4-way galvanic isolation between input, output 1, output 2 and power supplyswitch
---------------------	--

Approvals

Approvals	
ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E469563

ACT20P-VMR-1PH-H-P

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Downloads

Approval/Certificate/Document of Con-
formity

[Application notes – Declaration of Conformity](#)

Engineering Data

[CAD data – STEP](#)

Software

[DIP switch configuration tool](#)

User Documentation

[Instruction sheet](#)

Catalogues

[Catalogues in PDF-format](#)


ACT20P-VMR-1PH-H-P

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany


www.weidmueller.com

Drawings


Connection diagram




Dimensioned drawing





Overvoltage alarm (O)



Undervoltage alarm (U)



Window alarm (W)



example for DIP switch setting (with ACT20 tool)

ACT20P-VMR-1PH-H-P**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Blank**

ESG is the tried-and-tested marker in MultiCard format for use on many well-known electrical devices. The result is high-quality device marking with a high-contrast appearance.

Various types are available for devices from manufacturers like Siemens, ABB, Beckhoff etc.

Advantages at a glance:

- Tags for universal usage, self-adhesive or clip-on tags, depending on type
- For aligned equipment, e.g. circuit breakers, we supply ESG markers for clipping onto tag rails
- Individual laser-quality printing according to specifications

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Type	ESG 6.6/20 BHZ 5.00/04	Version
Order No.	1082540000	ESG, Device markers x 20 mm, PA 66, Colour: white
GTIN (EAN)	4032248845439	
Qty.	200 pc(s).	

ACT20P-VMR-1PH-H-P**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Blank**

ESG is the tried-and-tested marker in MultiCard format for use on many well-known electrical devices. The result is high-quality device marking with a high-contrast appearance.

Various types are available for devices from manufacturers like Siemens, ABB, Beckhoff etc.

Advantages at a glance:

- Tags for universal usage, self-adhesive or clip-on tags, depending on type
- For aligned equipment, e.g. circuit breakers, we supply ESG markers for clipping onto tag rails
- Individual laser-quality printing according to specifications

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Type	ESG 8/13.5/43.3 SAI AU	Version
Order No.	1912130000	ESG, Device markers x 13.5 mm, PA 66, Colour: Transparent
GTIN (EAN)	4032248541164	
Qty.	5 pc(s).	

ACT20P-VMR-1PH-H-P

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

