

**PAC-QTUM-HE20-V2-2M5****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Similar to illustration

The pre-assembled PAC cables establish an electrical and logical connection between the PLC and the PLC interfaces. These cables consist of the following components:

- Manufacturer's PLC connector.
- Multi-pole LIYY or LY YCY cable (shielded) with a cross-section of 0.14 mm<sup>2</sup> or 0.25 mm<sup>2</sup>.
- Flat cable connector, SUB-D or RSV, for connection to the interface.

The cables are tested automatically for their continuity and insulation to guarantee the functionality for which they have been designed.

**General ordering data**

|            |  |
|------------|--|
| Version    | Pre-assembled cable, PAC, Cable LiYY, 0.25 mm <sup>2</sup> |
| Order No.  | <a href="#">7789121025</a>                                 |
| Type       | PAC-QTUM-HE20-V2-2M5                                       |
| GTIN (EAN) | 8430243961615  |
| Qty.       | 1 pc(s).   |

## PAC-QTUM-HE20-V2-2M5

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |       |
|------------|-------|
| Net weight | 920 g |
|------------|-------|

## Temperatures

|                     |             |                       |          |
|---------------------|-------------|-----------------------|----------|
| Storage temperature | -10...60 °C | Operating temperature | -10...50 |
|---------------------|-------------|-----------------------|----------|

## General Data

|                    |                              |                       |                                     |
|--------------------|------------------------------|-----------------------|-------------------------------------|
| Cable              | Cable LiYY                   | Cable length          | 2.5                                 |
| Connector PLC side | SCHNEIDER<br>140XTS00200 40P | Interface connector   | 2X FLAT CABLE CONN-<br>TOR HE10 20P |
| Material           | PVC                          | Number of poles, min. | 20-pole                             |
| Outer diameter     | 8.6 ± 1 mm                   | Suitable for          | Digital signals                     |
| Wire cross-section | 0.25 mm <sup>2</sup>         |                       |                                     |

## Electrical Data

|                        |                   |  |           |
|------------------------|-------------------|--|-----------|
| Capacity wire / shield | 300 pF/m          | Capacity wire / wires                          | 300 pF/m  |
| High voltage test      | 1 KV/1s           | Permissible current strength per path,<br>max. | 1 A       |
| Rated voltage          | ≤ 60 Vdc ≤ 25 Vac | Resistance                                     | ≤ 80 mΩ/m |
| Total current, max.    | 3 A               |  |           |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000237    | ETIM 7.0    | EC000237    |
| ETIM 8.0    | EC000237    | ETIM 9.0    | EC000237    |
| ECLASS 9.0  | 27-24-22-20 | ECLASS 9.1  | 27-24-22-20 |
| ECLASS 10.0 | 27-24-22-20 | ECLASS 11.0 | 27-24-22-20 |
| ECLASS 12.0 | 27-24-22-20 | ECLASS 13.0 | 27-24-22-20 |

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

## Downloads

|            |  |
|------------|--|
| Catalogues | <a href="#">Catalogues in PDF-format</a> |
|------------|--|