

PORTACAL 275 CALIBRATOR**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Do not use product for new developments, Only remaining stock available



The Portacal 1000 and P275 calibration devices can be used to calibrate and set the analogue signal converters. They provide clean smoothed, analogue standard signals and make use of a load indicator for quick loop diagnostics. As a hand-held signal source, they are optionally available as conventionally controlled (Portacal 275) and microprocessor-controlled (Portacal 1000) versions. A variety of operating modes – such as voltage source, mV source, current source, current sink and adjustable continuous level and ramping functions (Portacal 1000) – makes them suitable for use during the installation and maintenance of processing plants.

General ordering data

Version	OMNIMATE Signal - series PM, Calibration device
Order No.	7940010202
Type	PORTACAL 275 CALIBRATOR
GTIN (EAN)	4032248565801
Qty.	1 pc(s).
Available until	2022-04-15

PORTACAL 275 CALIBRATOR

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Height	112 mm	Height (inches)	4.409 inch
Width	62 mm	Width (inches)	2.441 inch
Length	31 mm	Length (inches)	1.22 inch
Net weight	423 g		

Temperatures

Storage temperature	-25 °C...70 °C	Operating temperature	0 °C...60 °C
---------------------	----------------	-----------------------	--------------

Analogue output

Residual ripple (analogue output)	< 1 µA
-----------------------------------	--------

Functions

Accuracy	0.25 % of signal range	Temperature coefficient	typ. 40 ppm @ °C
----------	------------------------	-------------------------	------------------

General data

Accuracy	0.25 % of signal range	Protection degree	IP20
Temperature coefficient	typ. 40 ppm @ °C	Type of connection	Socket connector
Voltage supply	Batteries, 2 x 9-V blocks 6...22 mA (current source) 2 mA (current sink)		

Output

Residual ripple (analogue output)	< 1 µA
-----------------------------------	--------

Output current mode

Accuracy (current mode output)	< 0.1% (0% and 100%)	Load resistance, max. (current mode out-700 Ω (current source) put) (V _{out} - 4) / 0.02 Ω (current sink)	
Output current (current mode output)	0 (4)...20 mA	Output voltage, max. @ current sink (out-put of current mode)	4...45 V DC
Residual ripple (current mode output)	< 1 µA	Resolution (current mode output)	0.01 mA

Settings

Output, fixed	0 or 100 % with toggle switch	Output, variable	0... 100 % with precision potentiometer
Range of adjustment	0 (4)...20 mA / 0...200 mA (current source).0 ...5 V (voltage source) or as current sink selectable with toggle switch		

Connection data

Type of connection	Socket connector	Clamping range, rated connection	1.5 mm ²
Clamping range, min.	0.5 mm ²	Clamping range, max.	2.5 mm ²

PORTACAL 275 CALIBRATOR

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Classifications

ETIM 6.0	EC002744	ETIM 7.0	EC002744
ETIM 8.0	EC002744	ETIM 9.0	EC002744
ECLASS 9.0	21-17-08-90	ECLASS 9.1	27-21-92-90
ECLASS 10.0	21-17-08-90	ECLASS 11.0	25-14-17-02
ECLASS 12.0	25-14-17-02	ECLASS 13.0	25-14-17-02

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
RoHS Compliance Status	Compliant

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E256486

Downloads

Approval/Certificate/Document of Conformity	Application notes – Declaration of Conformity
User Documentation	Device description – Manual
Catalogues	Catalogues in PDF-format
Brochures	