

FPL 4G2.5C/Q8MW/3**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Take advantage of our pre-assembled FieldPower® connectors with HQ connectors acc. to IEC 23570 (DESINA) for connecting decentralised motor controller devices quickly and conveniently.

General ordering data

Version	FieldPower®, Cable, Metal housing, Number of wires: 4, Ölflex Classic 110 CY 4G2.5 or similar, Cross-section: 2.5 mm ² , 3 m
Order No.	8000011748
Type	FPL 4G2.5C/Q8MW/3
GTIN (EAN)	4050118190427
Qty.	1 pc(s).

Creation date May 23, 2024 6:49:56 AM CEST

Catalogue status 18.05.2024 / We reserve the right to make technical changes.

FPL 4G2.5C/Q8MW/3**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Net weight	915 g
------------	-------

Technical specifications for cable

Number of poles	8	Number of wires	4
-----------------	---	-----------------	---

General technical data

Contact surface	Ag (silver)	Housing main material	Zinc diecast
Protection degree	IP65	Rated current	16 A
Rated voltage	500 V		

Classifications

ETIM 6.0	EC001578	ETIM 7.0	EC003250
ETIM 8.0	EC003250	ETIM 9.0	EC003250
ECLASS 9.0	27-06-20-11	ECLASS 9.1	27-06-90-90
ECLASS 10.0	27-06-01-06	ECLASS 11.0	27-06-01-06
ECLASS 12.0	27-06-01-06	ECLASS 13.0	27-06-01-06

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1 Potassium perfluorobutane sulfonate 29420-49-3 6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol 119-47-1
SCIP	edb4769d-47d5-4f66-921a-c1f4685d793c

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	------------------------------------------

FPL 4G2.5C/Q8MW/3

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Pin assignments

	Pin	Conductor	Assignment
8 = nc	1	1	U
	2	-	-
5 = nc	3	3	W
	4	-	-
⊕ = PE	5	-	-
	6	-	-
3 = W	7	2	V
	8	-	-
2 = nc	PE	gr./yell.	PE