


MSTTAB2019ORANGE_ATTB**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Current and voltage transformer wiring**

Our test disconnect terminal blocks featuring spring and screw connection technology allow you to create all the important converter circuits for measuring current, voltage and power in a safe and sophisticated way.

General ordering data

Version	Test-disconnect terminal, PUSH IN, beige, 6 mm ² , 30 A, Number of connections: 40, Number of levels: 1, TS 35, V-0, Wemid
Order No.	8000080745
Type	MSTTAB2019ORANGE_ATTB
GTIN (EAN)	4064675417330
Qty.	1 pc(s).

MSTTAB2019ORANGE_ATTB

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	79 mm	Depth (inches)	3.11 inch
Height	100 mm	Height (inches)	3.937 inch
Width	203 mm	Width (inches)	7.992 inch
Net weight	1,939 g		

Temperatures

Continuous operating temp., min.	-60 °C	Continuous operating temp., max.	130 °C
----------------------------------	--------	----------------------------------	--------

Material data

Material	Wemid	Colour	beige
Colour of operational elements	Miscellaneous	UL 94 flammability rating	V-0

System specifications

End cover plate required	No	Number of levels	1
Number of clamping points per level	40	Rail	TS 35
N-function	No	PE function	Yes
PEN function	No		

Additional technical data

Explosion-tested version	No	Snap-on	Yes
Type of mounting	TS 35		

Conductors for clamping (rated connection)

Connection cross-section, stranded, max.	6 mm ²	Connection cross-section, stranded, min.	0.5 mm ²
Connection direction	top	Number of connections	40
Type of connection	PUSH IN	Wire connection cross section, finely stranded, max.	10 mm ²
Wire connection cross section, finely stranded, min.	0.5 mm ²	Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max.	6 mm ²
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min.	0.5 mm ²	Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max.	6 mm ²
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min.	0.5 mm ²	Wire connection cross-section, solid core, max.	10 mm ²
Wire connection cross-section, solid core, min.	0.5 mm ²		

General

Rail	TS 35	Standards	IEC 60947-7-1 (-7-2)
------	-------	-----------	----------------------

Rating data

Rated cross-section	6 mm ²	Rated current	30 A
Standards	IEC 60947-7-1 (-7-2)	Pollution severity	3
Surge voltage category	III		

Creation date August 28, 2024 12:45:38 PM CEST

MSTTAB2019ORANGE_ATTB**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Classifications**

ETIM 6.0	EC000902	ETIM 7.0	EC000902
ETIM 8.0	EC000902	ETIM 9.0	EC000902
ECLASS 9.0	27-14-11-26	ECLASS 9.1	27-14-11-26
ECLASS 10.0	27-14-11-26	ECLASS 11.0	27-14-11-26
ECLASS 12.0	27-14-11-26	ECLASS 13.0	27-25-01-09
ECLASS 14.0	27-25-01-09		

Approvals

ROHS	Conform
------	---------

Downloads

User Documentation	DATA_SHEET_MSTTAB2019ORANGE_ATTB_DE DATA_SHEET_MSTTAB2019ORANGE_ATTB_EN
Catalogues	Catalogues in PDF-format

MSTTAB2019ORANGE_ATTB**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Drawings**