


MPS 7S/04-5/04 S TN B B**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image**SNAP IN** **OMNIMATE® 4.0 - the next evolution step**

OMNIMATE® 4.0 follows the trend of One Cable Technology (OCT). The modular concept enables the fast configuration of hybrid interfaces, which transmit data, signals and energy in a single connector. As a result, you can reduce the cabling effort in a wide variety of applications, simplify maintenance and accelerate automation processes. The unique SNAP IN connection is the backbone and speeds up the wiring process.

The fastest connection yet

- Fast, safe, and tool-free wiring due to unique SNAP IN connection
- Ready for Robot through "wire ready" delivery with open clamping point
- Optical and acoustic feedback indicates proper wiring

Create your own configuration

- Flexible configuration and ordering via the Weidmüller Configurator (WMC)
- Dispatch within three days – even for individually configured products
- Automatic offer preparation for the configured product

Simply configuration of modular hybrid connectors

- Flexible combination options for power, signal and data transmission
- Future-proof Single-Pair Ethernet technology

General ordering data

| | |
|--------------|---|
| Version | PCB plug-in connector, female plug, Pitch in mm (P): 7.50 mm, Number of poles: 8, Box |
| Order No. | 8000078352 |
| Type | MPS 7S/04-5/04 S TN B B |
| GTIN (EAN) | 4064675622307 |
| Qty. | 36 pc(s). |
| Product data | IEC: 1000 V / 34.6 A / 0.5 - 4 mm ² UL: / 18.5 A / AWG 20 - AWG 12 |
| Packaging | Box |

MPS 7S/04-5/04 S TN B B

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|----------|-----------------|------------|
| Depth | 34.95 mm | Depth (inches) | 1.376 inch |
| Height | 15.5 mm | Height (inches) | 0.61 inch |
| Net weight | 20.184 g | | |

System Parameters

| | |
|--|-------------------------|
| Product family | OMNIMATE 4.0 |
| Type of connection | Field connection |
| Wire connection method | SNAP IN |
| Pitch in mm (P) | 7.5 mm |
| Conductor outlet direction | 180° |
| Number of poles | 8 |
| L1 in mm | 22.5 mm |
| L1 in inches | 0.886 " |
| L2 in mm | 15 mm |
| L2 in inch | 0.591 " |
| Number of rows | 1 |
| Pin series quantity | 1 |
| Rated cross-section | 2.5 mm ² |
| Touch-safe protection acc. to DIN VDE 57 106 | Safe from finger touch |
| Touch-safe protection acc. to DIN VDE 0470 | IP 20 |
| Stripping length | 9 mm |
| Stripping length tolerance | min. 8 mm max. 10 mm |
| Plugging cycles | ≥ 25 |
| Plugging force/pole, max. | 9 N |
| Pulling force/pole, max. | 8 N |

Material data

| | | | |
|----------------------------------|----------|-----------------------------|--------|
| Insulating material | PBT GF | Colour | black |
| Colour chart (similar) | RAL 9011 | Insulating material group | I |
| Comparative Tracking Index (CTI) | ≥ 600 | UL 94 flammability rating | V-0 |
| Contact material | Cu-alloy | Contact surface | tinned |
| Storage temperature, min. | -25 °C | Storage temperature, max. | 55 °C |
| Operating temperature, min. | -50 °C | Operating temperature, max. | 125 °C |

Conductors suitable for connection

| | |
|--|----------------------|
| Clamping range, min. | 0.34 mm ² |
| Clamping range, max. | 4 mm ² |
| Wire connection cross section AWG, min. | AWG 20 |
| Wire connection cross section AWG, max. | AWG 12 |
| Solid, min. H05(07) V-U | 0.5 mm ² |
| Solid, max. H05(07) V-U | 2.5 mm ² |
| Flexible, min. H05(07) V-K | 0.5 mm ² |
| Flexible, max. H05(07) V-K | 4 mm ² |
| w. plastic collar ferrule, DIN 46228 pt 4, 0.34 mm ² min. | |
| w. plastic collar ferrule, DIN 46228 pt 4, 2.5 mm ² max. | |

Creation date May 23, 2024 10:43:18 PM CEST

MPS 7S/04-5/04 S TN B B

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

w. wire end ferrule, DIN 46228 pt 1, min. 0.34 mm²w. wire end ferrule, DIN 46228 pt 1, max. 2.5 mm²

Outer diameter of insulation, max. 4 mm

| | | | |
|---------------------|--|------------------------------|-----------------------------|
| Clampable conductor | Cross-section for conductor connection | nominal | 0.34 mm ² |
| | wire end ferrule | Stripping length | nominal 10 mm |
| | | Recommended wire-end ferrule | H0.34/12 TK |
| | Cross-section for conductor connection | nominal | 0.5 mm ² |
| | wire end ferrule | Stripping length | nominal 12 mm |
| | | Recommended wire-end ferrule | H0.5/16 OR |
| | | Stripping length | nominal 10 mm |
| | | Recommended wire-end ferrule | H0.5/10 |
| | Cross-section for conductor connection | nominal | 0.75 mm ² |
| | wire end ferrule | Stripping length | nominal 12 mm |
| | | Recommended wire-end ferrule | H0.75/16 W |
| | | Stripping length | nominal 10 mm |
| | | Recommended wire-end ferrule | H0.75/10 |
| | Cross-section for conductor connection | nominal | 1 mm ² |
| | wire end ferrule | Stripping length | nominal 12 mm |
| | | Recommended wire-end ferrule | H1.0/16 GE |
| | | Stripping length | nominal 10 mm |
| | | Recommended wire-end ferrule | H1.0/10 |
| | Cross-section for conductor connection | nominal | 1.5 mm ² |
| | wire end ferrule | Stripping length | nominal 12 mm |
| | | Recommended wire-end ferrule | H1.5/16 R |
| | | Stripping length | nominal 10 mm |
| | | Recommended wire-end ferrule | H1.5/10 |
| | Cross-section for conductor connection | nominal | 2.5 mm ² |
| | wire end ferrule | Stripping length | nominal 10 mm |
| | | Recommended wire-end ferrule | H2.5/15D BL |
| | | Stripping length | nominal 10 mm |
| | | Recommended wire-end ferrule | H2.5/10 |

Reference text The outside diameter of the plastic collar should not be larger than the pitch (P)

Rated data acc. to IEC

| | | | |
|---|------------------------|--|---------|
| tested acc. to standard | IEC 60664-1, IEC 61984 | Rated current, min. number of poles (Tu=20°C) | 34.6 A |
| Rated current, max. number of poles (Tu=20°C) | 29.1 A | Rated current, min. number of poles (Tu=40°C) | 30.7 A |
| Rated current, max. number of poles (Tu=40°C) | 25.9 A | Rated voltage for surge voltage class / pollution degree II/2 | 1,000 V |
| Rated voltage for surge voltage class / pollution degree III/2 | 1,000 V | Rated impulse voltage for surge voltage class/ pollution degree II/2 | 6 kV |
| Rated impulse voltage for surge voltage class/ pollution degree III/2 | 8 kV | | |

MPS 7S/04-5/04 S TN B B

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Rated data acc. to UL 1059

Institute (cURus)



Certificate No. (cURus)

E60693

Rated voltage (Use group F / UL 1059) 1,000 V

Rated current (Use group C / UL 1059) 18.5 A

Rated current (Use group F / UL 1059) 18.5 A

Wire cross-section, AWG, max.

AWG 12

Rated current (Use group B / UL 1059) 18.5 A

Rated current (Use group D / UL 1059) 10 A

Wire cross-section, AWG, min. AWG 20

Reference to approval values

Specifications are maximum values, details - see approval certificate.

Technical data - hybrid (power)

Number of poles (Power) 4

Pitch in mm (Power) 7.5 mm

Contact material (Power) CuSn

Clamping range, min. (Power) 0.5 mm²w. wire end ferrule, DIN 46228 pt 1, min. (Power) 0.5 mm²

Wire cross-section, AWG, min. (Power) AWG 20

w. plastic collar ferrule, DIN 46228 pt 4, min. (Power) 2.5 mm²Flexible, min. H05(07) V-K (Power) 0.5 mm²Solid, min. H05(07) V-U (Power) 0.5 mm²

Outside diameter of the insulation, max. (Power) 4 mm

Rated current (Use group B / UL 1059) (Power) 18.5 A

Rated current (Use group D / UL 1059) (Power) 10 A

Rated current, max. number of poles (Tu=20°C) (Power) 29.1 A

Rated current, max. number of poles (Tu=40°C) (Power) 25.9 A

Rated impulse voltage for surge voltage class/ pollution degree III/2 (Power) 4 kV

Rated voltage (Use group C / UL 1059) (Power) 600 V

Rated voltage for surge voltage class / pollution degree II/2 (Power) 1,000 V

Rated voltage for surge voltage class / pollution degree III/3 (Power) 630 V

Number of rows (Power) 1

Pitch in inches (Power) 0.295 "

Contact surface (Power) tinned

Clamping range, max. (Power) 4 mm²w. wire end ferrule, DIN 46228 pt 1, max. (Power) 2.5 mm²

Wire cross-section, AWG, max. (Power) AWG 12

w. plastic collar ferrule, DIN 46228 pt 4, max. (Power) 0.5 mm²Flexible, max. H05(07) V-K (Power) 4 mm²Solid, max. H05(07) V-U (Power) 2.5 mm²

Stripping length (Power) 9 mm

Rated current (Use group C / UL 1059) (Power) 18.5 A

Rated current, min. number of poles (Tu=20°C) (Power) 34.6 A

Rated current, min. number of poles (Tu=40°C) (Power) 30.7 A

Rated impulse voltage for surge voltage class/ pollution degree II/2 (Power) 4 kV

Rated voltage (Use group B / UL 1059) (Power) 600 V

Rated voltage (Use group D / UL 1059) (Power) 600 V

Rated voltage for surge voltage class / pollution degree III/2 (Power) 1,000 V

Clearance distance, min. (Power) 9.96 mm

MPS 7S/04-5/04 S TN B B

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Technical data - hybrid (signal)

| | | | |
|--|---------------------|--|---------------------|
| Number of poles (Signal) | 4 | Pitch in mm (Signal) | 5 mm |
| Pitch in inches (Signal) | 0.197 " | Contact material (Signal) | CuSn |
| Contact surface (Signal) | tinned | Clamping range, min. (Signal) | 0.5 mm ² |
| Clamping range, max. (Signal) | 4 mm ² | Wire cross-section, AWG, min. (Signal) | AWG 20 |
| Wire cross-section, AWG, max. (Signal) | AWG 12 | w. plastic collar ferrule, DIN 46228 pt 4, min. (Signal) | 0.5 mm ² |
| w. plastic collar ferrule, DIN 46228 pt 4, max. (Signal) | 2.5 mm ² | w. wire end ferrule, DIN 46228 pt 1, min. (Signal) | 0.5 mm ² |
| w. wire end ferrule, DIN 46228 pt 1, max. (Signal) | 2.5 mm ² | Flexible, min. H05(07) V-K (Signal) | 0.5 mm ² |
| Flexible, max. H05(07) V-K (Signal) | 4 mm ² | Solid, min. H05(07) V-U (Signal) | 0.5 mm ² |
| Solid, max. H05(07) V-U (Signal) | 2.5 mm ² | Outside diameter of the insulation, max. (Signal) | 4 mm |
| Stripping length (Signal) | 9 mm | Rated current (Use group B / UL 1059) (Signal) | 18.5 A |
| Rated current (Use group C / UL 1059) (Signal) | 18.5 A | Rated current (Use group D / UL 1059) (Signal) | 10 A |
| Rated current, min. number of poles (Tu=20°C) (Signal) | 26.8 A | Rated current, max. number of poles (Tu=20°C) (Signal) | 19.7 A |
| Rated current, min. number of poles (Tu=40°C) (Signal) | 23.1 A | Rated current, max. number of poles (Tu=40°C) (Signal) | 16.9 A |
| Rated impulse voltage for surge voltage class/ pollution degree II/2 (Signal) | 4 kV | Rated impulse voltage for surge voltage class/ pollution degree III/2 (Signal) | 4 kV |
| Rated impulse voltage for surge voltage class/ pollution degree III/3 (Signal) | 4 kV | Rated voltage (Use group B / UL 1059) (Signal) | 600 V |
| Rated voltage (Use group C / UL 1059) (Signal) | 600 V | Rated voltage (Use group D / UL 1059) (Signal) | 600 V |
| Rated voltage for surge voltage class / pollution degree II/2 (Signal) | 400 V | Rated voltage for surge voltage class / pollution degree III/2 (Signal) | 320 V |
| Rated voltage for surge voltage class / pollution degree III/3 (Signal) | 250 V | Clearance distance, min. (Signal) | 7.5 mm |
| Creepage distance, min. (Signal) | 7.5 mm | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC002638 | ETIM 7.0 | EC002638 |
| ETIM 8.0 | EC002638 | ETIM 9.0 | EC002638 |
| ECLASS 9.0 | 27-44-03-09 | ECLASS 9.1 | 27-44-03-09 |
| ECLASS 10.0 | 27-44-03-09 | ECLASS 11.0 | 27-46-02-02 |
| ECLASS 12.0 | 27-46-03-02 | ECLASS 13.0 | 27-46-03-02 |

MPS 7S/04-5/04 S TN B B

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Important note

| | |
|----------------|---|
| IPC conformity | Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the products can be evaluated on request. |
| Notes | <ul style="list-style-type: none"> Rated current related to rated cross-section & min. No. of poles. P on drawing = pitch Rated data refer only to the component itself. Clearance and creepage distances to other components are to be designed in accordance with the relevant application standards. Wire end ferrule without plastic collar to DIN 46228/1 In accordance with IEC 61984, OMNIMATE-connectors are connectors without breaking capacity (COC). During designated use, connectors are not allowed to be engaged or disengaged when live or under load Long term storage of the product with average temperature of 50 °C and maximum humidity 70%, 36 months |

Approvals

Approvals



| | |
|-------------------------|------------|
| UL File Number Search | UL Website |
| Certificate No. (cURus) | E60693 |

Downloads

| | |
|---|--|
| Approval/Certificate/Document of Conformity | CoC_cURus_E60693_MPS_MHS_202207.pdf |
| Engineering Data | Declaration of the Manufacturer |
| User Documentation | CAD data – STEP |
| Catalogues | Assembly instructions MPS 7S/5 EN DE |
| | Catalogues in PDF-format |



MPS 7S/04-5/04 S TN B B

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Product image



Product benefits




Fastest connection technology SNAP IN

Product benefits



Acoustic and visual feedback



The reproduction, distribution and utilization of this document as well as the communication of its contents to others without explicit authorization is prohibited. Offenders will be held liable for the payment of damages. Weidmueller exclusively reserves the right to file for patents, utility models or designs.





© Weidmueller Interface GmbH & Co. KG

Dimensions without tolerances are no check dimensions


The English version is binding

Allgemeinguetlige Kundenzeichnung, aktueller Stand nur auf Anfrage
General customer drawing, topical version only if required

Shown: MPS 7S/04-5/04 S



Min. front plate cut-out



M 1/1

Further dim. & info. see data sheet

| | | | | | | |
|----------------|------------------|------------|--------------|----------------|------------|--------------|
| MPS 7S/01-5/09 | 1 | . | . | 9 | 40.00 | 1.575 |
| MPS 7S/02-5/08 | 2 | 7.50 | 0.295 | 8 | 35.00 | 1.378 |
| MPS 7S/01-5/08 | 1 | . | . | 8 | 35.00 | 1.378 |
| MPS 7S/02-5/07 | 2 | 7.50 | 0.295 | 7 | 30.00 | 1.181 |
| MPS 7S/01-5/07 | 1 | . | . | 7 | 30.00 | 1.181 |
| MPS 7S/03-5/06 | 3 | 15.00 | 0.591 | 6 | 25.00 | 0.984 |
| MPS 7S/02-5/06 | 2 | 7.50 | 0.295 | 6 | 25.00 | 0.984 |
| MPS 7S/01-5/06 | 1 | . | . | 6 | 25.00 | 0.787 |
| MPS 7S/04-5/05 | 4 | 22.50 | 0.886 | 5 | 20.00 | 0.787 |
| MPS 7S/03-5/05 | 3 | 15.00 | 0.591 | 5 | 20.00 | 0.787 |
| MPS 7S/02-5/05 | 2 | 7.50 | 0.295 | 5 | 20.00 | 0.787 |
| MPS 7S/01-5/05 | 1 | . | . | 5 | 20.00 | 0.787 |
| MPS 7S/04-5/04 | 4 | 22.50 | 0.886 | 4 | 15.00 | 0.591 |
| MPS 7S/03-5/04 | 3 | 15.00 | 0.591 | 4 | 15.00 | 0.591 |
| MPS 7S/02-5/04 | 2 | 7.50 | 0.295 | 4 | 15.00 | 0.591 |
| MPS 7S/01-5/04 | 1 | . | . | 4 | 15.00 | 0.591 |
| MPS 7S/05-5/03 | 5 | 30.00 | 1.181 | 3 | 10.00 | 0.394 |
| MPS 7S/04-5/03 | 4 | 22.50 | 0.886 | 3 | 10.00 | 0.394 |
| MPS 7S/03-5/03 | 3 | 15.00 | 0.591 | 3 | 10.00 | 0.394 |
| MPS 7S/02-5/03 | 2 | 7.50 | 0.295 | 3 | 10.00 | 0.394 |
| MPS 7S/01-5/03 | 1 | . | . | 3 | 10.00 | 0.394 |
| MPS 7S/06-5/02 | 6 | 37.50 | 1.476 | 2 | 5.00 | 0.197 |
| MPS 7S/05-5/02 | 5 | 30.00 | 1.181 | 2 | 5.00 | 0.197 |
| MPS 7S/04-5/02 | 4 | 22.50 | 0.886 | 2 | 5.00 | 0.197 |
| MPS 7S/03-5/02 | 3 | 15.00 | 0.591 | 2 | 5.00 | 0.197 |
| MPS 7S/02-5/02 | 2 | 7.50 | 0.295 | 2 | 5.00 | 0.197 |
| MPS 7S/01-5/02 | 1 | . | . | 2 | 5.00 | 0.197 |
| Name | n Poles P=7.5 | L1 [mm] | L1 [inch] | n Poles P=5 | L2 [mm] | L2 [inch] |

For the mounting of PCBs, it should be noted that the rated data given in the catalogue relates only to the connection elements. The necessary creepage and clearance paths must be observed in connection with the respective applicant in accordance to VDE 0110. The current-carrying capacity and pitch tolerance is to be determined according to DIN IEC 326 part 3 very fine.

Weidmueller connectors are tested to the DIN VDE 0627 standard, and are valid for its field of application. Provided that the connectors are used to the intended purpose, all requirements with respect to the occurring of electrical, mechanical, thermic and corrosive stress will be satisfied.

| | | | | | | | | | |
|-------------------|--|--------------------------------|--|---------------------------------------|--|--------------------------------------|--|------------------------|--|
| RoHS COMPLIANT | | First Issue Date 19.04.2021 | | Max. nos. Modification | | Prim PLM Part No.: . | | Prim ERP Part No.: . | |
| Scale: 2/1 | | Size: A3 | | Drawn 19.04.2021 Tauber-Reglin, | | Date 19.04.2021 Tauber-Reglin, | | Name Sapina, Svetos | |
| Drawings Assembly | | Product file: | | Approved 06.05.2021 | | Sapina, Svetos | | MPS 7S/...-5/... S | |
| Weidmüller | | 74516 | | Drawing no. Sheet 3 of 4 sheets | | Issue no. 0 | | | |