

PV CUXI17TXU1DXAXWXR2WW


Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Connecting photovoltaic power plants through reliable and safe industrial communications.

Weidmüller combined its extensive experience with photovoltaic projects and industrial communication to create this portfolio of PV Communication Boxes. For this portfolio we developed 2 different product ranges:

- The “Premium” family is our most robust product. Designed to offer constant connectivity thanks to its back-up power system. And thereby offers you reliability and power in one solution.
- The new “Lite” family offers you the same signal connectivity on site as the “Premium” version, but in a more compact version.

General ordering data

Version	Photovoltaics, Assembled enclosure, Communication module, 230 V AC, Surge protection I, Battery powered, Current monitoring, Monitoring components, Voltage monitoring, Limit value monitoring, Communication Box, RJ45
Order No.	8000101637
Type	PV CUXI17TXU1DXAXWXR2WW
GTIN (EAN)	4099986191990
Qty.	1 pc(s).

Creation date June 5, 2024 8:10:13 AM CEST

Catalogue status 01.06.2024 / We reserve the right to make technical changes.

PV CUXI17TXU1DXAXWXR2WW

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	200 mm	Depth (inches)	7.874 inch
Height	530 mm	Height (inches)	20.866 inch
Width	430 mm	Width (inches)	16.929 inch
Net weight	13,980.339 g		

DC electrical properties

Earthing	Directly at the VPU	Rated voltage	230 V
Surge protection AC side	PU I 1+1 LCF 280V/12.5kA, without auxiliary contact	Surge protection WIA RS485 side (string monitoring)	No

DC string monitoring

Monitoring function	Industrial Ethernet managed switch with RJ45 and SC Multi-mode ports, Connection between field devices to SCADA through RS-485	Supply	Battery PRO ECO 72W 24V 3A
Voltage monitoring	Yes		

Housing

Protection degree	IP65	Type of mounting	Wall mounting
-------------------	------	------------------	---------------

Norms and standards

Standards	IEC 61439-2 ed 3.0, EN 61439-2:2020
-----------	--

Guarantee

Time interval	5 years
---------------	---------

Enclosure

Enclosure attachment	Fixing lugs	Insulating material	Polyester glass-fibre reinforced, Polycarbonate
Type of mounting	Wall mounting		

General data

Installation location	Protected outdoor area (>1 km from sea)	Protection degree	IP65
Standards	IEC 61439-2 ed 3.0, EN 61439-2:2020		

Surge protection DC side

Standards	IEC 61439-2 ed 3.0, EN 61439-2:2020
-----------	--

PV CUXI17TXU1DXAXWXR2WW**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Classifications**

ETIM 6.0	EC002928	ETIM 7.0	EC002928
ETIM 8.0	EC003857	ETIM 9.0	EC003857
ECLASS 9.0	22-57-92-03	ECLASS 9.1	22-57-02-90
ECLASS 10.0	22-57-02-90	ECLASS 11.0	22-57-02-92
ECLASS 12.0	22-57-02-92	ECLASS 13.0	22-57-02-92

Approvals

Approvals

**Downloads**

Engineering Data	Thermal Report
Technical Documentation	Mechanical Drawing
Catalogues	Catalogues in PDF-format

PV CUXI17TXU1DXAXWXR2WW

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

