


TAB NS NORD 14**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Current and voltage transformer wiring**

Our test disconnect terminal blocks featuring spring and screw connection technology allow you to create all the important converter circuits for measuring current, voltage and power in a safe and sophisticated way.

General ordering data

| | |
|------------|--|
| Version | Test-disconnect terminal, PUSH IN, 6 mm ² , 30 A, sliding, Cross-disconnect: sliding, Integral test socket: Yes, TS 35, beige |
| Order No. | 8000104257 |
| Type | TAB NS NORD 14 |
| GTIN (EAN) | 4099986647664 |
| Qty. | 1 pc(s). |

TAB NS NORD 14

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|--------|-----------------|------------|
| Depth | 79 mm | Depth (inches) | 3.11 inch |
| Height | 100 mm | Height (inches) | 3.937 inch |
| Width | 136 mm | Width (inches) | 5.354 inch |
| Net weight | 551 g | | |

Temperatures

| | | | |
|----------------------------------|--------|----------------------------------|--------|
| Continuous operating temp., min. | -60 °C | Continuous operating temp., max. | 130 °C |
|----------------------------------|--------|----------------------------------|--------|

Material data

| | | | |
|--------------------------------|---------------|---------------------------|-------|
| Material | Wemid | Colour | beige |
| Colour of operational elements | Miscellaneous | UL 94 flammability rating | V-0 |

System specifications

| | | | |
|-------------------------------------|-------|-----------------------------------|----|
| End cover plate required | No | Number of levels | 1 |
| Number of clamping points per level | 14 | Levels cross-connected internally | No |
| Rail | TS 35 | N-function | No |
| PE function | No | PEN function | No |

Additional technical data

| | | | |
|--------------------------|---------|---------|-----|
| Explosion-tested version | No | Snap-on | Yes |
| Type of mounting | Snap-on | | |

Conductors for clamping (rated connection)

| | | | |
|---|---------------------|---|---------------------|
| Connection cross-section, stranded, max. | 6 mm ² | Connection cross-section, stranded, min. | 0.5 mm ² |
| Connection direction | top | Number of connections | 14 |
| Type of connection | PUSH IN | Wire connection cross section, finely stranded, max. | 10 mm ² |
| Wire connection cross section, finely stranded, min. | 0.5 mm ² | Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max. | 6 mm ² |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min. | 0.5 mm ² | Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max. | 6 mm ² |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min. | 0.5 mm ² | Wire connection cross-section, solid core, max. | 10 mm ² |
| Wire connection cross-section, solid core, min. | 0.5 mm ² | | |

General

| | | | |
|------|-------|-----------|---------------|
| Rail | TS 35 | Standards | IEC 60947-7-1 |
|------|-------|-----------|---------------|

Rating data

| | | | |
|------------------------|-------------------|--------------------|------|
| Rated cross-section | 6 mm ² | Rated current | 30 A |
| Standards | IEC 60947-7-1 | Pollution severity | 3 |
| Surge voltage category | III | | |

TAB NS NORD 14**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Classifications**

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000902 | ETIM 7.0 | EC000902 |
| ETIM 8.0 | EC000902 | ETIM 9.0 | EC000902 |
| ECLASS 9.0 | 27-14-11-26 | ECLASS 9.1 | 27-14-11-26 |
| ECLASS 10.0 | 27-14-11-26 | ECLASS 11.0 | 27-14-11-26 |
| ECLASS 12.0 | 27-14-11-26 | ECLASS 13.0 | 27-25-01-09 |

Downloads

| | |
|--------------------|--|
| User Documentation | DATA_SHEET_TAB_NS_NORD_14_DE DATA_SHEET_TAB_NS_NORD_14_EN |
| Catalogues | Catalogues in PDF-format |

TAB NS NORD 14

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

