

**PV 212SXFXCXXVXO3TA3PA15LWW****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Intelligent product in a compact size**

PV retrofit monitoring boxes make it possible to obtain data at string level in PV systems with existing, unmonitored PV-DC generator combiner boxes. All without additional work such as trenching and cabling.

Integrated power monitoring provided by our Solar SMS monitoring system allows to do the right surveillance of the PV site to guarantee the best performance of the system.

Additionally, our PV monitoring boxes fulfill the standard IEC/EN 61439-2:2020 to guarantee a high reliability of the supplied units.

**General ordering data**

Version	Photovoltaics, Assembled enclosure, 1500 V, Cable gland, for wall mounting, Landscape, Digital signals, Monitoring components, Current monitoring, Voltage monitoring, Temperature monitoring, 12-channel
Order No.	<a href="#">8000112714</a>
Type	PV 212SXFXCXXVXO3TA3PA15LWW
GTIN (EAN)	4099986869400
Qty.	1 pc(s).

**PV 212SXF CX XV X03TA3PA15LWW****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Depth	210 mm	Depth (inches)	8.268 inch
Height	302 mm	Height (inches)	11.89 inch
Width	558 mm	Width (inches)	21.968 inch
Net weight	7,452.393 g		

**Temperatures**

Ambient temperature	-20°C to +45 °C	Operating temperature	-20°C to +45 °C
---------------------	-----------------	-----------------------	-----------------

**DC electrical properties**

Rated voltage	1,500 V	Surge protection DC side	No surge protection
---------------	---------	--------------------------	---------------------

**DC inputs**

Connection DC input cable (+)	PUSH IN		
Connection DC input cable (-)	PUSH IN		
Connection type, DC input cable	Cable gland		
DC Input + & -	Wire connection	Type of connection	PUSH IN
		Wire cross-section, min.	0.5 mm <sup>2</sup>
		Wire cross-section, max.	6 mm <sup>2</sup>
	Cable entry	Number of cable entries	12
		Cable diameter, min.	5 mm
		Cable diameter, max.	7 mm
Fuse	No		
Fuse	Neither fuse cartridge nor holder		
Fuse type	Neither fuse cartridge nor holder		
Number of DC inputs	12		

**DC outputs**

Connection type, DC output cable	PUSH IN		
DC Output + & -	Wire connection	Type of connection	PUSH IN
		Wire cross-section, min.	0.5 mm <sup>2</sup>
		Wire cross-section, max.	6 mm <sup>2</sup>
DC output cable connection	Cable gland		
Number of DC outputs	12		

**DC string monitoring**

Current monitoring	Solar SMS	Monitoring function	Solar SMS, Output voltage, current, temperature
Supply	Self-powered	Temperature monitoring	Solar SMS
Voltage monitoring	Solar SMS		

**Housing**

Protection degree	IP65	Type of mounting	Wall mounting
-------------------	------	------------------	---------------

## PV 212SXFXCXXVXO3TA3PA15LWW

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Norms and standards

Standards	EN 61439-2:2020, IEC 61439-2 ed 3.0
-----------	-------------------------------------

## Guarantee

Time interval	5 years
---------------	---------

## Electrical characteristics

Rated DC voltage	1,500 V
------------------	---------

## Enclosure

Connection type string	Internal terminal (with cable gland feed-through)	Cover	with cover
Enclosure attachment	Fixing lugs	Impact resistance	IK10 in accordance with IEC 62262
Insulating material	Polyester glass-fibre reinforced, Polycarbonate	Switch disconnector execution	no switch
Type of mounting	Wall mounting		

## General data

Installation location	Protected outdoor area (>1 km from sea)	Protection degree	IP65
Standards	EN 61439-2:2020, IEC 61439-2 ed 3.0		

## Surge protection DC side

Short-circuit current $I_{SCP}$	12 A	Standards	EN 61439-2:2020, IEC 61439-2 ed 3.0
Surge protection DC side	No surge protection		

## Classifications

ETIM 6.0	EC002928	ETIM 7.0	EC002928
ETIM 8.0	EC003857	ETIM 9.0	EC003857
ECLASS 9.0	22-57-92-03	ECLASS 9.1	22-57-02-90
ECLASS 10.0	22-57-02-90	ECLASS 11.0	22-57-02-92
ECLASS 12.0	22-57-02-92	ECLASS 13.0	22-57-02-92

## Approvals

Approvals



## Downloads

Engineering Data	<a href="#">Thermal report</a>
Technical Documentation	<a href="#">Mechanical Drawing</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

Creation date June 4, 2024 8:19:39 PM CEST

Catalogue status 01.06.2024 / We reserve the right to make technical changes.

## PV 212SFXCXXVXO3TA3PA15LWW

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

