


PV WUCI08TXUXDXAXWXR3WW**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Connecting photovoltaic power plants through reliable and safe industrial communications.**

To provide you with reliable information on all important weather parameters of your PV power plant Weidmüller created this portfolio of PV Weather Boxes with 2 families of products:

- Premium: Ready for immediate use, extremely robust, and protected against all-weather influences.
- Lite: The new "Lite" family offers the main functionality and protections of the "Premium" version but in a compact enclosure.

General ordering data

Version	Photovoltaics, Enclosures, Industrial Monitor, 230 V AC, RJ45, Web-based, Weather Box
Order No.	8000113428
Type	PV WUCI08TXUXDXAXWXR3WW
GTIN (EAN)	4099986694217
Qty.	1 pc(s).

PV WUCI08TXUXDXAXWXR3WW

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	200 mm	Depth (inches)	7.874 inch
Height	530 mm	Height (inches)	20.866 inch
Width	430 mm	Width (inches)	16.929 inch
Net weight	10,418.595 g		

Temperatures

Ambient temperature	-20°C to +50°C	Operating temperature	-20°C to +50°C
---------------------	----------------	-----------------------	----------------

DC electrical properties

Earthing	Directly at the VPU	Rated voltage	230 V
Surge protection AC side	PU I 1+1 LCF 280V/12,5kA, without auxiliary contact	Surge protection WIA RS485 side (string monitoring)	yes, no auxiliary contact

DC inputs

Number of conduit inlets	9	Number of inputs	11
--------------------------	---	------------------	----

DC string monitoring

Monitoring function	Industrial Ethernet router with 4G and RJ45 ports, Connection between field weather sensors to SCADA through RS-485	Supply	Battery PRO ECO 72W 24V 3A
Voltage monitoring	Yes		

Housing

Protection degree	IP65	Type of mounting	Wall mounting
-------------------	------	------------------	---------------

Norms and standards

Standards	IEC 61439-2 ed 3.0, EN 61439-2:2011
-----------	--

Guarantee

Time interval	5 years
---------------	---------

Enclosure

Enclosure attachment	Fixing lugs	Impact resistance	IK10 in accordance with IEC 62262
Insulating material	Polyester glass-fibre rein- forced, Polycarbonate	Type of mounting	Wall mounting

General data

Installation location	Protected outdoor area (>1 km from sea)	Protection degree	IP65
Standards	IEC 61439-2 ed 3.0, EN 61439-2:2011		

Creation date August 24, 2024 3:15:19 AM CEST

Catalogue status 17.08.2024 / We reserve the right to make technical changes.

PV WUCI08TXUXDXAXWXR3WW**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Surge protection DC side**

Standards	IEC 61439-2 ed 3.0, EN 61439-2:2011
-----------	-------------------------------------

Classifications

ETIM 6.0	EC002928	ETIM 7.0	EC002928
ETIM 8.0	EC003857	ETIM 9.0	EC003857
ECLASS 9.0	22-57-92-03	ECLASS 9.1	22-57-02-90
ECLASS 10.0	22-57-02-90	ECLASS 11.0	22-57-02-92
ECLASS 12.0	22-57-02-92	ECLASS 13.0	22-57-02-92
ECLASS 14.0	22-57-02-92		

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1 6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol 119-47-1
RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c, 7a, 7cl

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Approval/Certificate/Document of Conformity	Declaration of of conformity utility communication boxes
Engineering Data	Thermal Report
Technical Documentation	Mechanical Drawing
User Documentation	PV Weather Box User Manual
Catalogues	Catalogues in PDF-format

PV WUCI08TXUXDXAXWXR3WW

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

