

**PAS CMR 0,5...2,5 A DC****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image, Similar to illustration**

The PLUGCONTROL PAS CMRs present a simple, cost-effective solution for monitoring DC currents up to 10 A.

The monitoring relay (REED contact) comes attached to a standard base so that it can be mounted on a TS35 DIN rail.

Current monitoring of valves, servo-controls and DC motors are typical applications for these modules.

**General ordering data**

Version	Current monitoring, 0.5...2.5 A DC, Screw connection
Order No.	<a href="#">8742610000</a>
Type	PAS CMR 0,5...2,5 A DC
GTIN (EAN)	4032248413928
Qty.	10 pc(s).

## PAS CMR 0,5...2,5 A DC

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	95 mm	Depth (inches)	3.74 inch
Width	15.3 mm	Width (inches)	0.602 inch
Length	92 mm	Length (inches)	3.622 inch
Net weight	69.6 g		

## Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-20 °C...60 °C
Humidity at operating temperature		Humidity	5-95% relative humidity, T <sub>u</sub> = 40°C, without condensation
	0...95 % (no condensation)		

## Probability of failure

SIL in compliance with IEC 61508	None
----------------------------------	------

## General data

Configuration	none	Galvanic isolation	2-way isolator, between input/output/supply
Protection degree	IP20	Rail	TS 35
Temperature coefficient	350 ppm/K		

## Insulation coordination

EMC standards	EN 55011, EN 61000-6-1, 2, 3, 4	Galvanic isolation	2-way isolator, between input/output/supply
Impulse withstand voltage	6 kV	Insulation voltage	4 kV <sub>eff</sub> / 1 min.
Pollution severity	2	Rated voltage	300 V
Surge voltage category	III		

## Input

Input current	0.5...2.5 A DC	Input resistance, current	<50 mΩ
Making current threshold	≤ 500 mA	Max. current	7.5 A for 10 s
Pulse duration	min. 1 ms	Secure off	≤ 50 mA

## Output

Contact assembly	1 NO contact	Contact material	RH/Rd (Reed contact)*
Continuous current	100 mA	Max. switching frequency	20 Hz
Max. switching voltage, AC	250 V	Max. switching voltage, DC	100 V
Switching current	100 mA	Switching voltage AC, min.	1 V
Switching voltage DC, min.	1 V	Temperature coefficient	350 ppm/K

## Connection data

Type of connection	Screw connection	Clamping range, rated connection	1.5 mm <sup>2</sup>
Clamping range, min.	2.5 mm <sup>2</sup>	Clamping range, max.	2.5 mm <sup>2</sup>

**PAS CMR 0,5...2,5 A DC****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Classifications**

ETIM 6.0	EC002654	ETIM 7.0	EC002654
ETIM 8.0	EC002654	ETIM 9.0	EC002654
ECLASS 9.0	27-21-01-22	ECLASS 9.1	27-21-01-22
ECLASS 10.0	27-21-01-22	ECLASS 11.0	27-21-01-22
ECLASS 12.0	27-21-01-22	ECLASS 13.0	27-21-01-22

## PAS CMR 0,5...2,5 A DC

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Tender specification sheets

## Long specification

**Limit-value monitoring  
of DC currents up to 2.5  
A with switching out-  
put**

limit-value monitoring component for measuring DC currents 0.5... 2.5 A with switching output. The monitoring unit is designed so that it can be plugged onto the mounting base.

**Pluggable unit on base,  
for mounting on TS35  
DIN rail**

**Dimensions: L/W/H 92/  
15.3/ 95 mm**

**Screw connection /  
Nominal cross-section  
2.5 mm<sup>2</sup>**

**Protection degree: IP  
20**

## Input

**0.5...2.5 A DC / Reed  
relay coil  
Switch-on threshold <  
500 mA  
Switch-off threshold  
< 50 mA  
Output**

**1 NO / Reed contact  
Switching current max  
100 mA AC/DC  
Switching voltage 100  
V AC / 50 V DC  
Ambient  
temperature range 0  
°C...+55 °C**

**Secure isolation EN 50178,  
2-way isolation up to 6  
kV**

**Test voltage 4  
kVeff / 1 min. input  
against output  
Rated  
voltage**

**300 V AC/DC at  
overvoltage category III  
and pollution degree 2  
Approvals cULus**

**Type  
PAS CMR 0.5...2.5 A  
DC**

## Short specification

**Limit-value monitoring  
of DC currents up to 2.5  
A with switching out-  
put**

limit-value monitoring component for measuring DC currents 0.5... 2.5 A with switching output. The monitoring unit is designed so that it can be plugged onto the mounting base.

## PAS CMR 0,5...2,5 A DC

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

## Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E141197

## Downloads

Approval/Certificate/Document of Conformity	<a href="#">Application notes – Declaration of Conformity</a>
User Documentation	<a href="#">Instruction sheet</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	



## PAS CMR 0,5...2,5 A DC

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

### Electric symbol



## PAS CMR 0,5...2,5 A DC

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Blank



WS markers are the perfect match for the W-series connectors. Thanks to their system compatibility, the WS tags can also be used with the I-series and the Z-series. The large marking surfaces do not only permit long character strings but also multi-line text. WS markers are ideal for labels with long, customised character strings. Thanks to the proven MultiCard format, printing with PrintJet CONNECT oder/or Plotter is possible.

- Can be fitted in strips or individually
- Markers in proven MultiCard format

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

Type	WS 10/5 MC NE WS	Version
Order No.	<a href="#">1635000000</a>	WS, Terminal marker, 10 x 5 mm, Pitch in mm (P): 5.00 Weidmueller,
GTIN (EAN)	4008190261948	Allen-Bradley, white
Qty.	720 pc(s).	

## PLUGSERIES

## General ordering data

Type	PRC HALTEBUEGEL	Version
Order No.	<a href="#">8536700000</a>	PLUGSERIES, Retaining clip
GTIN (EAN)	4032248171965	
Qty.	100 pc(s).	
Type	ZQV 2.5N 1/4-2 BL	Version
Order No.	<a href="#">1784290000</a>	PLUGSERIES, Cross-connector
GTIN (EAN)	4032248216383	
Qty.	60 pc(s).	
Type	ZQV 2.5N 1/4-2 RT	Version
Order No.	<a href="#">1784280000</a>	PLUGSERIES, Cross-connector
GTIN (EAN)	4032248214686	
Qty.	60 pc(s).	

**PAS CMR 0,5...2,5 A DC****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories**

Type	ZQV 2.5N 1/4-2 SW	Version
Order No.	<a href="#">1784270000</a>	PLUGSERIES, Cross-connector
GTIN (EAN)	40322482 14679	
Qty.	60 pc(s).	

**Blank**

WS markers are the perfect match for the W-series connectors. Thanks to their system compatibility, the WS tags can also be used with the I-series and the Z-series. The large marking surfaces do not only permit long character strings but also multi-line text. WS markers are ideal for labels with long, customised character strings. Thanks to the proven MultiCard format, printing with PrintJet CONNECT oder/or Plotter is possible.

- Can be fitted in strips or individually
- Markers in proven MultiCard format

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

**General ordering data**

Type	WS 15/5 MC NE WS	Version
Order No.	<a href="#">1609880000</a>	WS, Terminal marker, 15 x 5 mm, Pitch in mm (P): 5.00 Weidmueller,
GTIN (EAN)	4008190203504	Allen-Bradley, white
Qty.	480 pc(s).	