

**IE-C6ES8UG0150A40A40-E****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Assembled IE cables, patch cable Cabinet Line, various colours

**General ordering data**

Version	System cable, RJ45 IP 20, RJ45 IP 20, <20 m: Cat.6A / >20 m Class EA (ISO/IEC 11801 2010), PUR, 15 m
Order No.	<a href="#">8909650150</a>
Type	IE-C6ES8UG0150A40A40-E
GTIN (EAN)	4050118473629
Qty.	1 pc(s).

## IE-C6ES8UG0150A40A40-E

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Length	15 m	Length (inches)	590.551 inch
Net weight	672 g		

## Temperatures

Storage temperature	-40 °C...80 °C	Operating temperature	-40 °C...80 °C
Installation temperature	-15 °C...60 °C		

## Cable specific standards

Corrosiveness of fumes	to IEC 60754-2	Generic communication cable facilities	EN 50173-1:2007, ISO / IEC 11801:2002
Standard, assembly	UL-Style 20963 (80°C/30V)		

## Standards

Corrosiveness of fumes	to IEC 60754-2	Generic communication cable facilities	EN 50173-1:2007, ISO / IEC 11801:2002
Standard, assembly	UL-Style 20963 (80°C/30V)		

## Cable structure

Arrangement of wire cores		Colour sequence or wires - wire pairs	white - blue, white - orange, white - green, white - brown
	Twisted pair		
Complete shielding	Shielding braid made from copper wiring	Cross-section	4*2*AWG 26/7 - 4*2*0.128 mm <sup>2</sup>
Insulation	PE	Insulation cross-section	1.03 mm
Material sheath	PUR	Sheath diameter, max.	6.5 mm
Sheath diameter, min.	6.1 mm	Sheathing colour	green (RAL 6018)
Shielding	S/FTP	Shielding braid thickness	0.1 mm
Standard designations	S/FTP, LIO2YSC11Y 4x2x0.15 PIMF FRNC GN	Strands	7
Wire material	Stranded tin-plated copper wire	Wire pair shielding	Aluminium foil

## Electrical properties of cable

Capacity at 1 kHz		Category	<20 m: Cat.6A / >20 m Class EA (ISO/IEC 11801 2010)
	45 nF/km		
Characteristic impedance	100 ± 5 Ω at 100MHz	Delay skew	3 ns/100m
Loop resistance	290 Ω/km	Signal propagation time	4.5 ns/m
Test voltage: wire-wire-shield		Transfer impedance	15 mΩ/m at 1 MHz, 10 mΩ/m at 10 MHz, 30 mΩ/m at 30 MHz
	700 V AC		
Transmission rate	10 Gbit/s		

## IE-C6ES8UG0150A40A40-E

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Mechanical and material properties of cable

Abrasion resistance	very good	Corrosiveness of fumes	to IEC 60754-2
Halogen	halogen-free, according to IEC 60754-2	Min. bending radius, once only	5 x cable diameter
Min. bending radius, repetitive	10 x cable diameter	Pulling force	≤ 100 N
Resistance to oils	in accordance with IEC 60811-2-1	Resistance to spread of flame	in accordance with IEC 60332-1

## Plug

Plug left	RJ45, IP20, male contact, straight, plug, Plastic, shielded	Plug right	RJ45, IP20, male contact, straight, plug, Plastic, shielded
-----------	---	------------	---

## Plug, left

Plug left	RJ45, IP20, male contact, straight, plug, Plastic, shielded
-----------	---

## Plug, right

Plug right	RJ45, IP20, male contact, straight, plug, Plastic, shielded
------------	---

## Classifications

ETIM 6.0	EC002599	ETIM 7.0	EC002599
ETIM 8.0	EC002599	ETIM 9.0	EC002599
ECLASS 9.0	27-06-03-08	ECLASS 9.1	27-06-03-08
ECLASS 10.0	27-06-03-08	ECLASS 11.0	27-06-03-08
ECLASS 12.0	27-06-03-08	ECLASS 13.0	27-06-03-08

## Environmental Product Compliance

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

## Approvals

Approvals



ROHS	Conform
------	---------

## Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
User Documentation	<a href="#">MAN IE GUIDE DE</a> <a href="#">MAN IE GUIDE EN</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	<a href="#">FL FIELDWIRING EN</a> <a href="#">PI PROFINET CABLING EN</a>

Creation date July 15, 2024 5:03:01 PM CEST

Catalogue status 13.07.2024 / We reserve the right to make technical changes.

IE-C6ES8UG0150A40A40-E

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany  
  
[www.weidmueller.com](http://www.weidmueller.com)

Drawings

Wiring

RJ45	1	white (orange)	1	RJ45
	2	orange	2	
	3	white (green)	3	
	4	blue	4	
	5	white (blue)	5	
	6	green	6	
	7	white (brown)	7	
	8	brown	8	