

**H0,75/19DS ZH GR****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

- Polypropylene conical cable entry funnel
  - Heat-resistant up to 105°C
- For conductors from 0.5 – 10.0 mm<sup>2</sup> (AWG 20-7)  
Material: E-Cu, tin galvanised  
Dimensional tolerance acc. to DIN 46228 sect. 4

**General ordering data**

Version	Wire-end ferrule, Twin wire-end ferrule, 21 mm, 12 mm, grey
Order No.	<a href="#">9202830000</a>
Type	H0,75/19DS ZH GR
GTIN (EAN)	4032248515776
Qty.	500 pc(s).
Packaging	loose

## H0,75/19DS ZH GR

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Net weight	0.156 g
------------	---------

## Technical data

Description of article	Twin wire end ferrule, grey	Version	Twin wire-end ferrule
------------------------	-----------------------------	---------	-----------------------

## Wire-end ferrules

Collar height (A)	5.5 mm	Collar width (B)	3 mm
Colour code	DIN	Conductor cross-section	0.75 mm <sup>2</sup>
Contact surface diameter (D1)	1.7 mm	Contact surface length (L2)	12 mm
L1 in mm	18 mm	Metal sleeve thickness (S1)	0.15 mm
Plastic collar thickness (S2)	0.3 mm	Stripping length	21 mm
Wire connection cross section AWG, max.	AWG 18		

## Classifications

ETIM 6.0	EC000005	ETIM 7.0	EC000005
ETIM 8.0	EC000005	ETIM 9.0	EC000005
ECLASS 9.0	27-40-02-01	ECLASS 9.1	27-40-02-01
ECLASS 10.0	27-40-02-01	ECLASS 11.0	27-40-02-01
ECLASS 12.0	27-40-02-01	ECLASS 13.0	27-40-02-01

## Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (UR)	E354986

## Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
User Documentation	<a href="#">Technical information - EN</a> <a href="#">Technical information - DE</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

**H0,75/19DS ZH GR****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Drawings****Drawing**