

TS 35X7.5 2M/ST/SZ**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

Similar to illustration

Steel DIN rails are the most widespread on the market. Among metal DIN rails, they have the lowest shortcircuit protection, similar to stainless steel.

General ordering data

Version	Terminal rail, without slot, Accessories, 35 x 7.5 x 2000 mm, Steel, galvanic zinc plated and passivated
Order No.	9300090000
Type	TS 35X7.5 2M/ST/SZ
GTIN (EAN)	4032248387564
Qty.	2 m

TS 35X7.5 2M/ST/SZ

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	7.5 mm	Depth (inches)	0.295 inch
Height	35 mm	Height (inches)	1.378 inch
Width	2,000 mm	Width (inches)	78.74 inch
Net weight	327.5 g		

Mounting rail

Installation advice		Direct mounting	
Length of the terminal rail	nominal	2,000 mm	
	max.	2,000 mm	
	min.	0 mm	
Material	Steel		
Pre-punched mounting rail	No		
Short circuit strength corresponds to E-Cu wire	16 mm ²		
Short-time withstand current per second 1.92 kA according to IEC 60947-7-2			
Slit gap			
Slit length			
Slit width			
Standards	DIN EN 60715		
Surface finish	galvanic zinc plated and passivated		
Thickness	1 mm		

Classifications

ETIM 6.0	EC001285	ETIM 7.0	EC001285
ETIM 8.0	EC001285	ETIM 9.0	EC001285
ECLASS 9.0	27-40-06-02	ECLASS 9.1	27-40-06-02
ECLASS 10.0	27-40-06-02	ECLASS 11.0	27-40-06-02
ECLASS 12.0	27-40-06-02	ECLASS 13.0	27-40-06-02

Important note

Product information	Din rails with Sendzimier treatment have limited corrosion resistance on the outer and cut edges
---------------------	--

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
User Documentation	StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format

TS 35X7.5 2M/ST/SZ

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings

Product image

