

H1,0/15S ZH GE SV**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

- Polypropylene conical cable entry funnel
 - Heat-resistant up to 105°C
- For conductors from 0.5 – 10.0 mm² (AWG 20-7)
Material: E-Cu, tin galvanised
Dimensional tolerance acc. to DIN 46228 sect. 4

General ordering data

Version	Wire-end ferrule, Twin wire-end ferrule, 12 mm, 8 mm, yellow
Order No.	9018650000
Type	H1,0/15S ZH GE SV
GTIN (EAN)	4032248011407
Qty.	500 pc(s).
Packaging	Multipack bag

H1,0/15S ZH GE SV**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Net weight	0.178 g
------------	---------

Technical data

Description of article	Twin wire end ferrule, yellow	Version	Twin wire-end ferrule
------------------------	-------------------------------	---------	-----------------------

Wire-end ferrules

Collar height (A)	5.8 mm	Collar width (B)	3.2 mm
Colour code	Weidmueller	Conductor cross-section	1 mm ²
Contact surface diameter (D1)	2.2 mm	Contact surface length (L2)	8 mm
L1 in mm	15 mm	Metal sleeve thickness (S1)	0.15 mm
Plastic collar thickness (S2)	0.3 mm	Stripping length	12 mm
Wire connection cross section AWG, max.	AWG 17		

Classifications

ETIM 6.0	EC000005	ETIM 7.0	EC000005
ETIM 8.0	EC000005	ETIM 9.0	EC000005
ECLASS 9.0	27-40-02-01	ECLASS 9.1	27-40-02-01
ECLASS 10.0	27-40-02-01	ECLASS 11.0	27-40-02-01
ECLASS 12.0	27-40-02-01	ECLASS 13.0	27-40-02-01

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
User Documentation	Technical information - EN Technical information - DE
Catalogues	Catalogues in PDF-format
Brochures	

H1,0/15S ZH GE SV**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Drawings****Drawing**