

H1,5/14S R SV**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

- Polypropylene conical cable entry funnel
 - Heat-resistant up to 105°C
- For conductors from 0.5 – 10.0 mm² (AWG 20-7)
Material: E-Cu, tin galvanised
Dimensional tolerance acc. to DIN 46228 sect. 4

General ordering data

| | |
|------------|--|
| Version | Wire-end ferrule, Standard, 10 mm, 8 mm, red |
| Order No. | 9025720000 |
| Type | H1,5/14S R SV |
| GTIN (EAN) | 4008190072681 |
| Qty. | 500 pc(s). |
| Packaging | Multipack bag |

H1,5/14S R SV**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

| | |
|------------|---------|
| Net weight | 0.138 g |
|------------|---------|

Technical data

| Description of article | Wire end ferrule with plastic collar, special size, red | Version | Standard |
|------------------------|---|---------|----------|
|------------------------|---|---------|----------|

Wire-end ferrules

| | | | |
|-----------------------------|---------------------|---|-------------|
| Collar diameter (D2) | 4 mm | Colour code | Weidmueller |
| Conductor cross-section | 1.5 mm ² | Contact surface diameter (D1) | 1.7 mm |
| Contact surface length (L2) | 8 mm | L1 in mm | 14 mm |
| Metal sleeve thickness (S1) | 0.15 mm | Plastic collar thickness (S2) | 0.25 mm |
| Stripping length | 10 mm | Wire connection cross section AWG, max. | AWG 16 |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000005 | ETIM 7.0 | EC000005 |
| ETIM 8.0 | EC000005 | ETIM 9.0 | EC000005 |
| ECLASS 9.0 | 27-40-02-01 | ECLASS 9.1 | 27-40-02-01 |
| ECLASS 10.0 | 27-40-02-01 | ECLASS 11.0 | 27-40-02-01 |
| ECLASS 12.0 | 27-40-02-01 | ECLASS 13.0 | 27-40-02-01 |

Approvals

Approvals



| | |
|-------------------------|------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate no. (cULus) | E499744 |

Downloads

| | |
|--------------------|--|
| Engineering Data | CAD data – STEP |
| User Documentation | Technical information - EN Technical information - DE |
| Catalogues | Catalogues in PDF-format |
| Brochures | |

H1,5/14S R SV**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Drawings****Drawing**