

SAIL-VSB-30U**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Weidmüller can supply valve plugs as connecting lines with M12 plugs and one end without connector. The status of the valve plug is shown by an LED. Every valve plug is fitted with a protective circuit. The Weidmüller range includes valve plugs of type A, B and C to DIN and industry standards. In the plugged condition they achieve IP 67 class of protection. The outlet direction is also a decisive factor: Weidmüller can also supply 0° versions, i.e. the cable outlet direction is located at the PE contact.

General ordering data

| | |
|------------|--|
| Version | Valve plug, One end without connector - valve plug |
| Order No. | 9457933000 |
| Type | SAIL-VSB-30U |
| GTIN (EAN) | 4050118222746 |
| Qty. | 1 pc(s). |

SAIL-VSB-30U

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | |
|------------|-------|
| Net weight | 924 g |
|------------|-------|

Technical specifications for cable

| | | | |
|-------------------------------|---------------------|----------------------------------|---------------------------|
| Acceleration | 5 m/s ² | Bending cycles | 2 Mio |
| Bending radius, min., moving | 10 x cable diameter | Bending radius, min., stationary | 5 x cable diameter |
| Cable length | 30 m | Colour coding | brown, blue, Green/yellow |
| Core cross-section | 0.5 mm ² | Halogen | No |
| Insulation | PP | Number of poles | 3 |
| Outside diameter | 4.6 mm ± 0.2 mm | Resistant to welding beads | No |
| Sheath material | PUR | Sheathing colour | black |
| Shielded | No | Speed | 200 m/s |
| Suitable for cable carriers | Yes | Temperature range, moving | -25...80 °C |
| Temperature range, stationary | -50...80 °C | Torsion resistance | 0 °/m |
| Welding spark resistance | No | | |

General technical data

| | | | |
|---|--|------------------------------|-----------------------------|
| All valve plugs are fitted with protective circuits | Zener diode | Coding | Industrial design B (11 mm) |
| Contact surface | tinned | LED | Yes |
| Protection degree | IP67, when screwed in | Rated current | 4 A |
| Rated voltage | 24 V | Temperature range of housing | -25...+80 °C |
| Version | One end without connector - valve plug | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001855 | ETIM 7.0 | EC001855 |
| ETIM 8.0 | EC001855 | ETIM 9.0 | EC001855 |
| ECLASS 9.0 | 27-06-03-12 | ECLASS 9.1 | 27-06-03-11 |
| ECLASS 10.0 | 27-06-03-12 | ECLASS 11.0 | 27-06-03-12 |
| ECLASS 12.0 | 27-06-03-12 | ECLASS 13.0 | 27-06-03-12 |

Approvals

Approvals



| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads




| | |
|------------------|--|
| Engineering Data | CAD data – STEP |
| Catalogues | Catalogues in PDF-format |
| Brochures | FL FIELDWIRING EN |

SAIL-VSB-30U**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Drawings****Dimensioned drawing****Pole scheme****Wiring diagram****24V_{AC/DC}_4A**