


WTL 6 SL/EN**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image****Current and voltage transformer wiring**

Our test disconnect terminal blocks featuring spring and screw connection technology allow you to create all the important converter circuits for measuring current, voltage and power in a safe and sophisticated way.

General ordering data

| | |
|------------|---|
| Version | Test-disconnect terminal, Screw connection, 6 mm ² , 630 V, 41 A, without, Cross-disconnect: without, Integral test socket: No, TS 32, TS 35, dark beige |
| Order No. | 9538080000 |
| Type | WTL 6 SL/EN |
| GTIN (EAN) | 4008190574963 |
| Qty. | 50 pc(s). |

WTL 6 SL/EN

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|--------------------------|------------|----------------|------------|
| Depth | 49.5 mm | Depth (inches) | 1.949 inch |
| Depth including DIN rail | 51.5 mm | Height | 82.7 mm |
| Height (inches) | 3.256 inch | Width | 7.9 mm |
| Width (inches) | 0.311 inch | Net weight | 30.2 g |

Temperatures

| | | | |
|----------------------------------|----------------|----------------------------------|--------|
| Storage temperature | -25 °C...55 °C | Continuous operating temp., min. | -50 °C |
| Continuous operating temp., max. | 120 °C | | |

Material data

| | | | |
|---------------------------|-------|--------|------------|
| Material | Wemid | Colour | dark beige |
| UL 94 flammability rating | V-0 | | |

System specifications

| | | | |
|-------------------------------------|---|-------------------------------|-----|
| Version | Screw connection, Special terminal longitudinal isolator, with spring-loaded cable clamp, With sockets, One end without connector | End cover plate required | Yes |
| Number of potentials | 1 | Number of levels | 1 |
| Number of clamping points per level | 2 | Number of potentials per tier | 1 |
| Levels cross-connected internally | No | PE connection | No |
| Rail | TS 32, TS 35 | N-function | No |
| PE function | No | PEN function | No |

Additional technical data

| | | | |
|--------------------------|---------|------------|-------|
| Explosion-tested version | No | Open sides | right |
| Type of mounting | Snap-on | | |

Conductors for clamping (rated connection)

| | | | |
|--|---------------------|--|---------------------|
| Blade size | 0.8 x 4.0 mm | Clamping range, max. | 6 mm ² |
| Clamping range, min. | 0.5 mm ² | Clamping screw | M 3.5 |
| Connection cross-section, stranded, max. | 6 mm ² | Connection direction | on side |
| Gauge to IEC 60947-1 | A5 | Number of connections | 2 |
| Stripping length | 16 mm | Tightening torque, max. | 1.6 Nm |
| Tightening torque, min. | 0.8 Nm | Type of connection | Screw connection |
| Wire connection cross section, finely stranded, max. | 6 mm ² | Wire connection cross section, finely stranded, min. | 0.5 mm ² |
| Wire connection cross-section, solid core, max. | 6 mm ² | Wire connection cross-section, solid core, min. | 0.5 mm ² |

Dimensions

| | | | |
|--------------|---------|--------------|-------|
| TS 32 offset | 41.5 mm | TS 35 offset | 32 mm |
|--------------|---------|--------------|-------|

WTL 6 SL/EN

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Disconnect terminals

| | | | |
|-----------------------------|---------|-----------------------------|--------|
| Cross-disconnect | without | Integral test socket | No |
| Slitting | without | Torque max. screw separator | 0.7 Nm |
| Torque min. screw separator | 0.5 Nm | | |

General

| | | | |
|------|--------------|-----------|---------------|
| Rail | TS 32, TS 35 | Standards | IEC 60947-7-1 |
|------|--------------|-----------|---------------|

Rating data

| | | | |
|--|-------------------|---------------------------------|---------------|
| Rated cross-section | 6 mm ² | Rated voltage | 630 V |
| Rated DC voltage | 630 V | Rated current | 41 A |
| Current at maximum wires | 57 A | Standards | IEC 60947-7-1 |
| Volume resistance according to IEC 60947-7-x | 0.78 mΩ | Rated impulse withstand voltage | 6 kV |
| Power loss in accordance with IEC 60947-7-x | 1.31 W | Pollution severity | 2 |
| Surge voltage category | III | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000902 | ETIM 7.0 | EC000902 |
| ETIM 8.0 | EC000902 | ETIM 9.0 | EC000902 |
| ECLASS 9.0 | 27-14-11-26 | ECLASS 9.1 | 27-14-11-26 |
| ECLASS 10.0 | 27-14-11-26 | ECLASS 11.0 | 27-14-11-26 |
| ECLASS 12.0 | 27-14-11-26 | ECLASS 13.0 | 27-25-01-09 |

Environmental Product Compliance

| | |
|------------|--------------------------------------|
| REACH SVHC | Lead 7439-92-1 |
| SCIP | 0eb7d846-d0a1-43e5-93a4-d7c6856c4cda |

Approvals

Approvals



| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|---|--|
| Approval/Certificate/Document of Conformity | CE Declaration of Conformity UKCA declaration of conformity Confirmation of Standards EN 45545-2_2020-10 |
| Engineering Data | CAD data – STEP |
| Engineering Data | Zuken E3.S |
| User Documentation | StorageConditionsTerminalBlocks |
| Catalogues | Catalogues in PDF-format |

WTL 6 SL/EN

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

WTL 6 SL/EN

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

W-Series



A partition plate is used for the optical separation of circuits or used for electrical isolation from neighbouring cross-connectors. In contrast to the end plate, the contour can be larger than the adjacent terminal blocks. However, it should not be smaller, as otherwise the required clearance and creepage distances within the application can no longer be maintained.

General ordering data

| Type | WTW EN | Version |
|------------|----------------------------|---|
| Order No. | 1058800000 | Partition plate (terminal), Intermediate plate, 86 mm x 62 mm, dark |
| GTIN (EAN) | 4008190140175 | beige |
| Qty. | 20 pc(s). | |

Fixing screws



Fixing screws fix the short current bridge within the application. If the short current bridge is slid between two adjacent terminal blocks into the short circuit position, it can be fixed by means of a fastening screw. This ensures a permanent connection or short circuit.

General ordering data

| Type | BS 25 IH/GE SAKT1 | Version |
|------------|----------------------------|---|
| Order No. | 0335700000 | Mounting screw (Terminal), Depth: 28.7 mm |
| GTIN (EAN) | 4008190189235 | |
| Qty. | 50 pc(s). | |
| Type | BS 25 IH/BL SAKT1 | Version |
| Order No. | 0335400000 | Mounting screw (Terminal), Depth: 28.7 mm |
| GTIN (EAN) | 4008190086879 | |
| Qty. | 50 pc(s). | |
| Type | BS 25 IH/GN SAKT1 | Version |
| Order No. | 0335600000 | Mounting screw (Terminal), Depth: 28.7 mm |
| GTIN (EAN) | 4008190113490 | |
| Qty. | 50 pc(s). | |
| Type | BS 25 O.IH SAKT1 | Version |
| Order No. | 0334700000 | Mounting screw (Terminal), Depth: 28.7 mm |
| GTIN (EAN) | 4008190118839 | |
| Qty. | 50 pc(s). | |
| Type | BS 25 IH/SW SAKT1 | Version |
| Order No. | 0335200000 | Mounting screw (Terminal), Depth: 28.7 mm |
| GTIN (EAN) | 4008190114039 | |
| Qty. | 50 pc(s). | |

WTL 6 SL/EN

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26


D-32758 Detmold

Germany

www.weidmueller.com

Accessories

| | | |
|------------|----------------------------|---|
| Type | BS 25 IH/VI SAKT1 | Version |
| Order No. | 0335800000 | Mounting screw (Terminal), Depth: 28.7 mm |
| GTIN (EAN) | 4008190039196 | |
| Qty. | 50 pc(s). | |
| Type | BS 25 IH/GR SAKT1 | Version |
| Order No. | 0335300000 | Mounting screw (Terminal), Depth: 28.7 mm |
| GTIN (EAN) | 4008190136864 | |
| Qty. | 50 pc(s). | |
| Type | BS 25 IH/RT SAKT1 | Version |
| Order No. | 0335500000 | Mounting screw (Terminal), Depth: 28.7 mm |
| GTIN (EAN) | 4008190118877 | |
| Qty. | 50 pc(s). | |

10 mm²


10
mm²

Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | WQV 10/10 | Version |
| Order No. | 1052460000 | Cross-connector (terminal), when screwed in, Number of poles: 10, |
| GTIN (EAN) | 4008190152130 | Pitch in mm (P): 9.90, Insulated: Yes, 63 A, yellow |
| Qty. | 20 pc(s). | |
| Type | WQV 10/3 | Version |
| Order No. | 1054960000 | Cross-connector (terminal), when screwed in, Number of poles: 3, |
| GTIN (EAN) | 4008190079079 | Pitch in mm (P): 9.90, Insulated: Yes, 63 A, yellow |
| Qty. | 50 pc(s). | |
| Type | WQV 10/6 | Version |
| Order No. | 2226500000 | Cross-connector (terminal), when screwed in, Number of poles: 6, |
| GTIN (EAN) | 4032248793761 | Pitch in mm (P): 9.90, Insulated: Yes, 63 A, yellow |
| Qty. | 20 pc(s). | |
| Type | WQV 10/2 | Version |
| Order No. | 1052560000 | Cross-connector (terminal), when screwed in, Number of poles: 2, |
| GTIN (EAN) | 4008190154943 | Pitch in mm (P): 9.90, Insulated: Yes, 76 A, yellow |
| Qty. | 50 pc(s). | |
| Type | WQV 10/4 | Version |
| Order No. | 1055060000 | Cross-connector (terminal), when screwed in, Number of poles: 4, |
| GTIN (EAN) | 4008190188245 | Pitch in mm (P): 9.90, Insulated: Yes, 63 A, yellow |
| Qty. | 50 pc(s). | |
| Type | WQV 10/5 | Version |
| Order No. | 2091130000 | Cross-connector (terminal), when screwed in, Number of poles: 5, |
| GTIN (EAN) | 4008190215903 | Pitch in mm (P): 9.90, Insulated: Yes, 63 A, yellow |
| Qty. | 20 pc(s). | |

WTL 6 SL/EN

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Connection sleeves



General ordering data

| | | |
|------------|----------------------------|--|
| Type | VH 19/6.3/4.3 | Version |
| Order No. | 0318000000 | Connecting sleeve (terminal), Height: 6 mm, Width: 6 mm, Depth: 19 |
| GTIN (EAN) | 4008190059460 | mm, Cu Zn |
| Qty. | 50 pc(s). | |

Shorting elements



The short current bridges are inserted into two instrument transformer wiring terminal blocks. By using the short-circuit bridge, the desired short-circuit could be realized within the application for maintenance work.

General ordering data

| | | |
|------------|----------------------------|--|
| Type | QVS 2/4 SAKT4 | Version |
| Order No. | 1319260000 | Cross-connector (terminal), when screwed in, Number of poles: 2, |
| GTIN (EAN) | 4008190136512 | Pitch in mm (P): 12.00, Insulated: Yes, 32 A, orange |
| Qty. | 20 pc(s). | |

WTL 6 SL/EN

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Testsockets



Test adapters and test plugs are used for the electrical connection between terminal blocks and the test equipment. In this way, an electrical contact can be established in the wired state and measurements can be done easily.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | GWHUE M3 WTL6 | Version |
| Order No. | 1255010000 | Connecting sleeve (terminal), Height: 6 mm, Width: 6 mm, Depth: |
| GTIN (EAN) | 4050118075892 | 13.3 mm, Copper - zinc |
| Qty. | 50 pc(s). | |

W-Series



Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

General ordering data

| | | |
|------------|----------------------------|--|
| Type | WEW 35/2 | Version |
| Order No. | 1061200000 | End bracket, Wemid, dark beige, Rail: TS 35, when screwed in |
| GTIN (EAN) | 4008190030230 | |
| Qty. | 50 pc(s). | |

WTL 6 SL/EN

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Switch lock



The switch lock can be easily inserted into the terminal from above. The switch lock prevents unauthorised opening or closing of circuits as it blocks the disconnect lever in its respective position.

General ordering data

| | | |
|------------|----------------------------|-----------------------------------|
| Type | SSP 3 SAKT1 | Version |
| Order No. | 0531760000 | Lockout device (terminal), orange |
| GTIN (EAN) | 4008190130787 | |
| Qty. | 100 pc(s). | |

Blank



WS markers are the perfect match for the W-series connectors. Thanks to their system compatibility, the WS tags can also be used with the I-series and the Z-series. The large marking surfaces do not only permit long character strings but also multi-line text. WS markers are ideal for labels with long, customised character strings. Thanks to the proven MultiCard format, printing with PrintJet CONNECT oder/or Plotter is possible.

- Can be fitted in strips or individually
- Markers in proven MultiCard format

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | WS 12/6.5 MC NE WS | Version |
| Order No. | 1609920000 | WS, Terminal marker, 12 x 6.5 mm, Pitch in mm (P): 6.50 |
| GTIN (EAN) | 4008190203511 | Weidmueller, Allen-Bradley, white |
| Qty. | 540 pc(s). | |

WTL 6 SL/EN

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

End plate



Current and voltage transformer wiring

Our test disconnect terminal blocks featuring spring and screw connection technology allow you to create all the important converter circuits for measuring current, voltage and power in a safe and sophisticated way.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | WAP WTL6 SL 4-6 | Version |
| Order No. | 1238880000 | End plate (terminals), 82.2 mm x 1.5 mm, dark beige |
| GTIN (EAN) | 4050118045680 | |
| Qty. | 20 pc(s). | |
| Type | WAP WTL6 SL | Version |
| Order No. | 9538110000 | End plate (terminals), 82.2 mm x 1.5 mm, dark beige |
| GTIN (EAN) | 4008190574994 | |
| Qty. | 20 pc(s). | |

6 mm²

Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | WQV 6/7 | Version |
| Order No. | 1062680000 | Cross-connector (terminal), when screwed in, Number of poles: 7, |
| GTIN (EAN) | 4008190261788 | Pitch in mm (P): 8.00, Insulated: Yes, 57 A, yellow |
| Qty. | 50 pc(s). | |
| Type | WQV 6/3 | Version |
| Order No. | 1054760000 | Cross-connector (terminal), when screwed in, Number of poles: 3, |
| GTIN (EAN) | 4008190174163 | Pitch in mm (P): 8.00, Insulated: Yes, 57 A, yellow |
| Qty. | 50 pc(s). | |
| Type | WQV 6/6 | Version |
| Order No. | 1062670000 | Cross-connector (terminal), when screwed in, Number of poles: 6, |
| GTIN (EAN) | 4008190261771 | Pitch in mm (P): 8.00, Insulated: Yes, 57 A, yellow |
| Qty. | 50 pc(s). | |
| Type | WQV 6/10 | Version |
| Order No. | 1052260000 | Cross-connector (terminal), when screwed in, Number of poles: 10, |
| GTIN (EAN) | 4008190153977 | Pitch in mm (P): 8.00, Insulated: Yes, 57 A, yellow |
| Qty. | 20 pc(s). | |

WTL 6 SL/EN

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold


Germany

www.weidmueller.com

Accessories

| | | |
|------------|----------------------------|--|
| Type | WQV 6/5 | Version |
| Order No. | 1062660000 | Cross-connector (terminal), when screwed in, Number of poles: 5, |
| GTIN (EAN) | 4008190176914 | Pitch in mm (P): 8.00, Insulated: Yes, 57 A, yellow |
| Qty. | 50 pc(s). | |
| Type | WQV 6/2 | Version |
| Order No. | 1052360000 | Cross-connector (terminal), when screwed in, Number of poles: 2, |
| GTIN (EAN) | 4008190075866 | Pitch in mm (P): 8.00, Insulated: Yes, 57 A, yellow |
| Qty. | 50 pc(s). | |
| Type | WQV 6/4 | Version |
| Order No. | 1054860000 | Cross-connector (terminal), when screwed in, Number of poles: 4, |
| GTIN (EAN) | 4008190180799 | Pitch in mm (P): 8.00, Insulated: Yes, 57 A, yellow |
| Qty. | 50 pc(s). | |

Hook-type cable lugs



The use of insulated connectors guarantees users a permanent and consistent quality for their electrical connections.

In addition, they bring advantages during installation.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | HBT 2,5 - 4,6 BL | Version |
| Order No. | 1233330000 | cable lug, terminal end, Insulated cable connector, 1.5 mm² - 2.5 |
| GTIN (EAN) | 4050118016901 | mm², blue |
| Qty. | 100 pc(s). | |
| Type | HBT 6,0 - 4,6 GE | Version |
| Order No. | 1216230000 | cable lug, terminal end, Insulated cable connector, 4 mm² - 6 |
| GTIN (EAN) | 4050118000337 | mm², yellow |
| Qty. | 100 pc(s). | |
| Type | HBT 6,0 - 3,0 GE | Version |
| Order No. | 1312470000 | cable lug, terminal end, Insulated cable connector, 4 mm² - 6 |
| GTIN (EAN) | 4050118114980 | mm², yellow |
| Qty. | 100 pc(s). | |
| Type | HBT 1,5 - 3,0 RT | Version |
| Order No. | 1312440000 | cable lug, terminal end, Insulated cable connector, 0.5 mm² - 1.5 |
| GTIN (EAN) | 4050118115055 | mm², red |
| Qty. | 100 pc(s). | |
| Type | HBT 2,5 - 3,0 BL | Version |
| Order No. | 1312450000 | cable lug, terminal end, Insulated cable connector, 1.5 mm² - 2.5 |
| GTIN (EAN) | 4050118115130 | mm², blue |
| Qty. | 100 pc(s). | |
| Type | HBT 1,5 - 4,6 RT | Version |
| Order No. | 1233340000 | cable lug, terminal end, Insulated cable connector, 0.5 mm² - 1.5 |
| GTIN (EAN) | 4050118210972 | mm², red |
| Qty. | 100 pc(s). | |

WTL 6 SL/EN

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Test sockets



The test socket is used to connect test devices with a standard 4.0 plug. Depending on the potential within the application, different colors of the test sockets can be selected for quick and easy maintenance work.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | STB 21.6/IH/BL WTL6/3 | Version |
| Order No. | 1071080000 | Socket (terminal), Plug-in depth: 11.1 mm, Depth: 26.6 mm |
| GTIN (EAN) | 4008190043957 | |
| Qty. | 50 pc(s). | |
| Type | STB 21.6/45 GE | Version |
| Order No. | 1936240000 | Socket (terminal), Plug-in depth: 11.1 mm, Depth: 45 mm |
| GTIN (EAN) | 4032248605972 | |
| Qty. | 50 pc(s). | |
| Type | STB 36.8/IH/BL WTL6/1 | Version |
| Order No. | 1847790000 | Socket (terminal), Plug-in depth: 11.1 mm, Depth: 39.8 mm |
| GTIN (EAN) | 4032248379149 | |
| Qty. | 50 pc(s). | |
| Type | STB 21.6/IH/GN WTL6/3 | Version |
| Order No. | 1071020000 | Socket (terminal), Plug-in depth: 11.1 mm, Depth: 26.6 mm |
| GTIN (EAN) | 4008190259228 | |
| Qty. | 50 pc(s). | |
| Type | STB 21.6/IH/WS WTL6/3 | Version |
| Order No. | 1312520000 | Socket (terminal), Plug-in depth: 11.1 mm |
| GTIN (EAN) | 4050118121704 | |
| Qty. | 50 pc(s). | |
| Type | STB 21.6/45 GR | Version |
| Order No. | 1936280000 | Socket (terminal), Plug-in depth: 11.1 mm, Depth: 45 mm |
| GTIN (EAN) | 4032248606016 | |
| Qty. | 50 pc(s). | |
| Type | STB 21.6/45 BL | Version |
| Order No. | 1936290000 | Socket (terminal), Plug-in depth: 11.1 mm, Depth: 45 mm |
| GTIN (EAN) | 4032248606023 | |
| Qty. | 50 pc(s). | |
| Type | STB 21.6/IH/GE WTL6/3 | Version |
| Order No. | 1071010000 | Socket (terminal), Plug-in depth: 11.1 mm, Depth: 26.6 mm |
| GTIN (EAN) | 4008190259211 | |
| Qty. | 50 pc(s). | |
| Type | STB 21.6/45 RT | Version |
| Order No. | 1936300000 | Socket (terminal), Plug-in depth: 11.1 mm, Depth: 45 mm |
| GTIN (EAN) | 4032248606030 | |
| Qty. | 50 pc(s). | |
| Type | STB 21.6/45 SW | Version |
| Order No. | 1936270000 | Socket (terminal), Plug-in depth: 11.1 mm, Depth: 45 mm |
| GTIN (EAN) | 4032248606009 | |
| Qty. | 50 pc(s). | |

Creation date July 3, 2024 5:49:23 AM CEST

Catalogue status 29.06.2024 / We reserve the right to make technical changes.

12

WTL 6 SL/EN

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

| | | |
|------------|----------------------------|---|
| Type | STB 36.8/IH/GN WTL6/1 | Version |
| Order No. | 1847770000 | Socket (terminal), Plug-in depth: 11.1 mm, Depth: 39.8 mm |
| GTIN (EAN) | 4032248379163 | |
| Qty. | 50 pc(s). | |
| Type | STB 21.6/IH/SW WTL6/3 | Version |
| Order No. | 1071040000 | Socket (terminal), Plug-in depth: 11.1 mm, Depth: 26.6 mm |
| GTIN (EAN) | 4008190859985 | |
| Qty. | 50 pc(s). | |
| Type | STB 21.6/45 DB | Version |
| Order No. | 1938790000 | Socket (terminal), Plug-in depth: 11.1 mm, Depth: 45 mm |
| GTIN (EAN) | 4032248612840 | |
| Qty. | 50 pc(s). | |
| Type | STB 36.8/IH/GE WTL6/1 | Version |
| Order No. | 1847760000 | Socket (terminal), Plug-in depth: 11.1 mm, Depth: 39.8 mm |
| GTIN (EAN) | 4032248379170 | |
| Qty. | 50 pc(s). | |
| Type | STB 21.6/45 VI | Version |
| Order No. | 1936260000 | Socket (terminal), Plug-in depth: 11.1 mm, Depth: 45 mm |
| GTIN (EAN) | 4032248605996 | |
| Qty. | 50 pc(s). | |
| Type | STB 21.6/IH/DB WTL6/3 | Version |
| Order No. | 1071000000 | Socket (terminal), Plug-in depth: 11.1 mm, Depth: 26.6 mm |
| GTIN (EAN) | 4008190259204 | |
| Qty. | 50 pc(s). | |
| Type | STB 36.8/IH/VI WTL6/1 | Version |
| Order No. | 1847780000 | Socket (terminal), Plug-in depth: 11.1 mm, Depth: 39.8 mm |
| GTIN (EAN) | 4032248379156 | |
| Qty. | 50 pc(s). | |
| Type | STB 21.6/IH/VI WTL6/3 | Version |
| Order No. | 1071030000 | Socket (terminal), Plug-in depth: 11.1 mm, Depth: 26.6 mm |
| GTIN (EAN) | 4008190259235 | |
| Qty. | 50 pc(s). | |
| Type | STB 21.6/45 GN | Version |
| Order No. | 1936250000 | Socket (terminal), Plug-in depth: 11.1 mm, Depth: 45 mm |
| GTIN (EAN) | 4032248605989 | |
| Qty. | 50 pc(s). | |
| Type | STB 36.8/IH/RT WTL6/1 | Version |
| Order No. | 1312540000 | Socket (terminal), Plug-in depth: 11.1 mm, Depth: 39.8 mm |
| GTIN (EAN) | 4050118180992 | |
| Qty. | 50 pc(s). | |
| Type | STB 36.8/IH/SW WTL6/1 | Version |
| Order No. | 1312550000 | Socket (terminal), Plug-in depth: 11.1 mm, Depth: 39.8 mm |
| GTIN (EAN) | 4050118181210 | |
| Qty. | 50 pc(s). | |

WTL 6 SL/EN

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

WS 12/6.5



WS/ DEK

MultiMark terminal markers use an innovative composite material made from two components. The hard base contour of the marker snaps securely into the connector. The elastic surface finish makes the marker easy to mount. This specially punched material enables the strips to be stretched to accommodate the slight variations in spacing that tend to add up, especially with long terminal blocks. Another advantage: the excellent printability of the surface material guarantees durable and wear-resistant labelling. A print resolution of 300 dpi also produces a very legible script.

Your benefits with MultiMark

- Firm hold and durable printing
- Continuous strips save installation time
- Easy mounting thanks to an innovative composite material
- Large label field for optimal legibility
- High flexibility thanks to manufacturer independence

General ordering data

| | | |
|------------|----------------------------|--|
| Type | WS 12/6.5 MM WS | Version |
| Order No. | 2619930000 | WS, Terminal marker, 12 x 6.5 mm, Weidmueller, white |
| GTIN (EAN) | 4050118626155 | |
| Qty. | 600 pc(s). | |

Marker holder



The marker holder offer the possibility of additional mounting of standard markers with a pitch of 5 or 5.1 mm. The angled holders can be optionally snapped together and could be mounted in all standard marking channels of the Klippon® Connect modular terminal blocks. Fitting marker types could be found under the respective accessories of the designation marking holder.

General ordering data

| | | |
|------------|----------------------------|----------------------------|
| Type | BZT 1 WS 10/5 | Version |
| Order No. | 1805490000 | Accessories, Marker holder |
| GTIN (EAN) | 4032248270231 | |
| Qty. | 100 pc(s). | |
| Type | BZT 1 ZA WS 10/5 | Version |
| Order No. | 1805520000 | Accessories, Marker holder |
| GTIN (EAN) | 4032248270248 | |
| Qty. | 100 pc(s). | |