

**FUSE WSFL 10X85 32A 1K5V GPV****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

gPV 10×85 cylindrical fuse cartridges are designed to provide compact, safe and economical protection of photovoltaic modules (field protection) with voltages up to 1,500 DC. They provide protection against both overload and short circuit (gPV class according to the requirements of IEC60269-6 and UL248-19 standards).

**Informations générales de commande**

Version	Photovoltaïque, Fusible, 1500 V, 10x85, gPV, 32 A
Référence	<a href="#">4000002612</a>
Type	FUSE WSFL 10X85 32A 1K5V GPV
GTIN (EAN)	8430243419659
Qté.	5 pièce(s)

**FUSE WSFL 10X85 32A 1K5V GPV****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Caractéristiques techniques****Dimensions et poids**

Hauteur	85 mm	Hauteur (pouces)	3,346 inch
Largeur	10,3 mm	Largeur (pouces)	0,406 inch
Poids net	5 g		

**Classifications**

ETIM 7.0	EC002704	ETIM 8.0	EC002704
ETIM 9.0	EC002704	ECLASS 11.0	27-14-20-02
ECLASS 12.0	27-14-20-02	ECLASS 13.0	27-14-20-02

**Élément fusible**

Conducteur fusible standard	IEC 60269-6	Courant	32 A
Tension nominale DC	1 500 V		

**Agréments**

ROHS	Conforme
------	----------

**Téléchargements**

Données techniques	<a href="#">CAD data – Advanced Datasheet</a>
Catalogue	<a href="#">Catalogues in PDF-format</a>