
EGT5 EG2/EN TASTER

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



The profiles of the switch and button components match those of the electronic components.
Switches and buttons facilitate commissioning, servicing, monitoring and repair of industrial installations.

General ordering data

Version	, Function component CO contact, off position in the middle, sensing on both sides, Screw connection
Order No.	0104260000
Type	EGT5 EG2/EN TASTER
GTIN (EAN)	4008190100247
Qty.	10 pc(s).

EGT5 EG2/EN TASTER

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Dimensions and weights

Height	50 mm	Height (inches)	1.969 inch
Width	18 mm	Width (inches)	0.709 inch
Length	58 mm	Length (inches)	2.283 inch
Net weight	41.9 g		

Temperatures

Storage temperature	-40 °C...100 °C	Operating temperature	-25 °C...85

Output

Rated switching voltage	250 V AC	AC switching capacity (resistive), max.	1500 VA @ 250 V
AC switching capacity, max.	1,500 VA	Switching capacity	250 V
DC switching capacity (resistive), max.	180 W @ 30 V	DC switching capacity, max.	180 W
Switching capacity	30 V		

General data

Rail	TS 32, TS 35	Colour	beige

Connection data

Wire connection method	Screw connection	Clamping range, rated connection	6 mm²
Clamping range, min.	0.5 mm²	Clamping range, max.	6 mm²
Wire connection cross section, finely stranded, max.	4 mm²		

Classifications

ETIM 6.0	EC002498	ETIM 7.0	EC002498
ETIM 8.0	EC002498	ETIM 9.0	EC002498
ECLASS 9.0	27-37-92-01	ECLASS 9.1	27-37-92-01
ECLASS 10.0	27-37-13-92	ECLASS 11.0	27-37-13-92
ECLASS 12.0	27-37-13-92	ECLASS 13.0	27-37-13-92

Approvals

Approvals	CE
ROHS	Conform

Downloads

Approval/Certificate/Document of Conformity	Application notes – EU Konformitätserklärung / EU Declaration of Conformity
Catalogues	Catalogues in PDF-format

EGT5 EG2/EN TASTER

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Steel



Steel DIN rails are the most widespread on the market. Among metal DIN rails, they have the lowest shortcircuit protection, similar to stainless steel.

General ordering data

Type	TS 32X15 2M/ST/ZN	Version
Order No.	0122800000	Rail, TS 32, without slot, Steel, galvanic zinc plated and passivated
GTIN (EAN)	4008190066307	
Qty.	2 m	

TS 32



Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

General ordering data

Type	EWK 2	Version
Order No.	0199360000	Accessories, End bracket
GTIN (EAN)	4008190023546	
Qty.	50 pc(s).	

EGT5 EG2/EN TASTER

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Steel



Steel DIN rails are the most widespread on the market. Among metal DIN rails, they have the lowest shortcircuit protection, similar to stainless steel.

General ordering data

Type	TS 35X7.5 2M/ST/ZN	Version
Order No.	0383400000	Rail, TS 35, TS 35 x 7.5, without slot, Steel, galvanic zinc plated and
GTIN (EAN)	4008190088026	passivated
Qty.	2 m	
Type	TS 35X15/2.3 2M/ST/ZN	Version
Order No.	0498000000	Rail, TS 35, TS 35 x 15, without slot, Steel, galvanic zinc plated and
GTIN (EAN)	4008190042493	passivated
Qty.	2 m	

SAK-Series



Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

General ordering data

Type	EW 35	Version
Order No.	0383560000	Accessories, End bracket
GTIN (EAN)	4008190181314	
Qty.	50 pc(s).	