


Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Product image







To feed through power, signal, and data is the classical requirement in electrical engineering and panel building. The insulating material, the connection system and the design of the terminal blocks are the differentiating features. A feed-through terminal block is suitable for joining and/or connecting one or more conductors. They could have one or more connection levels that are on the same potential or insulated against one another.

Version	SAK Series, Feed-through terminal, Double-tier terminal, Rated cross-section: 4 mm², Screw connection
Order No.	<u>0590060000</u>
Туре	DK 4Q/32
GTIN (EAN)	4008190147228
Qty.	25 pc(s).



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Technical data

-			
Dim	ensions	and	weights

Depth	59.5 mm	Depth (inches)	2.343 inch
Height	50 mm	Height (inches)	1.969 inch
Width	6 mm	Width (inches)	0.236 inch
Net weight	13.685 g		

Temperatures

Storage temperature	-25 °C55 °C	Operating temperature range	For operating temperature range see EC Design Test Certificate / IEC Ex-Certificate of Conformity
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	100 °C

Material data

Material	PA 66	Colour	beige / yellow
UL 94 flammability rating	V-2	<u> </u>	

Rating data IECEx/ATEX

Certificate No. (ATEX)	TUEV18ATEX8210U	Certificate No. (IECEX)	IECEXTUR18.0020U
Max. voltage (ATEX)	275 V	Current (ATEX)	28 A
Wire cross section max. (ATEX)	4 mm²	Max. voltage (IECEX)	275 V
Current (IECEX)	28 A	Wire cross section max. (IECEX)	4 mm²
Operating temperature range	For operating temperature range see EC Design Test Certificate / IEC Ex-Certifi- cate of Conformity	Marking EN 60079-7	Ex eb II C Gb
Ex 2014/34/EU label	II 2 G D		27.00 11.0 00

System specifications

Version	Screw connection, for scre- wable cross-connection, One end without connec-	End cover plate required	
	tor		Yes
Number of potentials	2	Number of levels	2
Number of clamping points per level	2	Number of potentials per tier	1
Levels cross-connected internally	No	PE connection	No
Rail	TS 32	N-function	No
PE function	No	PEN function	No

Additional technical data

Explosion-tested version	Yes	Number of similar terminals	1	
Open sides	right	Type of mounting	Clamped	

CSA rating data

Certificate No. (CSA)	12400-124	Current size C (CSA)	10 A
Voltage size C (CSA)	300 V	Wire cross section max. (CSA)	12 AWG
Wire cross section min. (CSA)	26 AWG		



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Technical data

Conductors for clamping (additional connection)

Conductor cross-section, flexible plus plastic collar DIN 46228/1, further con-

nection, max. 2.5 mm²

Conductors for clamping (rated connection)

Blade size	0.6 x 3.5 mm	Clamping range, max.	6 mm ²
Clamping range, min.	0.13 mm ²	Clamping screw	M 3
Connection cross-section, stranded,		Connection cross-section, stranded, mi	n.
max.	4 mm ²		0.5 mm ²
Connection direction	on side	Gauge to IEC 60947-1	A3
Number of connections	4	Stripping length	9 mm
Tightening torque, max.	0.1 Nm	Tightening torque, min.	0.5 Nm
Torque level with DMS electric screw-	·	Twin wire-end ferrules, max.	
driver	2		1.5 mm ²
Twin wire-end ferrules, min.	0.5 mm ²	Type of connection	Screw connection
Wire connection cross section AWG,		Wire connection cross section AWG,	
max.	AWG 12	min.	AWG 26
Wire connection cross section, finely		Wire connection cross section, finely	
stranded, max.	4 mm ²	stranded, min.	0.5 mm ²
Wire connection cross-section, finely stranded with wire-end ferrules DIN		Wire connection cross-section, fine- ly stranded with wire-end ferrules DIN	
46228/1, max.	2.5 mm ²	46228/1, min.	0.5 mm ²
Wire connection cross-section, fine- ly stranded with wire-end ferrules DIN		Wire connection cross-section, fine- ly stranded with wire-end ferrules DIN	
46228/4, max.	2.5 mm ²	46228/4, min.	0.5 mm ²
Wire connection cross-section, solid		Wire connection cross-section, solid	
core, max.	6 mm ²	core, min.	0.5 mm ²

General

Rail	TS 32	Standards	IEC 60947-7-1
Wire connection cross section AWG,		Wire connection cross section AWG,	
max.	AWG 12	min.	AWG 26

Rating data

Rated cross-section	4 mm ²	Rated voltage	500 V
Rated DC voltage	500 V	Rated current	32 A
Current at maximum wires	41 A	Standards	IEC 60947-7-1
Volume resistance according to IEC		Rated impulse withstand voltage	
60947-7-x	1 mΩ		6 kV
Power loss in accordance with IEC		Pollution severity	
60947-7-x	1.02 W		3

UL rating data

Certificate No. (UR)	E60693	Conductor size Factory wiring max. (UR)	12 AWG
Conductor size Factory wiring min. (UR)	26 AWG	Conductor size Field wiring max. (UR)	12 AWG
Conductor size Field wiring min. (UR)	22 AWG	Current size C (UR)	27 A
Voltage size C (UR)	300 V		



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Technical data

Classifications

ETIM 6.0	EC000897	ETIM 7.0	EC000897
ETIM 8.0	EC000897	ETIM 9.0	EC000897
ECLASS 9.0	27-14-11-20	ECLASS 9.1	27-14-11-20
ECLASS 10.0	27-14-11-20	ECLASS 11.0	27-14-11-20
ECLASS 12.0	27-14-11-20	ECLASS 13.0	27-25-01-02

Approvals

Approvals





ROHS	Conform
UL File Number Search	UL Website
Certificate No. (UR)	E60693

Downloads

Approval/Certificate/Document of Con-	Attestation Of Conformity
formity	UKCA Ex Attestation of Conformity
	ATEX Certificate
	IECEx Certificate
	CB Test Certificate
	<u>CB Certificate</u>
	CCC Ex Certificate
	UKCA Ex Certificate
	Declaration of Conformity
	UKCA declaration of conformity
Engineering Data	CAD data – STEP
Product Change Notification	PCN_DK4_20190405
User Documentation	NTI DK 4Q/32
	<u>StorageConditionsTerminalBlocks</u>
Catalogues	Catalogues in PDF-format



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories

Screws



Depending on the terminal block or also accessories, we offer different types of screws as additional items or also spare parts.

General ordering data

Туре	KISC M3X15/6 SAK2.5	Version
Order No.	0359000000	Clamping yoke, Mounting screw, Steel
GTIN (EAN)	4008190061548	
Qty.	100 pc(s).	
Туре	BFSC M2.5X18 PA/RT	Version
Order No.	0303300000	Accessories, Mounting screw, for cross-connection link
GTIN (EAN)	4008190040673	
Qty.	100 pc(s).	
Туре	BFSC M2.5X14 SAKD2.5N	Version
Order No.	0266800000	SAK Series, Mounting screw, for cross-connection link
GTIN (EAN)	4008190084899	
Qty.	100 pc(s).	

SAK-Series



End plates are fitted to the open side of the last modular terminal before the end bracket. The use of an end plate ensures the function of the modular terminal and the specified rated voltage. It guarantees protection against contact with live parts and makes the final terminal finger-proof.

Туре	AP DK4Q BL	Version
Order No.	<u>1397180000</u>	SAK Series, End plate, 1.5 mm, blue, Direct mounting
GTIN (EAN)	4008190171728	
Qty.	20 pc(s).	
Туре	AP DK4 BL	Version
Order No.	0359280000	SAK Series, End plate, 1.5 mm, blue, Direct mounting
GTIN (EAN)	4008190031213	
Qty.	20 pc(s).	
Туре	AP DK4Q	Version
Order No.	<u>1397160000</u>	SAK Series, End plate, 1.5 mm, beige, Direct mounting
GTIN (EAN)	4008190125899	
Qty.	20 pc(s).	



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories

Туре	AP DK4	Version
Order No.	0359260000	SAK Series, End plate, 1.5 mm, beige, Direct mounting
GTIN (EAN)	4008190012991	
Qty.	20 pc(s).	
Туре	AP DK4S	Version
Order No.	0631360000	SAK Series, End plate, 1.5 mm, beige, Direct mounting
GTIN (EAN)	4008190101329	
Qty.	20 pc(s).	
Туре	AP DK4/380 Q	Version
Order No.	0438560000	SAK Series, End plate, 1.5 mm, beige, Direct mounting
GTIN (EAN)	4008190133351	
Qty.	20 pc(s).	

Insulation profiles



Туре	ISPF QB75 BL	Version
Order No.	0526780000	Accessories, Insulation profile
GTIN (EAN)	4008190093105	
Qty.	10 pc(s).	
Туре	ISPF QB75 RT	Version
Order No.	0526760000	Accessories, Insulation profile
GTIN (EAN)	4008190157821	
Qty.	10 pc(s).	
Туре	ISPF QB75 SW	Version
Order No.	0526700000	Accessories, Insulation profile
GTIN (EAN)	4008190093723	
Qty.	10 pc(s).	



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories

W-Series



A partition plate is used for the optical separation of circuits or used for electrical isolation from neighbouring cross-connectors. In contrast to the end plate, the contour can be larger than the adjacent terminal blocks. However, it should not be smaller, as otherwise the required clearance and creepage distances within the application can no longer be maintained.

General ordering data

Type WTW EN
Order No. 1058800000
GTIN (EAN) 4008190140175
Oty. 20 pc(s).

Version

W-Series, Partition plate

DEK 5/6



WS/ DEK

MultiMark terminal markers use an innovative composite material made from two components. The hard base contour of the marker snaps securely into the connector. The elastic surface finish makes the marker easy to mount. This specially punched material enables the strips to be stretched to accommodate the slight variations in spacing that tend to add up, especially with long terminal blocks. Another advantage: the excellent printability of the surface material guarantees durable and wear-resistant labelling. A print resolution of 300 dpi also produces a very legible script.

Your benefits with MultiMark

- Firm hold and durable printing
- Continuous strips save installation time
- Easy mounting thanks to an innovative composite material
- Large label field for optimal legibility
- · High flexibility thanks to manufacturer independence

General ordering data

 Type
 DEK 5/6 MM WS
 Version

 Order No.
 2007120000
 Dekafix, Terminal marker, 5 x 6 mm, Weidmueller, white

 GTIN (EAN)
 4050118392104

 Qty.
 600 pc(s).



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories

Marker holder



The marker holder offer the possibility of additional mounting of standard markers with a pitch of 5 or 5.1 mm. The angled holders can be optionally snaped together and could be mounted in all standard marking channels of the Klippon[®] Connect modular terminal blocks. Fitting marker types could be found under the respective accessories of the designation marking holder.

General ordering data

Туре	BZT 1 ZA WS 10/5	Version
Order No.	<u>1805520000</u>	Accessories, Marker holder
GTIN (EAN)	4032248270248	
Qty.	100 pc(s).	
Туре	BZT 1 WS 10/5	Version
Order No.	<u>1805490000</u>	Accessories, Marker holder
GTIN (EAN)	4032248270231	
Qty.	100 pc(s).	

Testsockets



Test adapters and test plugs are used for the electrical connection between terminal blocks and the test equipment. In this way, an electrical contact can be established in the wired state and measurements can be done easily.

Туре	STB 8.5/D4.5/2/M3 SAKT4	Version
Order No.	0244600000	SAK Series, Socket
GTIN (EAN)	4008190103828	
Qty.	50 pc(s).	
Туре	STB 8.5/5/2.3/M3 SAK2.5	Version
Order No.	0280600000	Accessories, Socket
GTIN (EAN)	4008190023188	
Qty.	50 pc(s).	
Туре	STB 8.5/D4/2.3/M2.5 AKZ	Version
Order No.	0215700000	Accessories, Socket
GTIN (EAN)	4008190184872	
Qty.	50 pc(s).	



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories

Q/AKZ



Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

	oraorring aata	
Туре	Q 2 AKZ1.5	Version
Order No.	0368200000	SAK Series, Cross-connector, for cross-connection link, Number of
GTIN (EAN)	4008190149987	poles: 2
Qty.	50 pc(s).	
Туре	Q 10 AKZ1.5	Version
Order No.	0368500000	SAK Series, Cross-connector, for cross-connection link, Number of
GTIN (EAN)	4008190159481	poles: 10
Qty.	20 pc(s).	
Туре	Q 4 AKZ1.5	Version
Order No.	0368400000	SAK Series, Cross-connector, for cross-connection link, Number of
GTIN (EAN)	4008190153892	poles: 4
Qty.	50 pc(s).	
Туре	Q 10 AKZ4SS	Version
Order No.	0369300000	SAK Series, Cross-connector, for cross-connection link, Number of
GTIN (EAN)	4008190065744	poles: 10
Qty.	20 pc(s).	
Туре	Q 2 AKZ4	Version
Order No.	0336400000	SAK Series, Cross-connector, for cross-connection link, Number of
GTIN (EAN)	4008190037680	poles: 2
Qty.	50 pc(s).	
Туре	Q 2 AKZ4SS	Version
Order No.	0369000000	SAK Series, Cross-connector, Number of poles: 2
GTIN (EAN)	4008190143589	
Qty.	50 pc(s).	
Туре	Q 3 AKZ1.5	Version
Order No.	0368300000	SAK Series, Cross-connector, for cross-connection link, Number of
GTIN (EAN)	4008190074913	poles: 3
Qty.	50 pc(s).	
Туре	Q 4 AKZ4	Version
Order No.	0336600000	SAK Series, Cross-connector, for cross-connection link, Number of
GTIN (EAN)	4008190096656	poles: 4
Qty.	50 pc(s).	
Туре	Q 10 AKZ4	Version
Order No.	0368600000	SAK Series, Cross-connector, for cross-connection link, Number of
GTIN (EAN)	4008190056766	poles: 10
Qty.	20 pc(s).	
	_	



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories

Type Q 3 AKZ4

Order No. 0336500000

GTIN (EAN) 4008190121730

Qty. 50 pc(s).

Version

SAK Series, Cross-connector, for cross-connection link, Number of

poles: 3

QB



Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

General ordering data

Туре	QB 75/6.2/9/WI	Version
Order No.	0526400000	SAK Series, Cross-connector, for cross-connection link, Number of
GTIN (EAN)	4008190099923	poles: 75
Qty.	10 pc(s).	
Туре	QB 75/6.2/15	Version
Type Order No.	QB 75/6.2/15 0535200000	Version SAK Series, Cross-connector, for cross-connection link, Number of
	, ,	

TS 32

TS 32

Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

Туре	EWK 1	Version
Order No.	0206160000	Accessories, End bracket
GTIN (EAN)	4008190080020	
Qty.	50 pc(s).	



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories

Connection sleeves



General ordering data

Туре	VL 2 AKZ4/DK4	Version
Order No.	0446700000	SAK Series, Cross-connector, Cross-connector, Number of poles: 2
GTIN (EAN)	4008190055486	
Qty.	50 pc(s).	
Туре	VH 10/4/2.8 AKZ4	Version
Order No.	0446600000	SAK Series, Connecting sleeve, for cross-connection link, Number of
GTIN (EAN)	4008190176211	poles: 1
Qty.	50 pc(s).	
Туре	VL 2 SAK4	Version
Order No.	0197000000	SAK Series, Cross-connector, Cross-connector, Number of poles: 2
GTIN (EAN)	4008190000271	
Qty.	50 pc(s).	

SAK-Series



A partition plate is used for the optical separation of circuits or used for electrical isolation from neighbouring cross-connectors. In contrast to the end plate, the contour can be larger than the adjacent terminal blocks. However, it should not be smaller, as otherwise the required clearance and creepage distances within the application can no longer be maintained.

Туре	TW SAKS2 HP/DBR/2	Version
Order No.	0607000000	SAK Series, Partition plate, 2 mm, dark brown, Used between
GTIN (EAN)	4008190002732	terminals
Qty.	20 pc(s).	
Туре	TSCH 4 AKZ4	Version
Order No.	0363360000	SAK Series, Small partition, beige, 6 mm
GTIN (EAN)	4008190136680	
Qty.	100 pc(s).	
Туре	TSCH 6 DKI S4	Version
Order No.	0190260000	SAK Series, Small partition, beige, 5 mm
GTIN (EAN)	4008190051075	
Qty.	100 pc(s).	



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories

SAK-Series



Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

General ordering data

Type EW 35
Order No. 0383560000
GTIN (EAN) 4008190181314
Oty. 50 pc(s).

.

Accessories, End bracket

Blank



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- · Large range of ready-to-use markers
- · Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

Туре	DEK 5/6 MC NE GR	Version
Order No.	1238330000	Dekafix, Terminal marker, 5 x 6 mm, Pitch in mm (P): 6.00
GTIN (EAN)	4050118323306	Weidmueller, grey
Qty.	1,000 pc(s).	
Туре	DEK 5/6 MC NE GN	Version
Order No.	1238310000	Dekafix, Terminal marker, 5 x 6 mm, Pitch in mm (P): 6.00
GTIN (EAN)	4050118271812	Weidmueller, green
Qty.	1,000 pc(s).	
Туре	DEK 5/6 MC NE BR	Version
Order No.	1454900000	Dekafix, Terminal marker, 5 x 6 mm, Pitch in mm (P): 6.00
GTIN (EAN)	4050118323313	Weidmueller, brown
Qty.	1,000 pc(s).	



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories

Туре	DEK 5/6 MC NE GE	Version
Order No.	1238280000	Dekafix, Terminal marker, 5 x 6 mm, Pitch in mm (P): 6.00
GTIN (EAN)	4050118038750	Weidmueller, yellow
Qty.	1,000 pc(s).	, , ,
Туре	DEK 5/6 MC NE WS	Version
Order No.	<u>1609820000</u>	Dekafix, Terminal marker, 5 x 6 mm, Pitch in mm (P): 6.00
GTIN (EAN)	4008190203436	Weidmueller, white
Qty.	1,000 pc(s).	
Туре	DEK 5/6 MC NE BL	Version
Order No.	1238290000	Dekafix, Terminal marker, 5 x 6 mm, Pitch in mm (P): 6.00
GTIN (EAN)	4050118267327	Weidmueller, blue
Qty.	1,000 pc(s).	
Туре	DEK 5/6 MC NE OR	Version
Order No.	<u>1912090000</u>	Dekafix, Terminal marker, 5 x 6 mm, Pitch in mm (P): 6.00
GTIN (EAN)	4032248540525	Weidmueller, orange
Qty.	1,000 pc(s).	

Insulation sleeves

With insulating sleeve for cable lug, an increase of the rated voltage within the application is possible.

Туре	IH 2.8 DB	Version
Order No.	0386060000	W-Series, Insulating sleeve
GTIN (EAN)	4008190043414	
Qty.	100 pc(s).	
Туре	IH 6.3 WEM GE	Version
Type Order No.	IH 6.3 WEM GE 0386260000	Version W-Series, Insulating sleeve



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories

2.5 mm²

2.5

 mm^2

End plates are fitted to the open side of the last modular terminal before the end bracket. The use of an end plate ensures the function of the modular terminal and the specified rated voltage. It guarantees protection against contact with live parts and makes the final terminal finger-proof.

General ordering data

Type WAP WDK2.5

Order No. 1059100000

GTIN (EAN) 4008190101954

Qty. 20 pc(s).

Version

W-Series, End plate

Test plugs



Test adapters and test plugs are used for the electrical connection between terminal blocks and the test equipment. In this way, an electrical contact can be established in the wired state and measurements can be done easily.

General ordering data

Type PS 2.3 RT
Order No. 0180400000
GTIN (EAN) 4008190060121
Oty. 20 pc(s).

Version

Accessories, Test plug



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories

Plus



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- · Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- · Available as blank MultiCard or with standard printing

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Type DEK 5/6 PLUS MC NE WS Version

Order No. 1011320000 Dekafix, Terminal marker, 5 x 6 mm, Pitch in mm (P): 6.00

GTIN (EAN) 4032248717644 Weidmueller, white

Qty. 1,000 pc(s).

SAK-Series



Warning covers with a flash symbol provide more safety for man and machine. They are used where external voltage must be indicated within the application.

Туре	AD 3 SAK2.5	Version
Order No.	0297900000	SAK Series, cover plate, yellow, 18 mm
GTIN (EAN)	4008190038229	
Qty.	50 pc(s).	
Туре	AD 4 AKZ4	Version
Type Order No.	AD 4 AKZ4 0303400000	Version SAK Series, cover plate, yellow, 20 mm



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

....

Accessories

Custom printing



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Туре	DEK 5/6 MC SDR	Version
Order No.	1609830000	Dekafix, Terminal marker, 5 x 6 mm, Pitch in mm (P): 6.00
GTIN (EAN)	4008190456603	Weidmueller, To customer specification
Qty.	200 pc(s).	
Туре	DEK 5/6 PLUS MC SDR	Version
Type Order No.	DEK 5/6 PLUS MC SDR 1038650000	Version Dekafix, Terminal marker, 5 x 6 mm, Pitch in mm (P): 6.00
• •	· ·	

QB RA



Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

General ordering data

Туре	QB 3 WI RA6 IS	Version
Order No.	0482800000	SAK Series, Cross-connector, Cross-connector, Number of poles: 3
GTIN (EAN)	4008190145217	
Qty.	50 pc(s).	
Туре	QB 2 WI RA6 IS	Version
Type Order No.	QB 2 WI RA6 IS 0482700000	Version SAK Series, Cross-connector, Cross-connector, Number of poles: 2

Creation date March 28, 2024 3:52:46 PM CET



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories

Type QB 4 WI RA6 IS Version

Order No. 0482900000
GTIN (EAN) 4008190086169
Oty. 50 pc(s).

SAK Series, Cross-connector, Cross-connector, Number of poles: 4