

CLI O 30-3 GE/SW Y MP**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

CLI O conductor markers are fitted to connected conductors, and are therefore suitable for updating existing systems. Without problems, three different sizes can be used for marking conductor cross-sections from 0.4 mm² to max. 4.0 mm². The shape and design guarantee secure and permanent attachment of the individually combinable markers.

Advantages:

- Open markers for connected conductors
- Marker version with anti-rotation safeguard for secure combination marking
- Perfect for any supplementary labelling
- Extremely low space requirements
- Rapid clip-on attachment saves time

General ordering data

| | |
|------------|--|
| Version | CableLine, Conductor and cable markers, 4 - 5 mm, 3 x 6 mm, yellow |
| Order No. | 0648201696 |
| Type | CLI O 30-3 GE/SW Y MP |
| GTIN (EAN) | 4008190018696 |
| Qty. | 200 pc(s). |

CLI O 30-3 GE/SW Y MP

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|---------|-----------------|------------|
| Depth | 6 mm | Depth (inches) | 0.236 inch |
| Height | 3 mm | Height (inches) | 0.118 inch |
| Width | 6 mm | Width (inches) | 0.236 inch |
| Net weight | 0.055 g | | |

Temperatures

| | |
|-----------------------------|-------------|
| Operating temperature range | -30...80 °C |
|-----------------------------|-------------|

General data

| | | | |
|--|--------------------|-----------------------------------|----------------------------|
| Colour | yellow | Colour of printing | black |
| Halogen | Yes | Material | PVC, soft, without Cadmium |
| Material colour according to resistance code | 4 | Operating temperature range | -30...80 °C |
| Operating temperature range, max. | 80 °C | Operating temperature range, min. | -30 °C |
| Orientation of print | horizontal | Printed characters | Upper-case letters |
| Printing | Y | Printing method | hot-embossing |
| Recommended industries | Process, Machinery | Type of printing | Standard |
| UL 94 flammability rating | V-0 | Version | MultiPack |
| Width | 6 mm | | |

Conductor and cable markers

| | | | |
|-------------------------------|-------------------|----------------------------------|-----------------------|
| Conductor O.D. | 4 - 5 mm | Conductor O.D., max. | 5 mm |
| Conductor O.D., min. | 4 mm | Conductor cross-section, max. | 4 mm ² |
| Conductor cross-section, min. | 3 mm ² | Cross-section for connected wire | 3 - 4 mm ² |
| Halogen | Yes | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001530 | ETIM 7.0 | EC001530 |
| ETIM 8.0 | EC001530 | ETIM 9.0 | EC001530 |
| ECLASS 9.0 | 27-40-04-01 | ECLASS 9.1 | 27-40-04-01 |
| ECLASS 10.0 | 27-40-04-01 | ECLASS 11.0 | 27-28-11-02 |
| ECLASS 12.0 | 27-28-11-02 | ECLASS 13.0 | 27-28-11-02 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|------------|--|
| Catalogues | Catalogues in PDF-format |
|------------|--|

CLI O 30-3 GE/SW Y MP

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings



Similar to illustration