

KLIPPON STB 6 SS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

Ideally suited for the energy, process and transportation industries, the Klippon® STB enclosure series is the perfect complement to our existing Klippon® enclosure portfolio. Enclosures in this series are approved according to international standards such as e.g. EN62208 and EN60079-0/7 (ATEX).

- Mirror-polished or electropolished stainless steel 1.4404 (316L), 1.5 mm
- High-temperature-resistant seal as standard - extended temperature range of -60°C to +100°C for Ex application (+120°C only for industrial application)
- Approved according to ATEX, IECEx, cULus, Lloyds Register, Germanischer Lloyd, GL DNV and INMETRO
- Flexible options for fastening the internal mounting rail
- IP66 protection
- Secure, permanent function of the seal is ensured by seal compression protection
- Earthing stud in the cover and base of the enclosure
- Laser cut weld seams for increased quality
- Already welded-on mounting feet guarantee optimum enclosure installation

Weidmüller can manufacture and supply this enclosure - according to customer specifications - fitted with all necessary terminals and cable glands.

General ordering data

| | |
|------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Version | Klippon STB (Small Terminal Box), Empty enclosure, stainless steel enclosure, Height: 250 mm, Width: 400 mm, Depth: 130 mm, Material: Stainless steel 1.4404 (316L), Mirror polished, silver |
| Order No. | 1002760000 |
| Type | KLIPPON STB 6 SS |
| GTIN (EAN) | 4032248695690 |
| Qty. | 1 pc(s). |

KLIPPON STB 6 SS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|-----------------------------|---------|----------------------------|-------------|
| Depth | 130 mm | Depth (inches) | 5.118 inch |
| Height | 250 mm | Height (inches) | 9.842 inch |
| Width | 400 mm | Width (inches) | 15.748 inch |
| Mounting dimension - height | 150 mm | Mounting dimension - width | 425 mm |
| Net weight | 5,714 g | | |

Temperatures

| | |
|-----------------------|------------------|
| Operating temperature | -60 °C... 100 °C |
|-----------------------|------------------|

Cable glands, left

| | | | |
|-----|----|-----|----|
| M12 | 64 | M16 | 33 |
| M20 | 30 | M25 | 16 |
| M32 | 10 | M40 | 6 |
| M50 | 4 | M63 | 2 |

Cable glands, right

| | | | |
|-----|----|-----|----|
| M12 | 36 | M16 | 21 |
| M20 | 18 | M25 | 10 |
| M32 | 8 | M40 | 3 |
| M50 | 2 | M63 | 2 |

Cable glands, top/bottom

| | | | |
|-----|----|-----|----|
| M12 | 64 | M16 | 33 |
| M20 | 30 | M25 | 16 |
| M32 | 10 | M40 | 6 |
| M50 | 4 | M63 | 2 |

Certificate numbers enclosure

| | | | |
|-----------------------------------------|--------------------------------------------------------------------------------------------|--------------------------------------------|---------------------------|
| Approval conditions | ATEX, DNV, IECEX, IN-METRO, LR, RMRS, UL AEx Class Div., UL AEx Class Zone, cULus, KC, CCC | Attestation of Conformity No. (AoC) | DE PS2620 160308 001ISS02 |
| Certificate No. (ATEX) | IBEXU07ATEX1148 | Certificate No. (IECEX) | IECEXIBE09.0018U |
| Certificate no. (INMETRO) | IEX13.0002U | Certificate no. (cULus) | E256877 |
| Certificate no. Terminal Box (AEx) | E223792 | Certificate no. Terminal Box (ATEX) | IBEXU07ATEX1148 |
| Certificate no. Terminal Box (IECEX) | IECEX IBE 09.0019 | Certificate no. Terminal Box (INMETRO) | LMP 21.0018 |
| Certificate no. Terminal Box (KOSHA) | 16-AV4BO-0247X | Certificate no. empty enclosure (ATEX) | IBEXU 07ATEX1147U |
| Certificate no. empty enclosure (IECEX) | IECEX IBE 09.0018U | Certificate no. empty enclosure (IN-METRO) | LMP 21.0015U |
| Declaration of Conformity No. (DoC LVD) | DE PS2620 160412 001ISS01 | | |

KLIPPON STB 6 SS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

General information

| | | | |
|-----------------------------|-----------------------------------------------------------------------------------------------|---------------------------------|-----------------------------------------|
| Access opening: height | 230 mm | Access opening: width | 382 mm |
| Areas of use | Explosive risk zone, Packaging industry, Transportation, Process industry, Marine engineering | Enclosure attachment | Welded-on mounting foot with 8-mm holes |
| Flange plate | No | Impact resistance | 10 J version standard, 7 J ATEX version |
| Integral fixing | TAS 20 rail welded to floor | Lid | Yes |
| Lid attachment | M5 hexagonal screw with slot and 10mm distance across flats | Material | Stainless steel 1.4404 (316L) |
| Material thickness of cover | 1.5 mm | Material thickness of enclosure | 1.5 mm |
| Number of lid screws | 4 | Operating temperature, max. | 100 °C |
| Operating temperature, min. | -60 °C | Protection class (UL) | Type 4, Type 4X |
| Protection degree | IP66 | Seal material | Silicone |
| Surface finish | Mirror polished | Torque for lid screws | 2.5 Nm |

Housing earth

| | | | |
|----------------------------|-----------------------------------------|----------------------------|----------------------------------------------|
| Cross-section, max. | 25 mm ² | Earth, enclosure, cover | Welded-on M6 x 10 stainless-steel earth stud |
| Earth, enclosure, external | Welded-on M6 x 16 stainless-steel bolts | Earth, enclosure, internal | Welded-on M6 x 16 stainless-steel bolts |

horizontal assembly

| | | | |
|-----------------------------|------|-----------------|------|
| WDU 10 / ZDU 10 | 2x37 | WDU 16 / ZDU 16 | 2x30 |
| WDU 2,5 / ZDU 2,5 / IDU 2,5 | 2x72 | WDU 4 / ZDU 4 | 2x60 |
| WDU 6 / ZDU 6 | 2x46 | | |

vertical assembly

| | | | |
|-----------------------------|------|-----------------|------|
| WDU 10 / ZDU 10 | 3x22 | WDU 16 / ZDU 16 | 3x18 |
| WDU 2,5 / ZDU 2,5 / IDU 2,5 | 3x42 | WDU 4 / ZDU 4 | 3x35 |
| WDU 6 / ZDU 6 | 3x27 | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC002503 | ETIM 7.0 | EC002503 |
| ETIM 8.0 | EC002503 | ETIM 9.0 | EC002503 |
| ECLASS 9.0 | 27-18-05-02 | ECLASS 9.1 | 27-18-05-02 |
| ECLASS 10.0 | 27-18-05-02 | ECLASS 11.0 | 27-18-05-02 |
| ECLASS 12.0 | 27-18-05-02 | ECLASS 13.0 | 27-18-05-02 |

Important note

| | |
|---------------------|----------------------------------------------------------------------------------------------------------|
| Product information | The ambient temperature for the assembly will be reduced to +60°C and the surface temperature to +100°C. |
|---------------------|----------------------------------------------------------------------------------------------------------|

KLIPPON STB 6 SS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

Approvals



| | |
|-------------------------|------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate no. (cULus) | E256877 |


Downloads

| | |
|---------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Approval/Certificate/Document of Conformity | CCC 2020322303002356 STB Assembly Enclosure UKCA TÜV 22 UKEX 7099 U UKCA TÜV 22 UKEX 7100 Attestation of Conformity - Klippon STB Empty Enclosures - AoC DE PS2620 160308 001ISS04 08_20032 IBEXU07ATEX1148 IECEXIBE09.0018U IECEXIBE09.0019 16-AV4BO-247X 59358-08 IBEXU07ATEX1147U INMETRO Certificado LMP 21.0018 KLIPPON STB CERTIFICADO LMP 21.0015U KLIPPON STB EU Declaration of Conformity - Klippon STB Empty Enclosures Ex - DoC DE PS2620 160412 001ISS01 |
| Engineering Data | CAD data – STEP |
| Tender specification | Klippon STB 6 SS_1002760000_DE Klippon STB 6 SS_1002760000_EN |
| User Documentation | Assembly guidelines - empty enclosures |
| Catalogues | Catalogues in PDF-format |
| Brochures | MB OVERV. PROCESS WD DE MB KLIPPON ENCL.TECN EN MB PROCESS EN FL KLIPPON STB EN FL SHIPBUILDING 2016 EN FL SHIPBUILDING 2016 EN |

KLIPPON STB 6 SS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings**Dimensioned drawing**

KLIPPON STB 6 SS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Ventilation plugs - DAE



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

| | | |
|------------|----------------------------|---------------------------------------------------------------------|
| Type | DAE M12 SS | Version |
| Order No. | 1868550000 | DAE (ventilation element), Compensating element, straight, M 12, 10 |
| GTIN (EAN) | 4032248440405 | mm, IP66, IP68, IP69K, Stainless steel 1.4305 (303) |
| Qty. | 10 pc(s). | |
| Type | DAE M12 PA LONG | Version |
| Order No. | 1868570000 | DAE (ventilation element), Compensating element, straight, M 12, 10 |
| GTIN (EAN) | 4032248440429 | mm, IP66, IP68, IP69K, Polyamide 6 |
| Qty. | 10 pc(s). | |

Installation material

**Integrate, expand and customise - the perfect supplement to every application**

The fully structured range of system accessories for the new Klippon® TB enclosure series allows you to easily adapt the enclosures to meet the specific requirements of every application.

Mounting hardware kits

Mounting hardware kits are available for quick and easy installation of type label holders, document holders and rain hoods.

The **label fastening set – SD** is required to install a plastic (Trafolyte) ID or type label. With the aid of this set can you mount the ID or type label directly on the enclosure cover. The label fastening set has been specially developed for this purpose. Only by using this fastening set can you ensure that there will be no leaks into the enclosure or damage to the label.

The **universal fastening set – TPSD** has been developed to enable secure and quick installation of type label holders, rain covers or document holders, for example. By using this fastening set, the risk of leaks can be minimised, if not avoided.

General ordering data

| | | |
|------------|----------------------------|------------------------------------------------------------------------|
| Type | TPSD FIXING SET KTB | Version |
| Order No. | 1252190000 | Klippon TB (Terminal Box), Type plate fixings set, Material: Stainless |
| GTIN (EAN) | 4050118043969 | steel, rust-proof, untreated, silver |
| Qty. | 1 pc(s). | |

KLIPPON STB 6 SS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

| Type | SD FIXING SET | Version |
|------------|----------------------------|------------------------------------------------------------------------|
| Order No. | 1285200000 | Klippon TB (Terminal Box), Identification plate fixing set, Height: 12 |
| GTIN (EAN) | 4050118075472 | mm, Width: 12 mm, Depth: 16.4 mm, Material: Stainless steel, rust- |
| Qty. | 1 pc(s). | proof, untreated, silver |

Grounding strap

The fully structured range of system accessories for the new Klippon® TB enclosure series allows you to easily adapt the enclosures to meet the specific requirements of every application. The following options are available:

- Closure Elements
- Document holders
- Earthing stud
- Gland plates
- Installation material
- Mounting plates
- Rain hoods
- Spacer
- Terminal rails
- Type label holder

General ordering data

| Type | PECD WIRE 6/200/D6 SET | Version |
|------------|----------------------------|------------------------------------------------------------------------|
| Order No. | 2475490000 | Klippon TB (Terminal Box), Grounding strap, Sscrewed, Material: Steel, |
| GTIN (EAN) | 4050118487206 | Green/yellow |
| Qty. | 1 pc(s). | |

Terminal rails - TS35



The system accessories for the Klippon® STB enclosure series allows you to easily adapt the enclosures to meet the specific requirements of every application.

- DIN Rails TS 35
- Mounting screws

Weidmüller can manufacture and supply this enclosure - according to customer specifications - fitted with all necessary terminals and cable glands.

General ordering data

| Type | TS35X7.5 ST STB 4 STB 6 | Version |
|------------|----------------------------|------------------------------------------------------------------------|
| Order No. | 8563410000 | Rail, TS 35, TS 35 x 7.5, Width: 200 mm, without slot, Steel, galvanic |
| GTIN (EAN) | 4050118652789 | zinc plated and passivated |
| Qty. | 20 pc(s). | |
| Type | TS35X7.5 ST STB 5 | Version |
| Order No. | 8803610000 | Rail, TS 35, TS 35 x 7.5, Width: 320 mm, without slot, Steel, |
| GTIN (EAN) | 4050118652796 | galvanized, chromium-plated |
| Qty. | 20 pc(s). | |
| Type | SFNS5 VKMU M5 SW15 | Version |
| Order No. | 0433500000 | Klippon STB (Small Terminal Box), Fixing nut, Square, Height: 15 |
| GTIN (EAN) | 4008190494520 | mm, Width: 15 mm, Depth: 11.7 mm, Material: Steel, galvanised, |
| Qty. | 20 pc(s). | galvanized, silver |

Creation date April 26, 2024 6:07:17 AM CEST

KLIPPON STB 6 SS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories**

| | | |
|------------|----------------------------|-----------------------------------------------------------------------------------------------|
| Type | TS35X15 ST STB 4 STB 6 | Version |
| Order No. | 8000073220 | Rail, TS 35, TS 35 x 15, Width: 200 mm, with slot, Steel, galvanic zinc plated and passivated |
| GTIN (EAN) | 4064675356783 | |
| Qty. | 20 pc(s). | |
| Type | TS35X15 ST STB 5 | Version |
| Order No. | 8000073222 | Rail, TS 35, TS 35 x 15, Width: 320 mm, with slot, Steel, galvanic zinc plated and passivated |
| GTIN (EAN) | 4064675356790 | |
| Qty. | 20 pc(s). | |