

**WDU 2.5/10 BEZ/NE****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

To feed through power, signal, and data is the classical requirement in electrical engineering and panel building. The insulating material, the connection system and the design of the terminal blocks are the differentiating features. A feed-through terminal block is suitable for joining and/or connecting one or more conductors. They could have one or more connection levels that are on the same potential or insulated against one another.

**General ordering data**

|            |  |
|------------|--|
| Version    | Single- and multi-pole terminal strip, Screw connection, 2.5 mm <sup>2</sup> , 500 V, 24 A, Number of poles: 10, 51 mm, dark beige |
| Order No.  | <a href="#">1020800000</a>   |
| Type       | WDU 2.5/10 BEZ/NE  |
| GTIN (EAN) | 4008190133368  |
| Qty.       | 10 pc(s).  |

## WDU 2.5/10 BEZ/NE

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Depth      | 46.5 mm | Depth (inches)  | 1.831 inch |
| Height     | 60 mm   | Height (inches) | 2.362 inch |
| Width      | 51 mm   | Width (inches)  | 2.008 inch |
| Net weight | 77.8 g  |                 |            |

## Temperatures

|                                  |                |                                  |   |
|----------------------------------|----------------|----------------------------------|---|
| Storage temperature              |                | Operating temperature range      | For operating temperature range see EC Design Test Certificate / IEC Ex-Certificate of Conformity |
|                                  | -25 °C...55 °C |                                  |   |
| Continuous operating temp., min. | -60 °C         | Continuous operating temp., max. | 130 °C  |

## Material data

|                           |       |        |            |
|---------------------------|-------|--------|------------|
| Material                  | Wemid | Colour | dark beige |
| UL 94 flammability rating | V-0   |        |            |

## Rating data IECEx/ATEX

|                                |   |                                 |                     |
|--------------------------------|---|---------------------------------|---------------------|
| Certificate No. (ATEX)         | DEMKO14ATEX1338U  | Certificate No. (IECEX)         | IECEXULD14.0005U    |
| Max. voltage (ATEX)            | 690 V   | Current (ATEX)                  | 24 A                |
| Wire cross section max. (ATEX) | 2.5 mm <sup>2</sup>   | Max. voltage (IECEX)            | 690 V               |
| Current (IECEX)                | 24 A  | Wire cross section max. (IECEX) | 2.5 mm <sup>2</sup> |
| Operating temperature range    | For operating temperature range see EC Design Test Certificate / IEC Ex-Certificate of Conformity | Marking EN 60079-7              |                     |
| Ex 2014/34/EU label            | II 2 G D  |                                 | Ex eb II C Gb       |

## System specifications

|                                     |  |                               |     |
|-------------------------------------|--|-------------------------------|-----|
| Version                             | Screw connection, for plug-in cross-connector, for screwable cross-connection, One end without connector | End cover plate required      | Yes |
| Number of potentials                | 1  | Number of levels              | 1   |
| Number of clamping points per level | 2  | Number of potentials per tier | 1   |
| Levels cross-connected internally   | No   | PE connection                 | No  |
| Rail                                | TS 35  | N-function                    | No  |
| PE function                         | No   | PEN function                  | No  |

## Additional technical data

|                          |       |                             |         |
|--------------------------|-------|-----------------------------|---------|
| Explosion-tested version | Yes   | Number of similar terminals | 10      |
| Open sides               | right | Type of mounting            | Snap-on |

## CSA rating data

|                               |                |                               |        |
|-------------------------------|----------------|-------------------------------|--------|
| Certificate No. (CSA)         | 200039-1057876 | Current size C (CSA)          | 20 A   |
| Voltage size C (CSA)          | 600 V          | Wire cross section max. (CSA) | 12 AWG |
| Wire cross section min. (CSA) | 26 AWG         |                               |        |

## WDU 2.5/10 BEZ/NE

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Conductors for clamping (additional connection)

Conductor cross-section, flexible plus plastic collar DIN 46228/1, further connection, max.

2.5 mm<sup>2</sup>

Connection type, additional connection

Screw connection

## Conductors for clamping (rated connection)

|   |  |                              |                      |                  |  |  |
|---|--|------------------------------|----------------------|------------------|--|--|
| Clampable conductor                         | Connection specification               |                              | Screw connection     |                  |  |  |
|   | Cross-section for conductor connection | Type                         | solid, H05(07) V-U   |                  |  |  |
|   |  | min.                         | 0.5 mm <sup>2</sup>  |                  |  |  |
|   |  | max.                         | 4 mm <sup>2</sup>    |                  |  |  |
|   |  | nominal                      | 2.5 mm <sup>2</sup>  |                  |  |  |
|   | wire end ferrule                       | Stripping length             | min.                 | 10 mm            |  |  |
|   |  |                              | max.                 | 10 mm            |  |  |
|   |  |                              | nominal              | 10 mm            |  |  |
|   |  | Tightening torque            | min.                 | 0.4 Nm           |  |  |
|   |  |                              | max.                 | 0.8 Nm           |  |  |
|   |  | Recommended wire-end ferrule |                      |                  |  |  |
|   |  | Connection specification     |                      | Screw connection |  |  |
|   | Cross-section for conductor connection | Type                         | stranded, H07V-R     |                  |  |  |
|   |  | min.                         | 1.5 mm <sup>2</sup>  |                  |  |  |
|   |  | max.                         | 4 mm <sup>2</sup>    |                  |  |  |
|   |  | nominal                      | 2.5 mm <sup>2</sup>  |                  |  |  |
|   | wire end ferrule                       | Stripping length             | min.                 | 10 mm            |  |  |
|   |  |                              | max.                 | 10 mm            |  |  |
|   |  |                              | nominal              | 10 mm            |  |  |
|   |  | Tightening torque            | min.                 | 0.4 Nm           |  |  |
| max.  |  |                              | 0.8 Nm               |                  |  |  |
| Recommended wire-end ferrule                |  |                              |                      |                  |  |  |
| Connection specification                    |  | Screw connection             |                      |                  |  |  |
| Cross-section for conductor connection      | Type                                   | flexible, H05(07) V-K        |                      |                  |  |  |
|   | min.                                   | 0.5 mm <sup>2</sup>          |                      |                  |  |  |
|   | max.                                   | 2.5 mm <sup>2</sup>          |                      |                  |  |  |
|   | nominal                                | 2.5 mm <sup>2</sup>          |                      |                  |  |  |
| wire end ferrule                            | Stripping length                       | min.                         | 10 mm                |                  |  |  |
|   |  | max.                         | 10 mm                |                  |  |  |
|   |  | nominal                      | 10 mm                |                  |  |  |
|   | Tightening torque                      | min.                         | 0.4 Nm               |                  |  |  |
|   |  | max.                         | 0.8 Nm               |                  |  |  |
|   | Recommended wire-end ferrule           |                              |                      |                  |  |  |
|   | Clamping range, min.                   |                              | 0.05 mm <sup>2</sup> |                  |  |  |
| Clamping screw                              |  | M 2.5                        |                      |                  |  |  |
| Connection direction                        |  | on side                      |                      |                  |  |  |
| Number of connections                       |  | 2                            |                      |                  |  |  |
| Stripping length                            |  | 10 mm                        |                      |                  |  |  |
| Torque level with DMS electric screw-driver |  | 1                            |                      |                  |  |  |
| Twin wire-end ferrules, max.                |  | 1.5 mm <sup>2</sup>          |                      |                  |  |  |
| Twin wire-end ferrules, min.                |  | 0.5 mm <sup>2</sup>          |                      |                  |  |  |
| Type of connection                          |  | Screw connection             |                      |                  |  |  |
| Wire connection cross section AWG, max.     |  | AWG 12                       |                      |                  |  |  |
| Wire connection cross section AWG, min.     |  | AWG 30                       |                      |                  |  |  |

Creation date May 3, 2024 10:11:41 AM CEST

## WDU 2.5/10 BEZ/NE

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

Wire connection cross section, finely

stranded, max.

4 mm<sup>2</sup>

Wire connection cross section, finely

stranded, min.

0.5 mm<sup>2</sup>Wire connection cross-section, finely  
stranded with wire-end ferrules DIN  
46228/1, max.2.5 mm<sup>2</sup>Wire connection cross-section, finely  
stranded with wire-end ferrules DIN  
46228/1, min.0.25 mm<sup>2</sup>Wire connection cross-section, finely  
stranded with wire-end ferrules DIN  
46228/4, max.2.5 mm<sup>2</sup>Wire connection cross-section, finely  
stranded with wire-end ferrules DIN  
46228/4, min.0.5 mm<sup>2</sup>Wire connection cross-section, solid  
core, max.4 mm<sup>2</sup>Wire connection cross-section, solid  
core, min.0.5 mm<sup>2</sup>

## General

Number of poles

10

Rail

TS 35

Wire connection cross section AWG,  
max.

AWG 12

Wire connection cross section AWG,  
min.

AWG 30

## Rating data

Rated cross-section

2.5 mm<sup>2</sup>

Rated voltage

500 V

Rated DC voltage

500 V

Rated current

24 A

Volume resistance according to IEC  
60947-7-x

1.33 mΩ

Power loss in accordance with IEC  
60947-7-x

0.77 W

## Classifications

ETIM 6.0

EC001284

ETIM 7.0

EC001284

ETIM 8.0

EC001284

ETIM 9.0

EC001284

ECLASS 9.0

27-14-11-06

ECLASS 9.1

27-14-11-06

ECLASS 10.0

27-14-11-06

ECLASS 11.0

27-14-11-06

ECLASS 12.0

27-14-11-06

ECLASS 13.0

27-14-11-06

## Approvals

Approvals



ROHS

Conform

## WDU 2.5/10 BEZ/NE

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Downloads


|  |   |
|--|---|
| Approval/Certificate/Document of Conformity                  | <a href="#">IECEX Certificate</a>               |
|  | <a href="#">CB Testreport</a>                   |
|  | <a href="#">CB Certificate</a>                  |
|  | <a href="#">CE Declaration of Conformity</a>    |
|  | <a href="#">ATEX Certificate</a>                |
|  | <a href="#">UKCA declaration of conformity</a>  |
| <a href="#">Confirmation of Standards EN 45545-2_2020-10</a> |   |
| Engineering Data   | <a href="#">CAD data – STEP</a>                 |
| Engineering Data   | <a href="#">Zuken E3.S</a>                      |
| User Documentation   | <a href="#">StorageConditionsTerminalBlocks</a> |
| Catalogues   | <a href="#">Catalogues in PDF-format</a>        |

## WDU 2.5/10 BEZ/NE

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

# Drawings



**WDU 2.5/10 BEZ/NE****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****W-Series**

W  
Series

Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

**General ordering data**

|            |                            |  |
|------------|----------------------------|--|
| Type       | WEW 35/2                   | Version  |
| Order No.  | <a href="#">1061200000</a> | End bracket, Wemid, dark beige, Rail: TS 35, when screwed in |
| GTIN (EAN) | 4008190030230              |  |
| Qty.       | 50 pc(s).                  |  |

**Blank**

The WAD connector marker is suitable for W-series terminals and for the WEW 35/2 and ZEW 35/2 end brackets. The markers are available as blank markers, with custom printing or standard print with lightning symbol. The WAD MultiCard markers are suitable for labelling with PrintJet CONNECT printers.

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

**General ordering data**

|            |                            |   |
|------------|----------------------------|---|
| Type       | WAD 5 MC NE WS             | Version   |
| Order No.  | <a href="#">1112910000</a> | Group markers, Cover, 33.3 x 5 mm, Pitch in mm (P): 5.00 WDU 2.5, |
| GTIN (EAN) | 4032248891689              | WEW 35/2, ZEW 35/2, white   |
| Qty.       | 48 pc(s).                  |   |
| Type       | WAD 5 MC NE GE             | Version   |
| Order No.  | <a href="#">1112920000</a> | Group markers, Cover, 33.3 x 5 mm, Pitch in mm (P): 5.00 WDU 2.5, |
| GTIN (EAN) | 4032248891771              | WEW 35/2, ZEW 35/2, yellow  |
| Qty.       | 48 pc(s).                  |   |

## WDU 2.5/10 BEZ/NE

Weidmüller Interface GmbH &amp; Co. KG


Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

2.5-10 mm<sup>2</sup>


2.5-10  
mm<sup>2</sup>

End plates are fitted to the open side of the last modular terminal before the end bracket. The use of an end plate ensures the function of the modular terminal and the specified rated voltage. It guarantees protection against contact with live parts and makes the final terminal finger-proof.

## General ordering data

|            |                            |  |
|------------|----------------------------|--|
| Type       | WAP 16+35 WTW 2.5-10 BL    | Version  |
| Order No.  | <a href="#">1050180000</a> | End and partition plate for terminals, End plate, 56 mm x 1.5 mm, blue       |
| GTIN (EAN) | 4008190013899              |  |
| Qty.       | 20 pc(s).                  |  |
| Type       | WAP 2.5-10 BL              | Version  |
| Order No.  | <a href="#">1050080000</a> | End plate (terminals), 56 mm x 1.5 mm, blue                                  |
| GTIN (EAN) | 4008190136611              |  |
| Qty.       | 50 pc(s).                  |  |
| Type       | WAP 2.5-10/0.5MM           | Version  |
| Order No.  | <a href="#">1966380000</a> | End plate (terminals), 54.5 mm x 0.35 mm, dark beige                         |
| GTIN (EAN) | 4032248688616              |  |
| Qty.       | 50 pc(s).                  |  |
| Type       | WAP 2.5-10                 | Version  |
| Order No.  | <a href="#">1050000000</a> | End plate (terminals), 56 mm x 1.5 mm, dark beige                            |
| GTIN (EAN) | 4008190103149              |  |
| Qty.       | 50 pc(s).                  |  |
| Type       | WAP 16+35 WTW 2.5-10       | Version  |
| Order No.  | <a href="#">1050100000</a> | End and partition plate for terminals, End plate, 56 mm x 1.5 mm, dark beige |
| GTIN (EAN) | 4008190079901              |  |
| Qty.       | 20 pc(s).                  |  |



## WDU 2.5/10 BEZ/NE

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

## WS 12/5



## WS/ DEK

MultiMark terminal markers use an innovative composite material made from two components. The hard base contour of the marker snaps securely into the connector. The elastic surface finish makes the marker easy to mount. This specially punched material enables the strips to be stretched to accommodate the slight variations in spacing that tend to add up, especially with long terminal blocks. Another advantage: the excellent printability of the surface material guarantees durable and wear-resistant labelling. A print resolution of 300 dpi also produces a very legible script.

## Your benefits with MultiMark

- Firm hold and durable printing
- Continuous strips save installation time
- Easy mounting thanks to an innovative composite material
- Large label field for optimal legibility
- High flexibility thanks to manufacturer independence

## General ordering data

|            |                            |  |
|------------|----------------------------|--|
| Type       | WS 12/5 MM WS              | Version  |
| Order No.  | <a href="#">2007190000</a> | WS, Terminal marker, 12 x 5 mm, Weidmueller, white |
| GTIN (EAN) | 4050118392036              |  |
| Qty.       | 800 pc(s).                 |  |

## WDU 2.5/10 BEZ/NE

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Blank



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

|            |                            |   |
|------------|----------------------------|---|
| Type       | DEK 5/5 MC NE WS           | Version   |
| Order No.  | <a href="#">1609801044</a> | Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 |
| GTIN (EAN) | 4008190397111              | Weidmueller, white  |
| Qty.       | 1,000 pc(s).               |   |

## Shielding connection



With the LS 2.8 WDU2.5-10, many feed-through modular terminal blocks from the W series can be converted very easily. Inserting the LS 2.8 WDU2.5-10 allows the cable shielding braid to be looped through directly at the terminal block by soldering or using a suitable flat cable lug.

## General ordering data

|            |                            |                      |
|------------|----------------------------|----------------------|
| Type       | LS 2.8 WDU2.5-10           | Version              |
| Order No.  | <a href="#">1056400000</a> | W-Series, Shield bus |
| GTIN (EAN) | 4008190036454              |                      |
| Qty.       | 100 pc(s).                 |                      |

## WDU 2.5/10 BEZ/NE

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Blank



WS markers are the perfect match for the W-series connectors. Thanks to their system compatibility, the WS tags can also be used with the I-series and the Z-series. The large marking surfaces do not only permit long character strings but also multi-line text. WS markers are ideal for labels with long, customised character strings. Thanks to the proven MultiCard format, printing with PrintJet CONNECT oder/or Plotter is possible.

- Can be fitted in strips or individually
- Markers in proven MultiCard format

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

| Type       | WS 12/5 MC NE WS           | Version  |
|------------|----------------------------|--|
| Order No.  | <a href="#">1609860000</a> | WS, Terminal marker, 12 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, |
| GTIN (EAN) | 4008190203481              | Allen-Bradley, white   |
| Qty.       | 720 pc(s).                 |  |

## W-Series



A partition plate is used for the optical separation of circuits or used for electrical isolation from neighbouring cross-connectors. In contrast to the end plate, the contour can be larger than the adjacent terminal blocks. However, it should not be smaller, as otherwise the required clearance and creepage distances within the application can no longer be maintained.

## General ordering data

| Type       | WTW EN                     | Version   |
|------------|----------------------------|---|
| Order No.  | <a href="#">1058800000</a> | Partition plate (terminal), Intermediate plate, 86 mm x 62 mm, dark |
| GTIN (EAN) | 4008190140175              | beige   |
| Qty.       | 20 pc(s).                  |   |

**WDU 2.5/10 BEZ/NE****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold


Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Step-down bridges**

Reducing cross-connectors enable simple and fast connection of terminal blocks with different rated cross-sections.

**General ordering data**

|            |                            |  |
|------------|----------------------------|--|
| Type       | WQV 16-2.5                 | Version  |
| Order No.  | <a href="#">1063900000</a> | Cross-connector (terminal), when screwed in, Number of poles: 2, |
| GTIN (EAN) | 4008190112158              | Pitch in mm (P): 11.90, Insulated: Yes, 76 A, yellow             |
| Qty.       | 10 pc(s).                  |  |

**2.5 mm<sup>2</sup>**

Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

**General ordering data**

|            |                            |   |
|------------|----------------------------|---|
| Type       | WQV 2.5/3                  | Version   |
| Order No.  | <a href="#">1053760000</a> | Cross-connector (terminal), when screwed in, Number of poles: 3,  |
| GTIN (EAN) | 4008190058999              | Pitch in mm (P): 5.10, Insulated: Yes, 32 A, yellow               |
| Qty.       | 50 pc(s).                  |   |
| Type       | WQV 2.5/2                  | Version   |
| Order No.  | <a href="#">1053660000</a> | Cross-connector (terminal), when screwed in, Number of poles: 2,  |
| GTIN (EAN) | 4008190031121              | Pitch in mm (P): 5.10, Insulated: Yes, 32 A, yellow               |
| Qty.       | 50 pc(s).                  |   |
| Type       | WQV 2.5/10                 | Version   |
| Order No.  | <a href="#">1054460000</a> | Cross-connector (terminal), when screwed in, Number of poles: 10, |
| GTIN (EAN) | 4008190135089              | Pitch in mm (P): 5.10, Insulated: Yes, 32 A, yellow               |
| Qty.       | 20 pc(s).                  |   |
| Type       | WQV 2.5/4                  | Version   |
| Order No.  | <a href="#">1053860000</a> | Cross-connector (terminal), when screwed in, Number of poles: 4,  |
| GTIN (EAN) | 4008190049706              | Pitch in mm (P): 5.10, Insulated: Yes, 32 A, yellow               |
| Qty.       | 50 pc(s).                  |   |

**WDU 2.5/10 BEZ/NE****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****WQB****General ordering data**

|            |                            |   |
|------------|----------------------------|---|
| Type       | WQB B/10                   | Version   |
| Order No.  | <a href="#">1579050000</a> | Cross-connector (terminal), when screwed in, Number of poles: 10, |
| GTIN (EAN) | 4008190094508              | Pitch in mm (P): 5.10, Insulated: Yes, black                      |
| Qty.       | 20 pc(s).                  |   |
| Type       | WQB B/24                   | Version   |
| Order No.  | <a href="#">1579060000</a> | Cross-connector (terminal), when screwed in, Number of poles: 24, |
| GTIN (EAN) | 4008190188597              | Pitch in mm (P): 5.10, Insulated: Yes, black                      |
| Qty.       | 20 pc(s).                  |   |
| Type       | WQB B/3                    | Version   |
| Order No.  | <a href="#">1579020000</a> | Cross-connector (terminal), when screwed in, Number of poles: 3,  |
| GTIN (EAN) | 4008190062392              | Pitch in mm (P): 5.10, Insulated: Yes, black                      |
| Qty.       | 50 pc(s).                  |   |
| Type       | WQB B/2                    | Version   |
| Order No.  | <a href="#">1579010000</a> | Cross-connector (terminal), when screwed in, Number of poles: 2,  |
| GTIN (EAN) | 4008190021696              | Pitch in mm (P): 5.10, Insulated: Yes, black                      |
| Qty.       | 50 pc(s).                  |   |
| Type       | WQB B/4                    | Version   |
| Order No.  | <a href="#">1579030000</a> | Cross-connector (terminal), when screwed in, Number of poles: 4,  |
| GTIN (EAN) | 4008190185046              | Pitch in mm (P): 5.10, Insulated: Yes, black                      |
| Qty.       | 50 pc(s).                  |   |
| Type       | WQB B/6                    | Version   |
| Order No.  | <a href="#">1579040000</a> | Cross-connector (terminal), when screwed in, Number of poles: 6,  |
| GTIN (EAN) | 4008190081041              | Pitch in mm (P): 5.10, Insulated: Yes, black                      |
| Qty.       | 20 pc(s).                  |   |

## WDU 2.5/10 BEZ/NE

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Testsockets



Test adapters and test plugs are used for the electrical connection between terminal blocks and the test equipment. In this way, an electrical contact can be established in the wired state and measurements can be done easily.

## General ordering data

|            |                            |                     |
|------------|----------------------------|---------------------|
| Type       | STB 8.5/D4/2.3/M2.5 AKZ    | Version             |
| Order No.  | <a href="#">0215700000</a> | Accessories, Socket |
| GTIN (EAN) | 4008190184872              |                     |
| Qty.       | 50 pc(s).                  |                     |

## DEK 5/5



## WS/ DEK

MultiMark terminal markers use an innovative composite material made from two components. The hard base contour of the marker snaps securely into the connector. The elastic surface finish makes the marker easy to mount. This specially punched material enables the strips to be stretched to accommodate the slight variations in spacing that tend to add up, especially with long terminal blocks. Another advantage: the excellent printability of the surface material guarantees durable and wear-resistant labelling. A print resolution of 300 dpi also produces a very legible script.

## Your benefits with MultiMark

- Firm hold and durable printing
- Continuous strips save installation time
- Easy mounting thanks to an innovative composite material
- Large label field for optimal legibility
- High flexibility thanks to manufacturer independence

## General ordering data

|            |                            |  |
|------------|----------------------------|--|
| Type       | DEK 5/5 MM WS              | Version  |
| Order No.  | <a href="#">2007110000</a> | Dekafix, Terminal marker, 5 x 5 mm, Weidmueller, white |
| GTIN (EAN) | 4050118391862              |  |
| Qty.       | 800 pc(s).                 |  |

## WDU 2.5/10 BEZ/NE

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Marker holder



The marker holder offer the possibility of additional mounting of standard markers with a pitch of 5 or 5.1 mm. The angled holders can be optionally snapped together and could be mounted in all standard marking channels of the Klippon® Connect modular terminal blocks. Fitting marker types could be found under the respective accessories of the designation marking holder.

## General ordering data

|            |                            |                            |
|------------|----------------------------|----------------------------|
| Type       | BZT 1 ZA WS 10/5           | Version                    |
| Order No.  | <a href="#">1805520000</a> | Accessories, Marker holder |
| GTIN (EAN) | 4032248270248              |                            |
| Qty.       | 100 pc(s).                 |                            |
| Type       | BZT 1 WS 10/5              | Version                    |
| Order No.  | <a href="#">1805490000</a> | Accessories, Marker holder |
| GTIN (EAN) | 4032248270231              |                            |
| Qty.       | 100 pc(s).                 |                            |

## W-Series



Test adapters and test plugs are used for the electrical connection between terminal blocks and the test equipment. In this way, an electrical contact can be established in the wired state and measurements can be done easily.

## General ordering data

|            |                            |  |
|------------|----------------------------|--|
| Type       | WTA 2 WDU2.5-10            | Version                                      |
| Order No.  | <a href="#">1632320000</a> | Test adapter (terminal), 1.5 mm², 250 V, 6 A |
| GTIN (EAN) | 4008190257347              |  |
| Qty.       | 25 pc(s).                  |  |
| Type       | WTA 2/ZA WDU2.5-10         | Version                                      |
| Order No.  | <a href="#">1632330000</a> | Test adapter (terminal), 1.5 mm², 250 V, 6 A |
| GTIN (EAN) | 4008190257330              |  |
| Qty.       | 25 pc(s).                  |  |