

**ESG X20 10/7 MC NE BL****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

ESG is the tried-and-tested marker in MultiCard format for use on many well-known electrical devices. The result is high-quality device marking with a high-contrast appearance.

Various types are available for devices from manufacturers like Siemens, ABB, Beckhoff etc.

Advantages at a glance:

- Tags for universal usage, self-adhesive or clip-on tags, depending on type
- For aligned equipment, e.g. circuit breakers, we supply ESG markers for clipping onto tag rails
- Individual laser-quality printing according to specifications

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

**General ordering data**

|                     |  |
|---------------------|--|
| Version             | ESG, Device markers x 7 mm, PA 66, Colour: blue, pluggable                       |
| Order No.           | <a href="#">1026560000</a>   |
| Type                | ESG X20 10/7 MC NE BL  |
| GTIN (EAN)          | 403224875 1822   |
| Qty.                | 240 pc(s).   |
| Alternative product | <a href="#">1038930000</a>   |
| compatible printer  | <a href="#">2715590000</a> <a href="#">2438520000</a> <a href="#">2438510000</a> |

## ESG X20 10/7 MC NE BL

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Depth      | 0.8 mm  | Depth (inches)  | 0.031 inch |
| Height     | 10 mm   | Height (inches) | 0.394 inch |
| Width      | 7 mm    | Width (inches)  | 0.276 inch |
| Net weight | 0.433 g |                 |            |

## Temperatures

|                             |              |
|-----------------------------|--------------|
| Operating temperature range | -40...100 °C |
|-----------------------------|--------------|

## General data

|  |                              |           |
|--|------------------------------|-----------|
| Application/manufacturer                     | B&R X20 System               |           |
| Colour                                       | blue                         |           |
| Halogen                                      | No                           |           |
| Material                                     | PA 66                        |           |
| Material colour according to resistance code | 6                            |           |
| Number of markers per combination            | 1 MultiCard = Device markers |           |
| Number of markers per packaging unit         | Form of supply               | MultiCard |
| Operating temperature range                  | -40... 100 °C                |           |
| Operating temperature range, max.            | 100 °C                       |           |
| Operating temperature range, min.            | -40 °C                       |           |
| UL 94 flammability rating                    | V-2                          |           |
| Version                                      | pluggable                    |           |
| Width  | 7 mm                         |           |

## Device markers

|         |    |
|---------|----|
| Halogen | No |
|---------|----|

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001288    | ETIM 7.0    | EC001288    |
| ETIM 8.0    | EC001288    | ETIM 9.0    | EC001288    |
| ECLASS 9.0  | 27-40-06-29 | ECLASS 9.1  | 27-40-06-29 |
| ECLASS 10.0 | 27-40-06-29 | ECLASS 11.0 | 27-28-11-04 |
| ECLASS 12.0 | 27-28-11-04 | ECLASS 13.0 | 27-28-11-04 |

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

## Downloads

|                             |  |
|-----------------------------|--|
| Engineering Data            | <a href="#">CAD data – STEP</a>  |
| Product Change Notification | <a href="#">MultiCard Material modification</a><br><a href="#">MultiCard Material Modifikation</a> |
| Catalogues                  | <a href="#">Catalogues in PDF-format</a>   |

### ESG X20 10/7 MC NE BL

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

