

WQV 35-2.5**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image****General ordering data**

Version	Cross-connector (terminal), when screwed in, Number of poles: 3, Pitch in mm (P): 16.00, Insu- lated: Yes, 41 A, yellow
Order No.	1064100000
Type	WQV 35-2.5
GTIN (EAN)	4008190142285
Qty.	10 pc(s).

WQV 35-2.5

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	41.5 mm	Depth (inches)	1.634 inch
Height	21 mm	Height (inches)	0.827 inch
Width	13 mm	Width (inches)	0.512 inch
Net weight	10.721 g		

Temperatures

Storage temperature	-25 °C...55 °C	Continuous operating temp., min.	-60 °C
Continuous operating temp., max.	130 °C		

Material data

Material	PA 66	Colour	yellow
UL 94 flammability rating	V-0		

System specifications

Version	For the terminals
---------	-------------------

Additional technical data

Installation advice	Direct mounting	Type of fixing	when screwed in
---------------------	-----------------	----------------	-----------------

Conductors for clamping (rated connection)

Tightening torque, max.	0.8 Nm	Tightening torque, min.	0.4 Nm
-------------------------	--------	-------------------------	--------

Cross-connector

Number of cross-connected terminals	2	Rated current, multi-pole	24 A
Type	Cross-connector		

Dimensions

Pitch in mm (P)	16 mm
-----------------	-------

General

Installation advice	Direct mounting	Number of poles	3
---------------------	-----------------	-----------------	---

Rating data

Rated current	41 A
---------------	------

Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ETIM 9.0	EC000489
ECLASS 9.0	27-14-11-40	ECLASS 9.1	27-14-11-40
ECLASS 10.0	27-14-11-40	ECLASS 11.0	27-14-11-40
ECLASS 12.0	27-14-11-40	ECLASS 13.0	27-25-03-03

WQV 35-2.5**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
SCIP	3431e478-7f08-4004-abeb-15560ca39d73

Approvals

ROHS	Conform
------	---------

Downloads

Approval/Certificate/Document of Conformity	Confirmation of Standards EN 45545-2_2020-10
Engineering Data	CAD data – STEP
Engineering Data	Zuken E3.S
User Documentation	Beipackzettel_WQV16-2.5.pdf StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format
Brochures	